


**Q 3 WDL2.5S****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image****Building installation wiring**

For building installations, we offer a complete system that revolves around the 10×3 copper rail and comprises perfectly coordinated components: from installation terminal blocks, neutral conductor terminal blocks and distribution terminal blocks to comprehensive accessories such as busbars and busbar holders.

**General ordering data**

|            |  |
|------------|--|
| Version    | Cross-connector (terminal), when screwed in, Number of poles: 3, Pitch in mm (P): 6.10, Insulated: Yes, 24 A, yellow |
| Order No.  | <a href="#">1071600000</a>   |
| Type       | Q 3 WDL2.5S  |
| GTIN (EAN) | 4008190424923  |
| Qty.       | 50 pc(s).  |

## Q 3 WDL2.5S

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 9.5 mm  | Depth (inches)  | 0.374 inch |
| Height     | 16.2 mm | Height (inches) | 0.638 inch |
| Width      | 4 mm    | Width (inches)  | 0.157 inch |
| Net weight | 2.3 g   |                 |            |

## Temperatures

|                     |                |
|---------------------|----------------|
| Storage temperature | -25 °C...55 °C |
|---------------------|----------------|

## Material data

|          |               |        |        |
|----------|---------------|--------|--------|
| Material | tinned copper | Colour | yellow |
|----------|---------------|--------|--------|

## System specifications

|         |                   |
|---------|-------------------|
| Version | For the terminals |
|---------|-------------------|

## Additional technical data

|                          |                 |                     |   |
|--------------------------|-----------------|---------------------|---|
| Explosion-tested version | No              | Installation advice | Feed-through (bushing), Direct mounting |
| Type of fixing           | when screwed in |                     |   |

## Dimensions

|                 |        |
|-----------------|--------|
| Pitch in mm (P) | 6.1 mm |
|-----------------|--------|

## General

|                     |   |                 |   |
|---------------------|---|-----------------|---|
| Installation advice | Feed-through (bushing), Direct mounting | Number of poles | 3 |
|---------------------|---|-----------------|---|

## Rating data

|               |      |
|---------------|------|
| Rated current | 24 A |
|---------------|------|

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000489    | ETIM 7.0    | EC000489    |
| ETIM 8.0    | EC000489    | ETIM 9.0    | EC000489    |
| ECLASS 9.0  | 27-14-11-40 | ECLASS 9.1  | 27-14-11-40 |
| ECLASS 10.0 | 27-14-11-40 | ECLASS 11.0 | 27-14-11-40 |
| ECLASS 12.0 | 27-14-11-40 | ECLASS 13.0 | 27-25-03-03 |

## Environmental Product Compliance

|            |                                      |
|------------|--------------------------------------|
| REACH SVHC | Lead 7439-92-1                       |
| SCIP       | abe9d042-078a-4094-b143-0a6a4ced35a2 |

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Q 3 WDL2.5S

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads

|                    |   |
|--------------------|---|
| Engineering Data   | <a href="#">CAD data – STEP</a>                 |
| Engineering Data   | <a href="#">Zuken E3.S</a>                      |
| User Documentation | <a href="#">StorageConditionsTerminalBlocks</a> |
| Catalogues         | <a href="#">Catalogues in PDF-format</a>        |
| Brochures          |   |