

**VGM32-MS68 15-25 BG****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Similar to illustration**

In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications.

The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure.

Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

**General ordering data**

Version	Heavy-duty connectors, Accessories, Cable glands, Brass, nickel-plated
Order No.	<a href="#">1193610000</a>
Type	VGM32-MS68 15-25 BG
GTIN (EAN)	4032248976621
Qty.	25 pc(s).

## VGM32-MS68 15-25 BG

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Length	40 mm	Length (inches)	1.575 inch
Net weight	112.84 g		

## Temperatures

Limit temperature	-40 °C ... 130 °C
-------------------	-------------------

## General information

AF size	36 mm	Cable glands	M 32
External thread	M 32	Length of thread	8 mm
Material	Brass, nickel-plated	O-Ring	NBR
Protection degree	IP68 - 15 bar	Standards	EN 45545-2:2013
UL 94 flammability rating	V-0		

## Classifications

ETIM 6.0	EC000441	ETIM 7.0	EC000441
ETIM 8.0	EC000441	ETIM 9.0	EC000441
ECLASS 9.0	27-14-44-32	ECLASS 9.1	27-14-44-32
ECLASS 10.0	27-14-44-32	ECLASS 11.0	27-14-44-32
ECLASS 12.0	27-14-08-01	ECLASS 13.0	27-14-08-01

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	b5ff1f66-ddba-4739-9fc0-0521ddb52139

## Approvals

Approvals



ROHS	Conform
------	---------

## Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">FL FIELDWIRING EN</a> <a href="#">FL FIELDWIRING EN</a>