


**WTL 6 SL O.STB****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Current and voltage transformer wiring**

Our test disconnect terminal blocks featuring spring and screw connection technology allow you to create all the important converter circuits for measuring current, voltage and power in a safe and sophisticated way.

**General ordering data**

Version	Test-disconnect terminal, Screw connection, 6 mm <sup>2</sup> , 630 V, 41 A, sliding, Cross-disconnect: without, Integral test socket: No, TS 35, dark beige
Order No.	<a href="#">1238930000</a>
Type	WTL 6 SL O.STB
GTIN (EAN)	4050118025880
Qty.	50 pc(s).

## WTL 6 SL 0.STB

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	50 mm	Depth (inches)	1.969 inch
Height	82.7 mm	Height (inches)	3.256 inch
Width	7.9 mm	Width (inches)	0.311 inch
Net weight	25.82 g		

## Temperatures

Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	120 °C		

## Material data

Material	Wemid	Colour	dark beige
UL 94 flammability rating	V-0		

## System specifications

Version	Screw connection, Special terminal longitudinal isolator, with spring-loaded cable clamp, With sockets, One end without connector	End cover plate required	Yes
Number of levels	1	Number of clamping points per level	2
Levels cross-connected internally	No	PE connection	No
Rail	TS 35		

## Additional technical data

Explosion-tested version	No	Open sides	right
Type of mounting	Snap-on		

## Conductors for clamping (rated connection)

Blade size	0.8 x 4.0 mm	Clamping range, max.	6 mm <sup>2</sup>
Clamping range, min.	0.5 mm <sup>2</sup>	Clamping screw	M 3.5
Connection cross-section, stranded, max.	6 mm <sup>2</sup>	Connection direction	on side
Gauge to IEC 60947-1	A5	Number of connections	2
Stripping length	16 mm	Tightening torque, max.	1.6 Nm
Tightening torque, min.	0.8 Nm	Type of connection	Screw connection
Wire connection cross section, finely stranded, max.	6 mm <sup>2</sup>	Wire connection cross section, finely stranded, min.	0.5 mm <sup>2</sup>
Wire connection cross-section, solid core, max.	6 mm <sup>2</sup>	Wire connection cross-section, solid core, min.	0.5 mm <sup>2</sup>

## Disconnect terminals

Cross-disconnect	without	Integral test socket	No
Slitting	sliding		

## General

Rail	TS 35	Standards	IEC 60947-7-1
------	-------	-----------	---------------

**WTL 6 SL 0.STB****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Rating data**

Rated cross-section	6 mm <sup>2</sup>	Rated voltage	630 V
Rated DC voltage	630 V	Rated current	41 A
Current at maximum wires	57 A	Standards	IEC 60947-7-1
Volume resistance according to IEC 60947-7-x	0.78 mΩ	Power loss in accordance with IEC 60947-7-x	1.31 W
Pollution severity	2	Surge voltage category	III

**Classifications**

ETIM 6.0	EC000902	ETIM 7.0	EC000902
ETIM 8.0	EC000902	ETIM 9.0	EC000902
ECLASS 9.0	27-14-11-26	ECLASS 9.1	27-14-11-26
ECLASS 10.0	27-14-11-26	ECLASS 11.0	27-14-11-26
ECLASS 12.0	27-14-11-26	ECLASS 13.0	27-25-01-09

**Approvals**

Approvals



ROHS

Conform

**Downloads**

Approval/Certificate/Document of Conformity	<a href="#">UKCA declaration of conformity</a> <a href="#">Confirmation of Standards EN 45545-2_2020-10</a>
Engineering Data	<a href="#">CAD data – STEP</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**WTL 6 SL O.STB****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Switch lock**

The switch lock can be easily inserted into the terminal from above. The switch lock prevents unauthorised opening or closing of circuits as it blocks the disconnect lever in its respective position.

**General ordering data**

Type	SSP 3 SAKT1	Version
Order No.	<a href="#">0531760000</a>	Lockout device (terminal), orange
GTIN (EAN)	4008190130787	
Qty.	100 pc(s).	

**W-Series**

Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

**General ordering data**

Type	WEW 35/2	Version
Order No.	<a href="#">1061200000</a>	End bracket, Wemid, dark beige, Rail: TS 35, when screwed in
GTIN (EAN)	4008190030230	
Qty.	50 pc(s).	

## WTL 6 SL 0.STB

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Fixing screws



Fixing screws fix the short current bridge within the application. If the short current bridge is slid between two adjacent terminal blocks into the short circuit position, it can be fixed by means of a fastening screw. This ensures a permanent connection or short circuit.

## General ordering data

Type	BS 25 IH/VI SAKT1	Version
Order No.	<a href="#">0335800000</a>	Mounting screw (Terminal), Depth: 28.7 mm
GTIN (EAN)	4008190039196	
Qty.	50 pc(s).	
Type	BS 25 IH/BL SAKT1	Version
Order No.	<a href="#">0335400000</a>	Mounting screw (Terminal), Depth: 28.7 mm
GTIN (EAN)	4008190086879	
Qty.	50 pc(s).	
Type	BS 25 IH/GR SAKT1	Version
Order No.	<a href="#">0335300000</a>	Mounting screw (Terminal), Depth: 28.7 mm
GTIN (EAN)	4008190136864	
Qty.	50 pc(s).	
Type	BS 25 IH/GN SAKT1	Version
Order No.	<a href="#">0335600000</a>	Mounting screw (Terminal), Depth: 28.7 mm
GTIN (EAN)	4008190113490	
Qty.	50 pc(s).	
Type	BS 25 O.IH SAKT1	Version
Order No.	<a href="#">0334700000</a>	Mounting screw (Terminal), Depth: 28.7 mm
GTIN (EAN)	4008190118839	
Qty.	50 pc(s).	
Type	BS 25 IH/GE SAKT1	Version
Order No.	<a href="#">0335700000</a>	Mounting screw (Terminal), Depth: 28.7 mm
GTIN (EAN)	4008190189235	
Qty.	50 pc(s).	
Type	BS 25 IH/SW SAKT1	Version
Order No.	<a href="#">0335200000</a>	Mounting screw (Terminal), Depth: 28.7 mm
GTIN (EAN)	4008190114039	
Qty.	50 pc(s).	
Type	BS 25 IH/RT SAKT1	Version
Order No.	<a href="#">0335500000</a>	Mounting screw (Terminal), Depth: 28.7 mm
GTIN (EAN)	4008190118877	
Qty.	50 pc(s).	

## WTL 6 SL O.STB

Weidmüller Interface GmbH &amp; Co. KG


Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

10 mm<sup>2</sup>


10  
mm<sup>2</sup>

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

## General ordering data

Type	WQV 10/3	Version
Order No.	<a href="#">1054960000</a>	Cross-connector (terminal), when screwed in, Number of poles: 3,
GTIN (EAN)	4008190079079	Pitch in mm (P): 9.90, Insulated: Yes, 63 A, yellow
Qty.	50 pc(s).	
Type	WQV 10/2	Version
Order No.	<a href="#">1052560000</a>	Cross-connector (terminal), when screwed in, Number of poles: 2,
GTIN (EAN)	4008190154943	Pitch in mm (P): 9.90, Insulated: Yes, 76 A, yellow
Qty.	50 pc(s).	
Type	WQV 10/6	Version
Order No.	<a href="#">2226500000</a>	Cross-connector (terminal), when screwed in, Number of poles: 6,
GTIN (EAN)	4032248793761	Pitch in mm (P): 9.90, Insulated: Yes, 63 A, yellow
Qty.	20 pc(s).	
Type	WQV 10/5	Version
Order No.	<a href="#">2091130000</a>	Cross-connector (terminal), when screwed in, Number of poles: 5,
GTIN (EAN)	4008190215903	Pitch in mm (P): 9.90, Insulated: Yes, 63 A, yellow
Qty.	20 pc(s).	
Type	WQV 10/4	Version
Order No.	<a href="#">1055060000</a>	Cross-connector (terminal), when screwed in, Number of poles: 4,
GTIN (EAN)	4008190188245	Pitch in mm (P): 9.90, Insulated: Yes, 63 A, yellow
Qty.	50 pc(s).	
Type	WQV 10/10	Version
Order No.	<a href="#">1052460000</a>	Cross-connector (terminal), when screwed in, Number of poles: 10,
GTIN (EAN)	4008190152130	Pitch in mm (P): 9.90, Insulated: Yes, 63 A, yellow
Qty.	20 pc(s).	

## WTL 6 SL O.STB

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## WS 12/6.5



## WS/ DEK

MultiMark terminal markers use an innovative composite material made from two components. The hard base contour of the marker snaps securely into the connector. The elastic surface finish makes the marker easy to mount. This specially punched material enables the strips to be stretched to accommodate the slight variations in spacing that tend to add up, especially with long terminal blocks. Another advantage: the excellent printability of the surface material guarantees durable and wear-resistant labelling. A print resolution of 300 dpi also produces a very legible script.

## Your benefits with MultiMark

- Firm hold and durable printing
- Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- Large label field for optimal legibility
- High flexibility thanks to manufacturer independence

## General ordering data

Type	WS 12/6.5 MM WS	Version
Order No.	<a href="#">2619930000</a>	WS, Terminal marker, 12 x 6.5 mm, Weidmueller, white
GTIN (EAN)	4050118626155	
Qty.	600 pc(s).	

## Shorting elements



The short current bridges are inserted into two instrument transformer wiring terminal blocks. By using the short-circuit bridge, the desired short-circuit could be realized within the application for maintenance work.

## General ordering data

Type	QVS 3 SAKT1+2	Version
Order No.	<a href="#">0329300000</a>	Cross-connector (terminal), when screwed in, Number of poles: 3,
GTIN (EAN)	4008190084714	Pitch in mm (P): 12.00, Insulated: Yes, 41 A, beige
Qty.	20 pc(s).	
Type	QVS 2/4 SAKT4	Version
Order No.	<a href="#">1319260000</a>	Cross-connector (terminal), when screwed in, Number of poles: 2,
GTIN (EAN)	4008190136512	Pitch in mm (P): 12.00, Insulated: Yes, 32 A, orange
Qty.	20 pc(s).	

## WTL 6 SL O.STB

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

Type	QVSK 2 SAKT1	Version
Order No.	<a href="#">1670360000</a>	Cross-connector (terminal), when screwed in, Number of poles: 2,
GTIN (EAN)	4008190431242	Pitch in mm (P): 12.00, Insulated: Yes, 57 A, beige
Qty.	20 pc(s).	
Type	QVS 2/S SAKT1+2	Version
Order No.	<a href="#">0358460000</a>	Cross-connector (terminal), when screwed in, Number of poles: 2,
GTIN (EAN)	4008190157937	Pitch in mm (P): 12.00, Insulated: Yes, 41 A, beige
Qty.	20 pc(s).	
Type	QVS 4 SAKT1+2	Version
Order No.	<a href="#">0307400000</a>	Cross-connector (terminal), when screwed in, Number of poles: 4,
GTIN (EAN)	4008190091941	Pitch in mm (P): 12.00, Insulated: Yes, 41 A, beige
Qty.	20 pc(s).	
Type	QVS 2 SAKT1+2	Version
Order No.	<a href="#">0307300000</a>	Cross-connector (terminal), when screwed in, Number of poles: 2,
GTIN (EAN)	4008190036140	Pitch in mm (P): 12.00, Insulated: Yes, 41 A, beige
Qty.	20 pc(s).	

## Blank



WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text. WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with PrintJet CONNECT oder/or Plotter is possible.

- Can be fitted in strips or individually
- Markers in proven MultiCard format

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

Type	WS 12/6.5 MC NE WS	Version
Order No.	<a href="#">1609920000</a>	WS, Terminal marker, 12 x 6.5 mm, Pitch in mm (P): 6.50
GTIN (EAN)	4008190203511	Weidmueller, Allen-Bradley, white
Qty.	540 pc(s).	

**WTL 6 SL 0.STB****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Connection sleeves****General ordering data**

Type	VH 19/6.3/4.3	Version
Order No.	<a href="#">0318000000</a>	Connecting sleeve (terminal), Height: 6 mm, Width: 6 mm, Depth: 19
GTIN (EAN)	4008190059460	mm, Cu Zn
Qty.	50 pc(s).	

**W-Series**

A partition plate is used for the optical separation of circuits or used for electrical isolation from neighbouring cross-connectors. In contrast to the end plate, the contour can be larger than the adjacent terminal blocks. However, it should not be smaller, as otherwise the required clearance and creepage distances within the application can no longer be maintained.

**General ordering data**

Type	WTW EN	Version
Order No.	<a href="#">1058800000</a>	Partition plate (terminal), Intermediate plate, 86 mm x 62 mm, dark
GTIN (EAN)	4008190140175	beige
Qty.	20 pc(s).	

## WTL 6 SL O.STB

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Test sockets



The test socket is used to connect test devices with a standard 4.0 plug. Depending on the potential within the application, different colors of the test sockets can be selected for quick and easy maintenance work.

## General ordering data

Type	STB 21.6/IH/WS WTL6/3	Version
Order No.	<a href="#">1312520000</a>	Socket (terminal), Plug-in depth: 11.1 mm
GTIN (EAN)	4050118121704	
Qty.	50 pc(s).	
Type	STB 21.6/45 VI	Version
Order No.	<a href="#">1936260000</a>	Socket (terminal), Plug-in depth: 11.1 mm, Depth: 45 mm
GTIN (EAN)	4032248605996	
Qty.	50 pc(s).	
Type	STB 36.8/IH/GN WTL6/1	Version
Order No.	<a href="#">1847770000</a>	Socket (terminal), Plug-in depth: 11.1 mm, Depth: 39.8 mm
GTIN (EAN)	4032248379163	
Qty.	50 pc(s).	
Type	STB 21.6/IH/BL WTL6/3	Version
Order No.	<a href="#">1071080000</a>	Socket (terminal), Plug-in depth: 11.1 mm, Depth: 26.6 mm
GTIN (EAN)	4008190043957	
Qty.	50 pc(s).	
Type	STB 21.6/IH/SW WTL6/3	Version
Order No.	<a href="#">1071040000</a>	Socket (terminal), Plug-in depth: 11.1 mm, Depth: 26.6 mm
GTIN (EAN)	4008190859985	
Qty.	50 pc(s).	
Type	STB 36.8/IH/SW WTL6/1	Version
Order No.	<a href="#">1312550000</a>	Socket (terminal), Plug-in depth: 11.1 mm, Depth: 39.8 mm
GTIN (EAN)	4050118181210	
Qty.	50 pc(s).	
Type	STB 36.8/IH/RT WTL6/1	Version
Order No.	<a href="#">1312540000</a>	Socket (terminal), Plug-in depth: 11.1 mm, Depth: 39.8 mm
GTIN (EAN)	4050118180992	
Qty.	50 pc(s).	
Type	STB 21.6/45 GE	Version
Order No.	<a href="#">1936240000</a>	Socket (terminal), Plug-in depth: 11.1 mm, Depth: 45 mm
GTIN (EAN)	4032248605972	
Qty.	50 pc(s).	
Type	STB 21.6/IH/DB WTL6/3	Version
Order No.	<a href="#">1071000000</a>	Socket (terminal), Plug-in depth: 11.1 mm, Depth: 26.6 mm
GTIN (EAN)	4008190259204	
Qty.	50 pc(s).	
Type	STB 21.6/45 SW	Version
Order No.	<a href="#">1936270000</a>	Socket (terminal), Plug-in depth: 11.1 mm, Depth: 45 mm
GTIN (EAN)	4032248606009	
Qty.	50 pc(s).	

## WTL 6 SL O.STB

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

Type	STB 36.8/IH/VI WTL6/1	Version
Order No.	<a href="#">1847780000</a>	Socket (terminal), Plug-in depth: 11.1 mm, Depth: 39.8 mm
GTIN (EAN)	4032248379156	
Qty.	50 pc(s).	
Type	STB 21.6/IH/RT WTL6/3	Version
Order No.	<a href="#">1778990000</a>	Socket (terminal), Plug-in depth: 11.1 mm, Depth: 26.6 mm
GTIN (EAN)	4032248169665	
Qty.	50 pc(s).	
Type	STB 21.6/45 DB	Version
Order No.	<a href="#">1938790000</a>	Socket (terminal), Plug-in depth: 11.1 mm, Depth: 45 mm
GTIN (EAN)	4032248612840	
Qty.	50 pc(s).	
Type	STB 21.6/45 RT	Version
Order No.	<a href="#">1936300000</a>	Socket (terminal), Plug-in depth: 11.1 mm, Depth: 45 mm
GTIN (EAN)	4032248606030	
Qty.	50 pc(s).	
Type	STB 21.6/45 GN	Version
Order No.	<a href="#">1936250000</a>	Socket (terminal), Plug-in depth: 11.1 mm, Depth: 45 mm
GTIN (EAN)	4032248605989	
Qty.	50 pc(s).	
Type	STB 21.6/IH/GE WTL6/3	Version
Order No.	<a href="#">1071010000</a>	Socket (terminal), Plug-in depth: 11.1 mm, Depth: 26.6 mm
GTIN (EAN)	4008190259211	
Qty.	50 pc(s).	
Type	STB 21.6/45 GR	Version
Order No.	<a href="#">1936280000</a>	Socket (terminal), Plug-in depth: 11.1 mm, Depth: 45 mm
GTIN (EAN)	4032248606016	
Qty.	50 pc(s).	
Type	STB 36.8/IH/WS WTL6/1	Version
Order No.	<a href="#">1312560000</a>	Socket (terminal), Plug-in depth: 11.1 mm, Depth: 39.8 mm
GTIN (EAN)	4050118181203	
Qty.	50 pc(s).	
Type	STB 21.6/45 BL	Version
Order No.	<a href="#">1936290000</a>	Socket (terminal), Plug-in depth: 11.1 mm, Depth: 45 mm
GTIN (EAN)	4032248606023	
Qty.	50 pc(s).	
Type	STB 36.8/IH/GE WTL6/1	Version
Order No.	<a href="#">1847760000</a>	Socket (terminal), Plug-in depth: 11.1 mm, Depth: 39.8 mm
GTIN (EAN)	4032248379170	
Qty.	50 pc(s).	
Type	STB 21.6/IH/VI WTL6/3	Version
Order No.	<a href="#">1071030000</a>	Socket (terminal), Plug-in depth: 11.1 mm, Depth: 26.6 mm
GTIN (EAN)	4008190259235	
Qty.	50 pc(s).	
Type	STB 21.6/IH/GN WTL6/3	Version
Order No.	<a href="#">1071020000</a>	Socket (terminal), Plug-in depth: 11.1 mm, Depth: 26.6 mm
GTIN (EAN)	4008190259228	
Qty.	50 pc(s).	
Type	STB 36.8/IH/DB WTL6/1	Version
Order No.	<a href="#">1847740000</a>	Socket (terminal), Plug-in depth: 11.1 mm, Depth: 39.8 mm
GTIN (EAN)	4032248379187	
Qty.	50 pc(s).	

Creation date May 1, 2024 7:56:31 AM CEST

Catalogue status 20.04.2024 / We reserve the right to make technical changes.

## WTL 6 SL O.STB

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26


D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

Type	STB 21.6/IH/BR WTL6/3	Version
Order No.	<a href="#">2715530000</a>	Socket (terminal), Plug-in depth: 11.1 mm, 3.00 mm, Depth: 26.6 mm
GTIN (EAN)	4050118782134	
Qty.	50 pc(s).	
Type	STB 36.8/IH/BL WTL6/1	Version
Order No.	<a href="#">1847790000</a>	Socket (terminal), Plug-in depth: 11.1 mm, Depth: 39.8 mm
GTIN (EAN)	4032248379149	
Qty.	50 pc(s).	

6 mm<sup>2</sup>

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

## General ordering data

Type	WQV 6/10	Version
Order No.	<a href="#">1052260000</a>	Cross-connector (terminal), when screwed in, Number of poles: 10,
GTIN (EAN)	4008190153977	Pitch in mm (P): 8.00, Insulated: Yes, 57 A, yellow
Qty.	20 pc(s).	
Type	WQV 6/12	Version
Order No.	<a href="#">1062720000</a>	Cross-connector (terminal), when screwed in, Number of poles: 12,
GTIN (EAN)	4050118259391	Pitch in mm (P): 8.00, Insulated: Yes, 57 A, yellow
Qty.	50 pc(s).	
Type	WQV 6/4	Version
Order No.	<a href="#">1054860000</a>	Cross-connector (terminal), when screwed in, Number of poles: 4,
GTIN (EAN)	4008190180799	Pitch in mm (P): 8.00, Insulated: Yes, 57 A, yellow
Qty.	50 pc(s).	
Type	WQV 6/3	Version
Order No.	<a href="#">1054760000</a>	Cross-connector (terminal), when screwed in, Number of poles: 3,
GTIN (EAN)	4008190174163	Pitch in mm (P): 8.00, Insulated: Yes, 57 A, yellow
Qty.	50 pc(s).	
Type	WQV 6/6	Version
Order No.	<a href="#">1062670000</a>	Cross-connector (terminal), when screwed in, Number of poles: 6,
GTIN (EAN)	4008190261771	Pitch in mm (P): 8.00, Insulated: Yes, 57 A, yellow
Qty.	50 pc(s).	
Type	WQV 6/2	Version
Order No.	<a href="#">1052360000</a>	Cross-connector (terminal), when screwed in, Number of poles: 2,
GTIN (EAN)	4008190075866	Pitch in mm (P): 8.00, Insulated: Yes, 57 A, yellow
Qty.	50 pc(s).	
Type	WQV 6/7	Version
Order No.	<a href="#">1062680000</a>	Cross-connector (terminal), when screwed in, Number of poles: 7,
GTIN (EAN)	4008190261788	Pitch in mm (P): 8.00, Insulated: Yes, 57 A, yellow
Qty.	50 pc(s).	

## WTL 6 SL 0.STB

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

Type	WQV 6/5	Version
Order No.	<a href="#">1062660000</a>	Cross-connector (terminal), when screwed in, Number of poles: 5,
GTIN (EAN)	4008190176914	Pitch in mm (P): 8.00, Insulated: Yes, 57 A, yellow
Qty.	50 pc(s).	

## Testsockets




Test adapters and test plugs are used for the electrical connection between terminal blocks and the test equipment. In this way, an electrical contact can be established in the wired state and measurements can be done easily.

## General ordering data

Type	GWHUE M3 WTL6	Version
Order No.	<a href="#">1255010000</a>	Connecting sleeve (terminal), Height: 6 mm, Width: 6 mm, Depth:
GTIN (EAN)	4050118075892	13.3 mm, Copper - zinc
Qty.	50 pc(s).	

## Hook-type cable lugs



The use of insulated connectors guarantees users a permanent and consistent quality for their electrical connections.

In addition, they bring advantages during installation.

## General ordering data

Type	HBT 1,5 - 4,6 RT	Version
Order No.	<a href="#">1233340000</a>	cable lug, terminal end, Insulated cable connector, 0.5 mm² - 1.5 mm², red
GTIN (EAN)	4050118210972	
Qty.	100 pc(s).	
Type	HBT 6,0 - 3,0 GE	Version
Order No.	<a href="#">1312470000</a>	cable lug, terminal end, Insulated cable connector, 4 mm² - 6 mm², yellow
GTIN (EAN)	4050118114980	
Qty.	100 pc(s).	
Type	HBT 6,0 - 4,6 GE	Version
Order No.	<a href="#">1216230000</a>	cable lug, terminal end, Insulated cable connector, 4 mm² - 6 mm², yellow
GTIN (EAN)	4050118000337	
Qty.	100 pc(s).	
Type	HBT 1,5 - 3,0 RT	Version
Order No.	<a href="#">1312440000</a>	cable lug, terminal end, Insulated cable connector, 0.5 mm² - 1.5 mm², red
GTIN (EAN)	4050118115055	
Qty.	100 pc(s).	

## WTL 6 SL 0.STB

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold


Germany

www.weidmueller.com

## Accessories

Type	HBT 2,5 - 3,0 BL	Version
Order No.	<a href="#">1312450000</a>	cable lug, terminal end, Insulated cable connector, 1.5 mm <sup>2</sup> - 2.5
GTIN (EAN)	4050118115130	mm <sup>2</sup> , blue
Qty.	100 pc(s).	
Type	HBT 2,5 - 4,6 BL	Version
Order No.	<a href="#">1233330000</a>	cable lug, terminal end, Insulated cable connector, 1.5 mm <sup>2</sup> - 2.5
GTIN (EAN)	4050118016901	mm <sup>2</sup> , blue
Qty.	100 pc(s).	

## Marker holder



The marker holder offer the possibility of additional mounting of standard markers with a pitch of 5 or 5.1 mm. The angled holders can be optionally snapped together and could be mounted in all standard marking channels of the Klippon® Connect modular terminal blocks. Fitting marker types could be found under the respective accessories of the designation marking holder.

## General ordering data

Type	BZT 1 ZA WS 10/5	Version
Order No.	<a href="#">1805520000</a>	Accessories, Marker holder
GTIN (EAN)	4032248270248	
Qty.	100 pc(s).	
Type	BZT 1 WS 10/5	Version
Order No.	<a href="#">1805490000</a>	Accessories, Marker holder
GTIN (EAN)	4032248270231	
Qty.	100 pc(s).	

## End plate



## Current and voltage transformer wiring

Our test disconnect terminal blocks featuring spring and screw connection technology allow you to create all the important converter circuits for measuring current, voltage and power in a safe and sophisticated way.

## General ordering data

Type	WAP WTL6 SL	Version
Order No.	<a href="#">9538110000</a>	End plate (terminals), 82.2 mm x 1.5 mm, dark beige
GTIN (EAN)	4008190574994	
Qty.	20 pc(s).	

**WTL 6 SL 0.STB****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories**

Type	WAP WTL6 SL 4-6	Version
Order No.	<a href="#">1238880000</a>	End plate (terminals), 82.2 mm x 1.5 mm, dark beige
GTIN (EAN)	4050118045680	
Qty.	20 pc(s).	