

IE-SW-VL08MT-6TX-2ST**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

The Value Line from Weidmüller consists of unmanaged and managed switches in a high-quality IP 30 protected metal housing. The equipment can be delivered with Fast Ethernet and Gigabit Ethernet ports. Value Line managed switches support a variety of helpful management functions, such as fast ring redundancy, port-based VLAN, QoS, RMON, bandwidth management, port mirroring and error notification via e-mail or a relay. The ring redundancy can be simply set via the web based management interface, or with a dip switch found on the top of the switch.

- Unmanaged Plug & Play switches in a high-quality metal housing (IP 30)
- Price-conscious middle-range
- Managed switches for the entry into a configurable network infrastructure
- Unmanaged full Gigabit switch with 8 ports
- Approvals: CE, FCC, cULus, Class I Div. 2 / ATEX, DNV / GL

General ordering data

Version	Network switch, managed, Fast Ethernet, Number of ports: 6x RJ45, 2 * ST Multi-mode, IP30, -40 °C...75 °C
Order No.	1240990000
Type	IE-SW-VL08MT-6TX-2ST
GTIN (EAN)	4050118029017
Qty.	1 pc(s).

IE-SW-VL08MT-6TX-2ST

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	105 mm	Depth (inches)	4.134 inch
Height	135 mm	Height (inches)	5.315 inch
Width	53.6 mm	Width (inches)	2.11 inch
Net weight	890 g		

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...75 °C
Humidity	5 to 95 % (non-condensing)		

EMC conformity and approvals

EMC standards	EN 55032, EN 55024, CISPR 32, FCC Part 15 Subpart B Class A, IEC 61000-4-2 ESD: Contact: 6 kV; Air: 8 kV, IEC 61000-4-3 RS: 80 MHz to 1 GHz: 20 V/m, IEC 61000-4-4 EFT: Power: 2 kV; Signal: 1 kV, IEC 61000-4-5 Surge: Power: 2 kV; Signal: 2 kV, IEC 61000-4-6 CS: 10 V, IEC 61000-4-8	Explosive risk zone	UL/cUL, Class I, Division 2, Groups A, B, C and D, ATEX Zone 2 Ex nA nC IIC T4 Gc
Free fall	According to IEC 60068-2-32	Safety standard	UL508, UL 60950-1, EN 60950-1
Ship use	DNV	Shock	according to IEC 60068-2-27
Vibration	according to IEC 60068-2-6		

Environmental conditions

Humidity	5 to 95 % (non-condensing)	Operating temperature, max.	75 °C
Operating temperature, min.	-40 °C	Storage temperature, max.	85 °C
Storage temperature, min.	-40 °C		

Fibre optic transceiver characteristics

Transmission rate	100 Mbps		
Transceiver type	Multimode		
Connector type	ST-Duplex		
Transmission distance, typ.	5 km		
Wavelength	typ.	1,300 nm	
	Wavelength	TX	
	min.	1,260 nm	
	max.	1,360 nm	
	Wavelength	RX	
	min.	1,100 nm	
	max.	1,600 nm	
Receive power	min.	-32 dBm	
	max.	-3 dBm	
Transmission power	min.	-20 dBm	
	max.	-10 dBm	

Creation date April 29, 2024 4:39:46 AM CEST

IE-SW-VL08MT-6TX-2ST

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Guarantee

Time interval	5 years
---------------	---------

Interfaces

Alarm contact	1 relay output with a current capacity of 1 A at 24 V DC	Console port interface	RS-232
Fibre-optic ports	100BaseFX ports (ST connector), Multimode	Function DIP switch	Turbo-Ring, Master, Coupler, Reserve
LED indicator	PWR1, PWR2, FAULT, MSTR/HEAD, CPLR/TAIL, 10/100M (TP-Port), 100M (fibre-optic port).	Number of ports	6x RJ45, 2 * ST Multi-mode
RJ45 ports	10/100BaseT(X), auto negotiation, Full/half-duplex mode, Auto MDI/MDI-X port		

MTBF

MTBF	According to Standard	Telcordia (Bellcore), GB
	Operating time (hours), min.	1,277,138 h

Management features

Device configuration	Webbrowser (HTTP/HTTPS), SNMP v1/v2c/v3, Telnet console, Local serial console port (RS-232 via RJ-45 port), Windows tool	Monitoring function	SNMP v1/v2c/v3, Link Layer Discovery Protocol (LLDP), Port mirroring, Port statistics, Port monitoring, Syslog, RMON (Remote monitoring), Event based warning via E-Mail, Event based warning via relay, Event based warning via SNMP trap
Network redundancy	Spanning Tree Protocol (STP), Rapid Spanning Tree Protocol (RSTP), Turbo-Ring (recovery time <20 ms), Turbo-Chain (recovery time <20 ms)	Network traffic filter	Quality of Service (QoS), Tag based VLAN, Port based VLAN, IGMP v1/v2, GMRP, Traffic Rate Limiting
IP-address management	Static, BootP, RARP, DHCP-Client, DHCP-Server (port based), DHCP Option 82 (Relay Agent)	Security functions	VLAN segmentation, Enable/disable ports, Loop protection
Time synchronization management	SNTP client, NTP client	Industrial protocol support	PROFINET device acc. to conformance class B, EtherNet/IP, Modbus/TCP slave

Power supply

Connection type	1 removable 6-pin terminal block
Current consumption	Voltage 24 V
	Current 0.35 A
Overload current protection	Yes
Reverse polarity protection	Yes
Voltage supply	12/24/48 V DC, 2 redundant inputs

Creation date April 29, 2024 4:39:46 AM CEST

Catalogue status 20.04.2024 / We reserve the right to make technical changes.

IE-SW-VL08MT-6TX-2ST

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Voltage supply range	Voltage type	DC
	Voltage, min.	9.6 V
	Voltage, max.	60 V

Switch characteristics

Bandwidth backplane	1.6 Gbit/s	IGMP-Groups	256
MAC table size	8 K	Max. number of available VLANs	64
Packet buffer size	1 Mbit	Priority queues	4
VLAN-ID max	4,094	VLAN-ID min	1

Technical data

Housing main material	metal	Protection degree	IP30
Speed	Fast Ethernet	Switch	managed
Type of mounting	DIN rail, Panel (with optional mounting kit)		

Technology

Data switching	Store and Forward	Flow control	IEEE 802.3x flow control, Back pressure flow control
MIB	MIB-II, Ethernet-Like MIB, P-BRIDGE MIB, Bridge MIB, RSTP MIB, RMON MIB Group 1, 2, 3, 9	Standard	IEEE 802.3 for 10BaseT, IEEE 802.3u for 100BaseT(X) and 100BaseFX, IEEE 802.3x for flow control, IEEE 802.1D-2004 for the Spanning Tree protocol, IEEE 802.1w for Rapid STP, IEEE 802.1p for Class of Service, IEEE 802.1Q for VLAN tagging

Classifications

ETIM 6.0	EC000734	ETIM 7.0	EC000734
ETIM 8.0	EC000734	ETIM 9.0	EC000734
ECLASS 9.0	19-17-01-06	ECLASS 9.1	19-17-01-06
ECLASS 10.0	19-17-04-01	ECLASS 11.0	19-17-04-01
ECLASS 12.0	19-17-04-01	ECLASS 13.0	19-17-04-01

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	9229992a-00b9-4096-8962-200a7f33e289

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E230683
Certificate no. (cULusEX)	E344136

Creation date April 29, 2024 4:39:46 AM CEST

Catalogue status 20.04.2024 / We reserve the right to make technical changes.

IE-SW-VL08MT-6TX-2ST**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Downloads**

Approval/Certificate/Document of Conformity	ODVA Certificate DNV certificate ATEX certificate EU Declaration of Conformity UK Declaration of Conformity
Engineering Data	CAD data – STEP
Product Change Notification	Firmware Release Notes Product Change Notification IE-SW-VL08MT-series
Software	Software – Managed Switch Configuration Utility Device description – SNMP MIB file Device description – GSDML IE-SW-VL08M-series Firmware – Firmware Version 3.5.22 Device description – EDS IE-SW-VL08M-series
User Documentation	Hardware Installation Guide Manual 20191204 Security Advisory - Multiple vulnerabilities in IE Managed Switches
Catalogues	Catalogues in PDF-format
Brochures	

IE-SW-VL08MT-6TX-2ST**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Configuration backup and restore module (for use with switches of Value- and PremiumLine such as Basic- and ValueLine WLAN devices)****Module for saving and loading a device configuration**

- Reduced system downtime by simple reconfiguration if equipment is swapped over
- Automatic loading of the saved configuration possible after device restart
- Compact and robust design
- Useable with all Weidmüller managed switches and industrial WLAN devices

General ordering data

Type	EBR-MODULE RS232	Version
Order No.	1241430000	Configuration module, IP40, 0 °C...60 °C
GTIN (EAN)	4050118029086	
Qty.	1 pc(s).	

Mounting kit for 19" rack assembly

- For assembling DIN rail-based devices on 19" racks

**General ordering data**

Type	RM-KIT	Version
Order No.	1241440000	Kit for 19"-rack mounting
GTIN (EAN)	4050118029154	
Qty.	1 pc(s).	

IE-SW-VL08MT-6TX-2ST**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Ethernet**

- Suitable for Cat. 5 (up to 100 MHz) and Cat. 6 (up to 250 MHz Class E)
- Suitable for PoE+ (according to IEEE 802.3at, IEEE 802.3bt Type 3 and 4)
- Protection of all wire pairs
- Connection via RJ45 sockets
- Metal housing

General ordering data

Type	VDATA CAT6	Version
Order No.	1348590000	Terminal rail fixing, Surge protection, Cat.6, PoE, 802.3 bt at Type 1,
GTIN (EAN)	4050118153002	802.3 bt at Type 2, 802.3 bt at Type 3, 802.3 bt at Type 4
Qty.	1 pc(s).	