

UR20-8DI-P-2W

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image

**Digital input modules P- or N-switching; Reverse polarity protection, up to 3-wire +FE**

Digital input modules from Weidmüller are available in different versions and are used primarily to receive binary control signals from sensors, transmitters, switches or proximity switches. Thanks to their flexible design, they will satisfy your need for well co-ordinated project planning with reserve potential.

All modules are available with 4, 8 or 16 inputs and comply fully with IEC 61131-2. The digital input modules are available as P- or N-switching variant. The digital inputs are for Type 1 and Type 3 sensors in accordance with the standard. With a maximum input frequency of up to 1 kHz, they are used in many different applications. The variant for PLC interface units enables rapid cabling to the proven Weidmüller interface sub-assemblies using system cables. This ensures rapid incorporation into your overall system. Two modules with a timestamp function are able to capture binary signals and to provide a timestamp in 1 µs resolution. Further solutions are possible with the mod-

ule UR20-4DI-2W-230V-AC which works with accurate current up to 230V as an input signal.

The module electronics supply the connected sensors from the input current path (U_{IN}).

General ordering data

| | |
|-------------------|--|
| Version | Remote I/O module, IP20, Digital signals, Input, 8-channel, 2-conductor connection |
| Order No. | 1315180000 |
| Type | UR20-8DI-P-2W |
| GTIN (EAN) | 4050118118155 |
| Qty. | 1 pc(s). |
| Replacement parts | 1350930000 1346430000 1490220000 |

UR20-8DI-P-2W

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|-----------------------------|---------|-----------------|------------|
| Depth | 76 mm | Depth (inches) | 2.992 inch |
| Height | 120 mm | Height (inches) | 4.724 inch |
| Width | 11.5 mm | Width (inches) | 0.453 inch |
| Mounting dimension - height | 128 mm | Net weight | 85 g |

Temperatures

| | | | |
|---------------------|-------------------|-----------------------|-------------------|
| Storage temperature | -40 °C ... +85 °C | Operating temperature | -20 °C ... +60 °C |
|---------------------|-------------------|-----------------------|-------------------|

digital inputs

| | | | |
|------------------------------|--------|--------------------------|---------------------------|
| Individual channel diagnosis | No | Input filter | configurable |
| Input voltage, high | > 11 V | Input voltage, low | < 5 V |
| Module diagnosis | Yes | Number of digital inputs | 8 |
| Reverse polarity protection | Yes | Sensor connection | 2-wire |
| Sensor supply | Yes | Type | Types 1 and 3, EN 61131-2 |

Connection data

| | | | |
|--|----------------------|--|----------------------|
| Type of connection | PUSH IN | Wire connection cross section, finely stranded, max. | 1.5 mm ² |
| Wire connection cross section, finely stranded, min. | 0.14 mm ² | Wire cross-section, finely stranded, max. (AWG) | AWG 16 |
| Wire cross-section, finely stranded, min. (AWG) | AWG 26 | Wire cross-section, solid, max. | 1.5 mm ² |
| Wire cross-section, solid, max. (AWG) | AWG 16 | Wire cross-section, solid, min. | 0.14 mm ² |
| Wire cross-section, solid, min. (AWG) | AWG 26 | | |

General data

| | | | |
|--------------------------|--|---------------------------|--|
| Air humidity (operation) | 10% to 95%, non-condensing as per DIN EN 61131-2 | Air humidity (storage) | 10% to 95%, non-condensing as per DIN EN 61131-2 |
| Air humidity (transport) | 10% to 95%, non-condensing as per DIN EN 61131-2 | Air pressure (operation) | ≥ 795 hPa (height ≤ 2000 m) as per DIN EN 61131-2 |
| Air pressure (storage) | 1013 hPa (height 0 m) to 700 hPa (height 3000 m) as per DIN EN 61131-2 | Air pressure (transport) | 1013 hPa (height 0 m) to 700 hPa (height 3000 m) as per DIN EN 61131-2 |
| Pollution severity | 2 | Rail | TS 35 |
| Shock | 15 g over 11 ms, half sinus wave, acc. to IEC 60068-2-27 | Surge voltage category | II |
| Test voltage | 500 V | UL 94 flammability rating | V-0 |
| Vibration resistance | 5 Hz ≤ f ≤ 8.4 Hz: 3.5-mm amplitude as per IEC 60068-2-6, 8.4 Hz ≤ f ≤ 150 Hz: 1 g acceleration as per IEC 60068-2-6 | | |

Power supply

| | | | |
|--|---|-----------------------------|-----|
| Current consumption from I _{sys} , typ. | 8 mA | Reverse polarity protection | Yes |
| Voltage supply | 24 V DC +20 %/-15 %, via the system bus | | |

UR20-8DI-P-2W

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

System data

| | | | |
|--|---|--------------------|------------------------------------|
| Connection type | PUSH IN | Diagnostic data | 1 Bit |
| Field bus protocol | PROFINET IRT, PROFINET RT, PROFIBUS DP-V1, EtherCAT, Modbus/TCP, EtherNet/IP, CANopen, DeviceNet, POWERLINK, CC-Link, CC-Link IE TSN, IEC 61162-450 | Galvanic isolation | 500 V DC between the current paths |
| Interface | u-remote system bus | Module type | Digital input module |
| Possible connection | 2-wire, Single-conductor | Process data | 1 Byte |
| Transmission speed of system bus, max. 48 Mbit | | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001599 | ETIM 7.0 | EC001599 |
| ETIM 8.0 | EC001599 | ETIM 9.0 | EC001599 |
| ECLASS 9.0 | 27-24-26-04 | ECLASS 9.1 | 27-24-26-04 |
| ECLASS 10.0 | 27-24-26-04 | ECLASS 11.0 | 27-24-26-04 |
| ECLASS 12.0 | 27-24-26-04 | ECLASS 13.0 | 27-24-26-04 |

Approvals

Approvals



| | |
|---------------------------|------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate no. (cULus) | E141197 |
| Certificate no. (cULusEX) | E223527 |

UR20-8DI-P-2W**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Downloads**

| | |
|---|---|
| Approval/Certificate/Document of Conformity | KC certificate |
| | Compass safe distance certificate |
| | Lloyds Register certificate |
| | DNV/GL certificate |
| | ABS certificate |
| | RINA certificate |
| | Bureau Veritas - Type Approval Certificate |
| | PRS (Polish Register of Shipping) |
| | NIPPON KAIJI KYOKAI Certificate |
| | DEMKO 15ATEX1525X |
| | CCC certificate |
| | CCS certificate |
| | UKCA Declaration of Conformity - EN |
| | CE Declaration of Conformity - DE |
| Engineering Data | CAD data – STEP |
| | Compatibility information – Combinability of UR20 |
| Engineering Data | Zuken E3.S |
| User Documentation | MAN_U-REMOTE_DE |
| | MAN_U-REMOTE_EN |
| Catalogues | Catalogues in PDF-format |


UR20-8DI-P-2W

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany


www.weidmueller.com

Drawings

Block diagram




Connection diagram



Explanation of abbreviations


Digital input modules



UR20-8DI-P-2W

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Replacement parts**Plugkit****General ordering data**

| | | |
|------------|----------------------------|--|
| Type | UR20-PK-1315180000-SP | Version |
| Order No. | 1346430000 | Replacement part, Plug-in connector, , |
| GTIN (EAN) | 4050118151350 | |
| Qty. | 5 pc(s). | |

Basic modules**General ordering data**


| | | | |
|------------|----------------------------|--|---------------|
| Type | UR20-BM-SP | Version | Packaging |
| Order No. | 1350930000 | Replacement part, , Flange-mounted housing | Cardboard box |
| GTIN (EAN) | 4050118402735 | | |
| Qty. | 5 pc(s). | | |

UR20-8DI-P-2W**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Replacement parts****Electronic modules****General ordering data**

| | | |
|------------|----------------------------|------------------|
| Type | UR20-EM-1315180000-SP | Version |
| Order No. | 1490220000 | Replacement part |
| GTIN (EAN) | 4050118299588 | |
| Qty. | 1 pc(s). | |

UR20-8DI-P-2W

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Accessories




System accessory

Discover a wide range of accessories for your u-remote system - the ideal addition to make your applications even more efficient and flexible.

General ordering data

| | | |
|------------|----------------------------|----------------|
| Type | UR20-EBK-ACC | Version |
| Order No. | 1346610000 | End bracket, , |
| GTIN (EAN) | 4050118151596 | |
| Qty. | 5 pc(s). | |
| Type | UR20-SM-ACC | Version |
| Order No. | 1339920000 | Cover, , |
| GTIN (EAN) | 4050118144727 | |
| Qty. | 20 pc(s). | |

Custom printing



General ordering data

| | | |
|------------|----------------------------|---|
| Type | PM 2.7/2.6 MC SDR | Version |
| Order No. | 1323700000 | OMNIMATE Signal - series PM, Pusher markers, 2.7 x 2.6 mm, Pitch in |
| GTIN (EAN) | 4050118126761 | mm (P): 3.50 Weidmueller, To customer specification |
| Qty. | 192 pc(s). | |

UR20-8DI-P-2W

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Blank



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | DEK 5/8-11.5 MC NE WS | Version |
| Order No. | 1341630000 | Dekafix, Terminal marker, 5 x 8 mm, Pitch in mm (P): 8.00 |
| GTIN (EAN) | 4050118145946 | Weidmueller, white |
| Qty. | 500 pc(s). | |

Blank



General ordering data

| | | |
|------------|----------------------------|---|
| Type | PM 2.7/2.6 MC NE WS | Version |
| Order No. | 1323710000 | OMNIMATE Signal - series PM, Pusher markers, 2.7 x 2.6 mm, Pitch in |
| GTIN (EAN) | 4050118126778 | mm (P): 3.50 Weidmueller, white |
| Qty. | 960 pc(s). | |

UR20-8DI-P-2W**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Steel**

Steel DIN rails are the most widespread on the market. Among metal DIN rails, they have the lowest shortcircuit protection, similar to stainless steel.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | TS 35X7.5 2M/ST/ZN | Version |
| Order No. | 0383400000 | Terminal rail, without slot, Accessories, 35 x 7.5 x 2000 mm, Steel, |
| GTIN (EAN) | 4008190088026 | galvanic zinc plated and passivated |
| Qty. | 2 m | |
| Type | TS 35X7.5/LL 1M/ST/ZN | Version |
| Order No. | 0514510000 | Terminal rail, with slot, Accessories, 35 x 7.5 x 1000 mm, Slit width: |
| GTIN (EAN) | 4008190116620 | 5.20 mm, Slit length: 25.00 mm, Steel, galvanic zinc plated and |
| Qty. | 1 m | passivated |
| Type | TS 35X7.5/LL 2M/ST/ZN | Version |
| Order No. | 0514500000 | Terminal rail, with slot, Accessories, 35 x 7.5 x 2000 mm, Slit width: |
| GTIN (EAN) | 4008190046019 | 5.20 mm, Slit length: 25.00 mm, Steel, galvanic zinc plated and |
| Qty. | 2 m | passivated |
| Type | TS 35X7.5/LL 2M/ST/SZ | Version |
| Order No. | 7915060000 | Terminal rail, with slot, Accessories, 35 x 7.5 x 2000 mm, Slit width: |
| GTIN (EAN) | 4032248296279 | 5.20 mm, Slit length: 25.00 mm, Steel, galvanic zinc plated and |
| Qty. | 2 m | passivated |

UR20-8DI-P-2W

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Custom printing



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | DEK 5/8-11.5 MC SDR | Version |
| Order No. | 1341610000 | Dekafix, Terminal marker, 5 x 8 mm, Pitch in mm (P): 8.00 |
| GTIN (EAN) | 4050118146059 | Weidmueller, To customer specification |
| Qty. | 100 pc(s). | |

Stainless steel



Stainless steel is a collective term for all types of steel (alloys) with a high degree of purity and corrosion resistance.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | TS 35X7.5 2M/CRN | Version |
| Order No. | 1747350000 | Terminal rail, without slot, Accessories, 35 x 7.5 x 2000 mm, |
| GTIN (EAN) | 4032248003372 | Stainless steel, rust-proof, Stainless steel 1.4301, untreated |
| Qty. | 2 m | |

UR20-8DI-P-2W**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Aluminum**

Aluminum has the second best electrical conductivity after copper. One advantage is low weight, anMiscellaneous is outstanding corrosion protection.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | TS 35X7.5 2M/AL/BK | Version |
| Order No. | 0330800000 | Terminal rail, without slot, Accessories, 35 x 7.5 x 2000 mm, |
| GTIN (EAN) | 4008190100650 | Aluminium, untreated |
| Qty. | 2 m | |