

SAIE-M12S-8S2.0U HW**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Various build-in connectors are required for the connections on the device side of the sensor/actuator cabling. These are available in the versions M12, M8 and M5.

General ordering data

Version	Built-in plugs, M12, PG 9, Number of poles: 8, 2 m
Order No.	1341240200
Type	SAIE-M12S-8S2.0U HW
GTIN (EAN)	4050118145694
Qty.	1 pc(s).

SAIE-M12S-8S2.0U HW**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Net weight	129 g
------------	-------

Technical specifications for cable

Cable length	2 m	Core cross-section	0.25 mm ²
Number of poles	8	PE function	No
Sheathing colour	black		

Technical data customisable plug-in connectors

Cable glands	PG 9	Coding	A-coded
Contact surface	Gold-plated	Housing main material	Zinc diecast, nickel-plated
Number of poles	8	Protection degree	IP68
Rated current		Rated current	4 A (3-, 4- and 5-pole) / 1.5 A (8-pole)
	2 A	Temperature range of housing	-5 ... +70 °C
Rated voltage	60 V		
Type of connection	Pin		

Classifications

ETIM 6.0	EC002635	ETIM 7.0	EC003570
ETIM 8.0	EC003570	ETIM 9.0	EC003570
ECLASS 9.0	27-44-01-03	ECLASS 9.1	27-44-01-03
ECLASS 10.0	27-44-01-03	ECLASS 11.0	27-44-01-03
ECLASS 12.0	27-44-01-03	ECLASS 13.0	27-44-01-03

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	ebf89fc8-a87f-4691-b87a-dfb9921774b4

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN FL FIELDWIRING EN


SAIE-M12S-8S2.0U HW

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Wiring diagram



Pole scheme

