


**WTL 6/1/TNSC/EN****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image****Current and voltage transformer wiring**

Our test disconnect terminal blocks featuring spring and screw connection technology allow you to create all the important converter circuits for measuring current, voltage and power in a safe and sophisticated way.

**General ordering data**

Version	Test-disconnect terminal, Screw connection, 6 mm <sup>2</sup> , 630 V, 41 A, sliding, Cross-disconnect: without, Integral test socket: No, TS 35, dark beige
Order No.	<a href="#">1345280000</a>
Type	WTL 6/1/TNSC/EN
GTIN (EAN)	4050118180985
Qty.	50 pc(s).

## WTL 6/1/TNSC/EN

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	66 mm	Depth (inches)	2.598 inch
Depth including DIN rail	66.5 mm	Height	65 mm
Height (inches)	2.559 inch	Width	7.9 mm
Width (inches)	0.311 inch	Net weight	23.34 g

## Temperatures

Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	120 °C		

## Material data

Material	Wemid	Colour	dark beige
UL 94 flammability rating	V-0		

## System specifications

Version	Screw connection, Spacer, for screwable cross-connection, One end without connector	End cover plate required	Yes
Number of potentials	1	Number of levels	1
Number of clamping points per level	2	Number of potentials per tier	1
Levels cross-connected internally	No	PE connection	No
Rail	TS 35	N-function	No
PE function	No	PEN function	No

## 2 clampable conductors (H05V/H07V) with equal cross-section (rated connection)

Wire connection cross section, finely stranded with wire-end ferrules DIN 46228/1, 2 clampable wires, max.	2.5 mm <sup>2</sup>	Wire connection cross section, finely stranded with wire-end ferrules DIN 46228/1, 2 clampable wires, min.	0.5 mm <sup>2</sup>
Wire connection cross section, finely stranded, two clampable wires, min.	0.5 mm <sup>2</sup>	Wire cross-section, finely stranded, two clampable wires, max.	2.5 mm <sup>2</sup>

## Additional technical data

Explosion-tested version	No	Open sides	right
Type of mounting	Snap-on		

## WTL 6/1/TNSC/EN

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Conductors for clamping (rated connection)

Blade size	0.8 x 4.0 mm	Clamping range, max.	10 mm <sup>2</sup>
Clamping range, min.	0.5 mm <sup>2</sup>	Clamping screw	M 3.5
Connection cross-section, stranded, min.	1.5 mm <sup>2</sup>	Connection direction	on side
Gauge to IEC 60947-1	A5	Number of connections	2
Stripping length	12 mm	Tightening torque, max.	1.6 Nm
Tightening torque, min.	1 Nm	Torque level with DMS electric screw-driver	3
Type of connection	Screw connection	Wire connection cross section AWG, max.	AWG 8
Wire connection cross section AWG, min.	AWG 20	Wire connection cross section, finely stranded, max.	10 mm <sup>2</sup>
Wire connection cross section, finely stranded, min.	0.5 mm <sup>2</sup>	Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max.	6 mm <sup>2</sup>
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min.	0.5 mm <sup>2</sup>	Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max.	6 mm <sup>2</sup>
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min.	0.5 mm <sup>2</sup>	Wire connection cross-section, solid core, max.	10 mm <sup>2</sup>
Wire connection cross-section, solid core, min.	0.5 mm <sup>2</sup>		

## Disconnect terminals

Cross-disconnect	without	Integral test socket	No
Slitting	sliding	Torque max. screw separator	0.6 Nm
Torque min. screw separator	0.5 Nm		

## General

Rail	TS 35	Wire connection cross section AWG, max.	AWG 8
Wire connection cross section AWG, min.	AWG 20		

## Rating data

Rated cross-section	6 mm <sup>2</sup>	Rated voltage	630 V
Rated DC voltage	630 V	Rated current	41 A
Current at maximum wires	57 A	Volume resistance according to IEC 60947-7-x	0.78 mΩ
Rated impulse withstand voltage	6 kV	Power loss in accordance with IEC 60947-7-x	1.31 W
Pollution severity	3		

## Classifications

ETIM 6.0	EC000902	ETIM 7.0	EC000902
ETIM 8.0	EC000902	ETIM 9.0	EC000902
ECLASS 9.0	27-14-11-26	ECLASS 9.1	27-14-11-26
ECLASS 10.0	27-14-11-26	ECLASS 11.0	27-14-11-26
ECLASS 12.0	27-14-11-26	ECLASS 13.0	27-25-01-09

## WTL 6/1/TNSC/EN

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	0eb7d846-d0a1-43e5-93a4-d7c6856c4cda

## Approvals

Approvals



ROHS	Conform
------	---------

## Downloads

Approval/Certificate/Document of Conformity	<a href="#">CE Declaration of Conformity</a> <a href="#">UKCA declaration of conformity</a> <a href="#">Confirmation of Standards EN 45545-2_2020-10</a>
Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">Zuken E3.S</a>
User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

### WTL 6/1/TNSC/EN

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings



## WTL 6/1/TNSC/EN

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Fixing screws



Fixing screws fix the short current bridge within the application. If the short current bridge is slid between two adjacent terminal blocks into the short circuit position, it can be fixed by means of a fastening screw. This ensures a permanent connection or short circuit.

## General ordering data

Type	BS 25 IH/VI SAKT1	Version
Order No.	<a href="#">0335800000</a>	Mounting screw (Terminal), Depth: 28.7 mm
GTIN (EAN)	4008190039196	
Qty.	50 pc(s).	
Type	BS 25 O.IH SAKT1	Version
Order No.	<a href="#">0334700000</a>	Mounting screw (Terminal), Depth: 28.7 mm
GTIN (EAN)	4008190118839	
Qty.	50 pc(s).	
Type	KISC M3X20 SAK 10 CU5	Version
Order No.	<a href="#">0377100000</a>	SAK Series, Mounting screw, Copper
GTIN (EAN)	4008190060350	
Qty.	100 pc(s).	
Type	BS 25 IH/GR SAKT1	Version
Order No.	<a href="#">0335300000</a>	Mounting screw (Terminal), Depth: 28.7 mm
GTIN (EAN)	4008190136864	
Qty.	50 pc(s).	
Type	BS 25 IH/SW SAKT1	Version
Order No.	<a href="#">0335200000</a>	Mounting screw (Terminal), Depth: 28.7 mm
GTIN (EAN)	4008190114039	
Qty.	50 pc(s).	
Type	BS 25 IH/RT SAKT1	Version
Order No.	<a href="#">0335500000</a>	Mounting screw (Terminal), Depth: 28.7 mm
GTIN (EAN)	4008190118877	
Qty.	50 pc(s).	
Type	BS 25 IH/BL SAKT1	Version
Order No.	<a href="#">0335400000</a>	Mounting screw (Terminal), Depth: 28.7 mm
GTIN (EAN)	4008190086879	
Qty.	50 pc(s).	
Type	BS 25 IH/GE SAKT1	Version
Order No.	<a href="#">0335700000</a>	Mounting screw (Terminal), Depth: 28.7 mm
GTIN (EAN)	4008190189235	
Qty.	50 pc(s).	
Type	BS 25 IH/GN SAKT1	Version
Order No.	<a href="#">0335600000</a>	Mounting screw (Terminal), Depth: 28.7 mm
GTIN (EAN)	4008190113490	
Qty.	50 pc(s).	

## WTL 6/1/TNSC/EN

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## DEK 5/8



## WS/ DEK

MultiMark terminal markers use an innovative composite material made from two components. The hard base contour of the marker snaps securely into the connector. The elastic surface finish makes the marker easy to mount. This specially punched material enables the strips to be stretched to accommodate the slight variations in spacing that tend to add up, especially with long terminal blocks. Another advantage: the excellent printability of the surface material guarantees durable and wear-resistant labelling. A print resolution of 300 dpi also produces a very legible script.

## Your benefits with MultiMark

- Firm hold and durable printing
- Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- Large label field for optimal legibility
- High flexibility thanks to manufacturer independence

## General ordering data

Type	DEK 5/8 MM WS	Version
Order No.	<a href="#">2007130000</a>	Dekafix, Terminal marker, 5 x 8 mm, Weidmueller, white
GTIN (EAN)	4050118392012	
Qty.	500 pc(s).	

## Test sockets



The test socket is used to connect test devices with a standard 4.0 plug. Depending on the potential within the application, different colors of the test sockets can be selected for quick and easy maintenance work.

## General ordering data

Type	STB 21.6/45 GR	Version
Order No.	<a href="#">1936280000</a>	Socket (terminal), Plug-in depth: 11.1 mm, Depth: 45 mm
GTIN (EAN)	4032248606016	
Qty.	50 pc(s).	
Type	STB 21.6/IH/GN WTL6/3	Version
Order No.	<a href="#">1071020000</a>	Socket (terminal), Plug-in depth: 11.1 mm, Depth: 26.6 mm
GTIN (EAN)	4008190259228	
Qty.	50 pc(s).	

## WTL 6/1/TNSC/EN

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

Type	STB 21.6/IH/VI WTL6/3	Version
Order No.	<a href="#">1071030000</a>	Socket (terminal), Plug-in depth: 11.1 mm, Depth: 26.6 mm
GTIN (EAN)	4008190259235	
Qty.	50 pc(s).	
Type	STB 21.6/45 DB	Version
Order No.	<a href="#">1938790000</a>	Socket (terminal), Plug-in depth: 11.1 mm, Depth: 45 mm
GTIN (EAN)	4032248612840	
Qty.	50 pc(s).	
Type	STB 21.6/IH/WS WTL6/3	Version
Order No.	<a href="#">1312520000</a>	Socket (terminal), Plug-in depth: 11.1 mm
GTIN (EAN)	4050118121704	
Qty.	50 pc(s).	
Type	STB 36.8/IH/WS WTL6/1	Version
Order No.	<a href="#">1312560000</a>	Socket (terminal), Plug-in depth: 11.1 mm, Depth: 39.8 mm
GTIN (EAN)	4050118181203	
Qty.	50 pc(s).	
Type	STB 36.8/IH/SW WTL6/1	Version
Order No.	<a href="#">1312550000</a>	Socket (terminal), Plug-in depth: 11.1 mm, Depth: 39.8 mm
GTIN (EAN)	4050118181210	
Qty.	50 pc(s).	
Type	STB 36.8/IH/GN WTL6/1	Version
Order No.	<a href="#">1847770000</a>	Socket (terminal), Plug-in depth: 11.1 mm, Depth: 39.8 mm
GTIN (EAN)	4032248379163	
Qty.	50 pc(s).	
Type	STB 21.6/45 RT	Version
Order No.	<a href="#">1936300000</a>	Socket (terminal), Plug-in depth: 11.1 mm, Depth: 45 mm
GTIN (EAN)	4032248606030	
Qty.	50 pc(s).	
Type	STB 36.8/IH/BL WTL6/1	Version
Order No.	<a href="#">1847790000</a>	Socket (terminal), Plug-in depth: 11.1 mm, Depth: 39.8 mm
GTIN (EAN)	4032248379149	
Qty.	50 pc(s).	
Type	STB 21.6/IH/GE WTL6/3	Version
Order No.	<a href="#">1071010000</a>	Socket (terminal), Plug-in depth: 11.1 mm, Depth: 26.6 mm
GTIN (EAN)	4008190259211	
Qty.	50 pc(s).	
Type	STB 21.6/45 GE	Version
Order No.	<a href="#">1936240000</a>	Socket (terminal), Plug-in depth: 11.1 mm, Depth: 45 mm
GTIN (EAN)	4032248605972	
Qty.	50 pc(s).	
Type	STB 21.6/IH/DB WTL6/3	Version
Order No.	<a href="#">1071000000</a>	Socket (terminal), Plug-in depth: 11.1 mm, Depth: 26.6 mm
GTIN (EAN)	4008190259204	
Qty.	50 pc(s).	
Type	STB 36.8/IH/DB WTL6/1	Version
Order No.	<a href="#">1847740000</a>	Socket (terminal), Plug-in depth: 11.1 mm, Depth: 39.8 mm
GTIN (EAN)	4032248379187	
Qty.	50 pc(s).	
Type	STB 21.6/45 GN	Version
Order No.	<a href="#">1936250000</a>	Socket (terminal), Plug-in depth: 11.1 mm, Depth: 45 mm
GTIN (EAN)	4032248605989	
Qty.	50 pc(s).	

Creation date May 2, 2024 9:10:43 AM CEST

Catalogue status 20.04.2024 / We reserve the right to make technical changes.



## WTL 6/1/TNSC/EN

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

Type	STB 21.6/45 VI	Version
Order No.	<a href="#">1936260000</a>	Socket (terminal), Plug-in depth: 11.1 mm, Depth: 45 mm
GTIN (EAN)	4032248605996	
Qty.	50 pc(s).	
Type	STB 36.8/IH/VI WTL6/1	Version
Order No.	<a href="#">1847780000</a>	Socket (terminal), Plug-in depth: 11.1 mm, Depth: 39.8 mm
GTIN (EAN)	4032248379156	
Qty.	50 pc(s).	
Type	STB 21.6/IH/BL WTL6/3	Version
Order No.	<a href="#">1071080000</a>	Socket (terminal), Plug-in depth: 11.1 mm, Depth: 26.6 mm
GTIN (EAN)	4008190043957	
Qty.	50 pc(s).	
Type	STB 36.8/IH/RT WTL6/1	Version
Order No.	<a href="#">1312540000</a>	Socket (terminal), Plug-in depth: 11.1 mm, Depth: 39.8 mm
GTIN (EAN)	4050118180992	
Qty.	50 pc(s).	
Type	STB 21.6/IH/SW WTL6/3	Version
Order No.	<a href="#">1071040000</a>	Socket (terminal), Plug-in depth: 11.1 mm, Depth: 26.6 mm
GTIN (EAN)	4008190859985	
Qty.	50 pc(s).	
Type	STB 21.6/45 SW	Version
Order No.	<a href="#">1936270000</a>	Socket (terminal), Plug-in depth: 11.1 mm, Depth: 45 mm
GTIN (EAN)	4032248606009	
Qty.	50 pc(s).	
Type	STB 36.8/IH/GE WTL6/1	Version
Order No.	<a href="#">1847760000</a>	Socket (terminal), Plug-in depth: 11.1 mm, Depth: 39.8 mm
GTIN (EAN)	4032248379170	
Qty.	50 pc(s).	
Type	STB 21.6/45 BL	Version
Order No.	<a href="#">1936290000</a>	Socket (terminal), Plug-in depth: 11.1 mm, Depth: 45 mm
GTIN (EAN)	4032248606023	
Qty.	50 pc(s).	

## End plate



## Current and voltage transformer wiring

Our test disconnect terminal blocks featuring spring and screw connection technology allow you to create all the important converter circuits for measuring current, voltage and power in a safe and sophisticated way.

## General ordering data

Type	WTW WTL6/1 DB	Version
Order No.	<a href="#">1068400000</a>	Test adapter (terminal)
GTIN (EAN)	4008190091996	
Qty.	20 pc(s).	

Creation date May 2, 2024 9:10:43 AM CEST

Catalogue status 20.04.2024 / We reserve the right to make technical changes.

## WTL 6/1/TNSC/EN

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

Type	WAP WTL6/1 EN	Version
Order No.	<a href="#">1957710000</a>	End plate (terminals), 65 mm x 1.5 mm, dark beige
GTIN (EAN)	4032248654024	
Qty.	20 pc(s).	

## Shorting elements



The short current bridges are inserted into two instrument transformer wiring terminal blocks. By using the short-circuit bridge, the desired short-circuit could be realized within the application for maintenance work.

## General ordering data

Type	WKS 1/4	Version
Order No.	<a href="#">1604310000</a>	Cross-connector (terminal), when screwed in, Number of poles: 4,
GTIN (EAN)	4008190886851	Pitch in mm (P): 14.10, Insulated: Yes, 41 A, orange
Qty.	50 pc(s).	
Type	WKB 1/4	Version
Order No.	<a href="#">1604320000</a>	Cross-connector (terminal), when screwed in, Number of poles: 4,
GTIN (EAN)	4008190023713	Pitch in mm (P): 8.00, Insulated: Yes, 41 A, orange
Qty.	50 pc(s).	
Type	WKS 1/3	Version
Order No.	<a href="#">1604290000</a>	Cross-connector (terminal), when screwed in, Number of poles: 3,
GTIN (EAN)	4008190164027	Pitch in mm (P): 14.10, Insulated: Yes, 41 A, orange
Qty.	50 pc(s).	
Type	QS 2/8/4	Version
Order No.	<a href="#">0270960000</a>	Cross-connector (terminal), Plugged, Number of poles: 2, Pitch in mm
GTIN (EAN)	4008190077006	(P): 8.00, Insulated: Yes, 44 A, beige
Qty.	20 pc(s).	
Type	WKS 2/2	Version
Order No.	<a href="#">1936140000</a>	Accessories, Cross-connection slider, x 14.1
GTIN (EAN)	4032248605866	
Qty.	50 pc(s).	
Type	WKB 1/10	Version
Order No.	<a href="#">1604330000</a>	Cross-connector (terminal), Plugged, Number of poles: 10, Pitch in mm
GTIN (EAN)	4008190129576	(P): 8.00, Insulated: Yes, 41 A, orange
Qty.	20 pc(s).	
Type	WKS 2/4	Version
Order No.	<a href="#">1936160000</a>	Accessories, Cross-connection slider, x 29.9
GTIN (EAN)	4032248605880	
Qty.	50 pc(s).	
Type	WKB 1/2	Version
Order No.	<a href="#">1604280000</a>	Cross-connector (terminal), when screwed in, Number of poles: 2,
GTIN (EAN)	4008190165338	Pitch in mm (P): 8.00, Insulated: Yes, 41 A, orange
Qty.	50 pc(s).	

## WTL 6/1/TNSC/EN

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

Type	WKB 1/3	Version
Order No.	<a href="#">1604300000</a>	Cross-connector (terminal), when screwed in, Number of poles: 3,
GTIN (EAN)	4008190010225	Pitch in mm (P): 8.00, Insulated: Yes, 41 A, orange
Qty.	50 pc(s).	
Type	WKS 2/3	Version
Order No.	<a href="#">1936150000</a>	Accessories, Cross-connection slider, x 22
GTIN (EAN)	4032248605873	
Qty.	50 pc(s).	
Type	WKS 1/2	Version
Order No.	<a href="#">1604270000</a>	Cross-connector (terminal), when screwed in, Number of poles: 2,
GTIN (EAN)	4008190863432	Pitch in mm (P): 14.10, Insulated: Yes, 41 A, orange
Qty.	50 pc(s).	

## Blank



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data


Type	DEK 5/8 MC NE WS	Version
Order No.	<a href="#">1856740000</a>	Dekafix, Terminal marker, 5 x 8 mm, Pitch in mm (P): 8.00
GTIN (EAN)	4032248400850	Weidmueller, white
Qty.	800 pc(s).	

**WTL 6/1/TNSC/EN****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Blank**

WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text. WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with PrintJet CONNECT oder/or Plotter is possible.

- Can be fitted in strips or individually
- Markers in proven MultiCard format

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**

Type	WS 12/8 PLUS MC NE WS	Version
Order No.	<a href="#">1906000000</a>	WS, Terminal marker, 12 x 8 mm, Pitch in mm (P): 8.00 Weidmueller,
GTIN (EAN)	4032248528158	white
Qty.	420 pc(s).	

**Connection sleeves****General ordering data**

Type	VH 16.1/5/3.4	Version
Order No.	<a href="#">0309700000</a>	Connecting sleeve (terminal), Height: 5 mm, Width: 5 mm, Depth:
GTIN (EAN)	4008190037024	16.1 mm, Cu Zn
Qty.	50 pc(s).	

## WTL 6/1/TNSC/EN

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Marker holder



The marker holder offer the possibility of additional mounting of standard markers with a pitch of 5 or 5.1 mm. The angled holders can be optionally snapped together and could be mounted in all standard marking channels of the Klippon® Connect modular terminal blocks. Fitting marker types could be found under the respective accessories of the designation marking holder.

## General ordering data

Type	BZT 1 ZA WS 10/5	Version
Order No.	<a href="#">1805520000</a>	Accessories, Marker holder
GTIN (EAN)	4032248270248	
Qty.	100 pc(s).	
Type	BZT 1 WS 10/5	Version
Order No.	<a href="#">1805490000</a>	Accessories, Marker holder
GTIN (EAN)	4032248270231	
Qty.	100 pc(s).	

6 mm<sup>2</sup>

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

## General ordering data

Type	WQV 6/2	Version
Order No.	<a href="#">1052360000</a>	Cross-connector (terminal), when screwed in, Number of poles: 2,
GTIN (EAN)	4008190075866	Pitch in mm (P): 8.00, Insulated: Yes, 57 A, yellow
Qty.	50 pc(s).	
Type	WQV 6/7	Version
Order No.	<a href="#">1062680000</a>	Cross-connector (terminal), when screwed in, Number of poles: 7,
GTIN (EAN)	4008190261788	Pitch in mm (P): 8.00, Insulated: Yes, 57 A, yellow
Qty.	50 pc(s).	
Type	WQV 6/6	Version
Order No.	<a href="#">1062670000</a>	Cross-connector (terminal), when screwed in, Number of poles: 6,
GTIN (EAN)	4008190261771	Pitch in mm (P): 8.00, Insulated: Yes, 57 A, yellow
Qty.	50 pc(s).	
Type	WQV 6/3	Version
Order No.	<a href="#">1054760000</a>	Cross-connector (terminal), when screwed in, Number of poles: 3,
GTIN (EAN)	4008190174163	Pitch in mm (P): 8.00, Insulated: Yes, 57 A, yellow
Qty.	50 pc(s).	

## WTL 6/1/TNSC/EN

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

Type	WQV 6/4	Version
Order No.	<a href="#">1054860000</a>	Cross-connector (terminal), when screwed in, Number of poles: 4,
GTIN (EAN)	4008190180799	Pitch in mm (P): 8.00, Insulated: Yes, 57 A, yellow
Qty.	50 pc(s).	
Type	WQV 6/10	Version
Order No.	<a href="#">1052260000</a>	Cross-connector (terminal), when screwed in, Number of poles: 10,
GTIN (EAN)	4008190153977	Pitch in mm (P): 8.00, Insulated: Yes, 57 A, yellow
Qty.	20 pc(s).	
Type	WQV 6/5	Version
Order No.	<a href="#">1062660000</a>	Cross-connector (terminal), when screwed in, Number of poles: 5,
GTIN (EAN)	4008190176914	Pitch in mm (P): 8.00, Insulated: Yes, 57 A, yellow
Qty.	50 pc(s).	

## SAK-Series



A partition plate is used for the optical separation of circuits or used for electrical isolation from neighbouring cross-connectors. In contrast to the end plate, the contour can be larger than the adjacent terminal blocks. However, it should not be smaller, as otherwise the required clearance and creepage distances within the application can no longer be maintained.

## General ordering data

Type	TSCH 2	Version
Order No.	<a href="#">0353660000</a>	Small partition (terminal), PA 66, beige, Continuous operating temp.,
GTIN (EAN)	4008190128432	max.: 100 °C
Qty.	100 pc(s).	

## W-Series



Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

## General ordering data

Type	WEW 35/2	Version
Order No.	<a href="#">1061200000</a>	End bracket, Wemid, dark beige, Rail: TS 35, when screwed in
GTIN (EAN)	4008190030230	
Qty.	50 pc(s).	

**WTL 6/1/TNSC/EN****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Switch lock**

The switch lock can be easily inserted into the terminal from above. The switch lock prevents unauthorised opening or closing of circuits as it blocks the disconnect lever in its respective position.

**General ordering data**

Type	SSP 3 SAKT1	Version
Order No.	<a href="#">0531760000</a>	Lockout device (terminal), orange
GTIN (EAN)	4008190130787	
Qty.	100 pc(s).	