

IE-MCT-1RS232/485-1ST**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image****Serial/fibre-optic converter**

Media converter for implementing serial, copper-based interfaces on fibre-optic cables and vice versa. Facilitates communication between terminal devices with type RS232/422/485 serial interface over a distance of up to 5 km.

- Ring and point-to-point transmission modes
- Extension of the RS232/422/485 transmission to up to 5 km
- Supports baud rates of 50 bps to 921.6 Kbps
- Expanded temperature range of -40 to 75°C
- Compact design

General ordering data

Version	Serial/fibre-optic converter, 1 x terminal block for RS232/422/485, 1 x ST multimode, IP30, -40 °C...75
Order No.	1362950000
Type	IE-MCT-1RS232/485-1ST
GTIN (EAN)	4050118165203
Qty.	1 pc(s).
Delivery status	This article will no longer be available in the future.
Available until	2022-06-01

IE-MCT-1RS232/485-1ST

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	22 mm	Depth (inches)	0.866 inch
Height	100 mm	Height (inches)	3.937 inch
Width	90.2 mm	Width (inches)	3.551 inch
Net weight	130 g		

Temperatures

Storage temperature	-40 °C...75 °C	Operating temperature	-40 °C...75
Humidity	5 to 95 % (non-condensing)		

Serial interface

Baud rate	50 bit/s to 921.6 kbit/s	Connection type	1 removable 7-pole terminal block
Interface standards	RS-232/422/485	RS485 data direction control	ADDC® (automatic data direction control)
Serial cable protection	15 KV ESD protection for all signals		

fibre-optic interface

Receive sensitivity	-20 dBm	Transmission mode: "Point-to-point"	Half-duplex, Full-duplex
Transmission mode: "Ring"	Half-duplex	Transmit power	> - 5 dBm
Type of connection		Typical distances	5 km (50/125, 62.5/125, 100/140 µm multimode cable)
	ST connection, Multimode		
Wave length	850 nm		

EMC conformity and approvals

EMC standards	FCC Part 15 Class B, EN 61000-4-2 (ESD), Stage 3, EN 61000-4-3 (RS), Stage 2, EN 61000-4-4 (EFT), Stage 2, EN 61000-4-5 (Surge), Stage 3, EN 61000-4-6 (CS), EN 61000-4-8, Stage 1, cULus	Safety standard	UL 60950-1
---------------	---	-----------------	------------

Environmental conditions

Humidity	5 to 95 % (non-condensing)	Operating temperature, max.	75
Operating temperature, min.	-40 °C	Storage temperature, max.	75 °C
Storage temperature, min.	-40 °C		

Guarantee

Time interval	5 years
---------------	---------

MTBF

MTBF	According to Standard	Telcordia (Bellcore), GB
	Operating time (hours), min.	780,480 h

IE-MCT-1RS232/485-1ST

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Power supply

Connection type	1 removable 3-pole terminal block	
Current consumption	Voltage	12 V
	Current	140 mA
	Voltage	24 V
	Current	67.7 mA
	Voltage	48 V
	Current	28.7 mA
Overload current protection	1.1 A	
Reverse polarity protection	Available	
Supply line protection	2 KV Burst (EFT), EN61000-4-4, 2 KV Surge, EN61000-4-5	
Voltage supply	24 V DC, 1 single input	
Voltage supply range	Voltage type	DC
	Voltage, min.	12 V
	Voltage, max.	48 V

Serial signals

RS232	Tx, Rx, GND	RS422	TxD+, TxD-, RxD+, RxD-, GND
RS485 2-wire	Data+, Data-, GND	RS485 4-wire	TxD+, TxD-, RxD+, RxD-, GND

Technical data

Housing main material	Aluminum	Protection degree	IP30
Type of mounting	Mounting plate, Wall mounting, when screwed in, TS 35, (with optional mounting kit IE-DINRAILMOUNT-KIT 1504430000)		

Classifications

ETIM 6.0	EC000310	ETIM 7.0	EC000310
ETIM 8.0	EC000310	ETIM 9.0	EC000310
ECLASS 9.0	19-17-01-14	ECLASS 9.1	19-17-01-14
ECLASS 10.0	19-17-04-11	ECLASS 11.0	19-17-04-11
ECLASS 12.0	19-17-04-11	ECLASS 13.0	19-17-04-11

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	9229992a-00b9-4096-8962-200a7f33e289

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E230683

Creation date May 6, 2024 10:34:44 PM CEST

Catalogue status 04.05.2024 / We reserve the right to make technical changes.

IE-MCT-1RS232/485-1ST

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

Approval/Certificate/Document of Con-
formity

[EU Declaration of Conformity](#)

Engineering Data

[CAD data – STEP](#)

User Documentation

[Hardware Installation Guide](#)

Catalogues

[Catalogues in PDF-format](#)

Brochures