

**IE-CC-NM-RPSMAM-2M****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image****Antennas and antenna accessories (coax cables and mounts)**

- State-of-the-art antennas
- Industry proven
- Robust design (up to IP67 protection)
- For outdoor and indoor use
- Latest technology support
- Up to Wi-Fi 6 and Wi-Fi 6E (2.4 GHz, 5 GHz, 6 GHz)
- Up to 5G (NR) support (700 MHz - 3.8 GHz)
- Also support for other technologies (e.g. Bluetooth, GNSS, etc.)
- Appropriate coax cables at different lengths
- Suitable pole and wall mounts

**General ordering data**

Version	Antenna cable, Connection 1.: N male, Connection 2.: RP-SMA male, Length: 2 m
Order No.	<a href="#">1367110000</a>
Type	IE-CC-NM-RPSMAM-2M
GTIN (EAN)	4050118186376
Qty.	1 pc(s).

**IE-CC-NM-RPSMAM-2M****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Length	2 m	Length (inches)	78.74 inch
Net weight	152.68 g		

**Temperatures**

Operating temperature	-40 °C...85
-----------------------	-------------

**Electrical properties of cable**

Attenuation at 2.4 GHz	approx. 0.55 dB/m	Attenuation at 5 GHz	approx. 0.87 dB/m
Characteristic impedance	50 Ohm +- 2	Max. operating frequency	6 GHz
Signal propagation time	4.08 ns/m		

**Mechanical and material properties of cable**

Cable length	2	Halogen	No, halogen-free, according to IEC 60754
Material sheath	LSFH (modified polyethylene)	Min. bending radius, once only	28 mm
Min. bending radius, repetitive	58 mm (for max. 50 bending cycles)	Sheath diameter	5.7 mm
Sheathing colour	black (similar to RAL 9005)	UV-resistant	ISO 4892-2A

**Technical data**

Type of connection	Connection 1:, N male, Connection 2:, RP-SMA male
--------------------	--

**Environmental conditions**

Operating temperature, max.	85	Operating temperature, min.	-40 °C
-----------------------------	----	-----------------------------	--------

**Classifications**

ETIM 6.0	EC001682	ETIM 7.0	EC001682
ETIM 8.0	EC001682	ETIM 9.0	EC001682
ECLASS 9.0	27-06-03-10	ECLASS 9.1	27-06-03-10
ECLASS 10.0	27-06-03-10	ECLASS 11.0	27-06-03-10
ECLASS 12.0	27-06-03-10	ECLASS 13.0	27-06-03-10

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
------------	----------------

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	