

**VPU III R 230V/6KV AC****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Type III surge protection**

- Compact Type III arrester for AC/DC protection acc. to IEC 61643-11:2012
- Suitable for protecting terminals
- Installed in the vicinity of the equipment to be protected
- Can be used as single-port arrester when nominal current is greater than 16 A

**General ordering data**

Version	Surge voltage arrester, Low voltage, with remote contact, Single-phase
Order No.	<a href="#">1351650000</a>
Type	VPU III R 230V/6KV AC
GTIN (EAN)	4050118158496
Qty.	1 pc(s).

## VPU III R 230V/6KV AC

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	71.5 mm	Depth (inches)	2.815 inch
Height	102 mm	Height (inches)	4.016 inch
Width	18 mm	Width (inches)	0.709 inch
Net weight	77 g		

## Temperatures

Storage temperature	-40 °C...70 °C	Operating temperature	-40 °C...70 °C
Humidity	5 - 95% rel. humidity		

## Connection data, remote alert

Connection type	Screw connection	Cross-section for connected wire, solid core, max.	1.5 mm <sup>2</sup>
Cross-section for connected wire, solid core, min.	0.2 mm <sup>2</sup>	Max. torque	0.5 Nm
Stripping length	5 mm		

## General data

Colour	orange	Design	Installation housing; 1TE, Insta IP 20
Optical function display	Green LED = OK, Red LED = arrester is defective, replace	Protection degree	IP20
Rail	TS 35	Segment	Power distribution
UL 94 flammability rating	V-0	Version	with remote contact

## Insulation coordination acc. to EN 50178

Pollution severity	2	Surge voltage category	II
--------------------	---	------------------------	----

## Rated data IEC / EN

Combined pulse $U_{OC}$	6 kV	Discharge current, max. (8/20 $\mu$ s)	3 kA
Energy coordination ( $\leq 10$ m)	Type II, Type III	Fuse	16 A
Leakage current at $U_n$	30 $\mu$ A	Low voltage network	Single-phase
Mains frequency at 250 Vmax	50...60Hz	Max. continuous voltage, $U_c$ (AC)	300 V
Number of poles	1	PE conductor current $I_{PE}$	30 $\mu$ A
Protection level $U_p$ at $I_N$ (L/N-PE)	$\leq 1.8$ kV	Rated current $I_N$	16 A
Rated voltage (AC)	230 V	Requirements category acc. to IEC 61643-11	Type III
Requirements class, acc. to EN 61643-11	T3	Response time	$\leq 100$ ns
Short-circuit current rating $I_{SCCR}$	1.5 kA	Signalling contact	250 V 10 A 1 NC
Standards	IEC 61643-11, EN 61643-11	Temporary surge voltage (over-voltage) - TOV	438 V
Voltage type	AC		

## VPU III R 230V/6KV AC

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Connection data

Stripping length	7 mm	Type of connection	Screw connection
Stripping length, rated connection	7 mm	Tightening torque, min.	0.4 Nm
Tightening torque, max.	0.5 Nm	Clamping range, rated connection	2.5 mm <sup>2</sup>
Clamping range, min.	0.5 mm <sup>2</sup>	Clamping range, max.	2.5 mm <sup>2</sup>
Wire cross-section, solid, min.	0.13 mm <sup>2</sup>	Wire cross-section, solid, max.	2.5 mm <sup>2</sup>
Wire connection cross section, finely stranded, min.	0.5 mm <sup>2</sup>	Wire connection cross section, finely stranded, max.	2.5 mm <sup>2</sup>
Conductor cross-section, flexible, AEH (DIN 46228-1), min.	0.5 mm <sup>2</sup>	Conductor cross-section, flexible, AEH (DIN 46228-1), max.	2.5 mm <sup>2</sup>
Connection cross-section, stranded, min.	0.5 mm <sup>2</sup>	Connection cross-section, stranded, max.	2.5 mm <sup>2</sup>

## Guarantee

Time interval	5 years
---------------	---------

## Classifications

ETIM 6.0	EC000941	ETIM 7.0	EC000941
ETIM 8.0	EC000941	ETIM 9.0	EC000941
ECLASS 9.0	27-13-08-05	ECLASS 9.1	27-13-08-05
ECLASS 10.0	27-13-08-05	ECLASS 11.0	27-13-08-05
ECLASS 12.0	27-17-90-90	ECLASS 13.0	27-17-90-90

## VPU III R 230V/6KV AC

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Tender specification sheets

## Long specification

Surge protection according to the requirements of Class III in accordance with IEC 61643-11, EN61643-11:2013. The arrester serves as surge protection and is used in applications in accordance with IEC 61643-12. The arrester is installed in the vicinity of the equipment that needs protection in a standard installation/distributor housing. The VPU III R 230 V is earthed between the phase and the neutral conductor. With thermal separation device on the varistor. If there is no longer any protection, the colour of the LEDs changes from green to red. The functional state is also displayed by a voltage-free signalling contact (NC contact). Rated voltage: 230 VAC In/max (8/20 µs): 3 kA protection level < 1.8 kV load current II: 16 A telecommunication output: contact NC: 250 V/0.5 A 48 VDC/0.1 A Type: Weidmüller VPU III R 230 V Order No. 1351650000 or equivalent

## Short specification

Class III arrester with Uoc: 6 kV suitable for 230 V AC mains systems. Protection level < 1.8 kV. With remote alert Type: Weidmüller VPU III R 230 V/6 kV Order no. 1351650000 or equivalent

## Approvals

## Approvals



ROHS

Conform

## Downloads

Approval/Certificate/Document of Conformity

[EU\\_Konformitätserklärung / EU\\_Declaration\\_of\\_Conformity](#)

Engineering Data

[CAD data – STEP](#)

Tender specification

[Ausschreibungstext DE](#)  
[Tenderspecification EN](#)

User Documentation

[Beipackzettel / Instruction sheet](#)

Catalogues

[Catalogues in PDF-format](#)

Brochures


## VPU III R 230V/6KV AC

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

# Drawings

## Electric symbol



Schematic circuit diagram