

TBY-RS-UNIV-SP-2KS-Z**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

Analogue interfaces are equipped with 40-pole connectors (KS). Versions are available with disconnecting plugs and test points which are extremely useful for voltage and current measurements. There are also versions with useful additional pins for customers who wish to incorporate other elements (resistor ...) for converting voltage/current or monitoring the current loop.

General ordering data

Version	Interface, RS, 2 x KS (40P), LM2NZF 5.08mm
Order No.	1371370000
Type	TBY-RS-UNIV-SP-2KS-Z
GTIN (EAN)	4050118207149
Qty.	1 pc(s).

TBY-RS-UNIV-SP-2KS-Z**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	65 mm	Depth (inches)	2.559 inch
Height	109 mm	Height (inches)	4.291 inch
Width	112 mm	Width (inches)	4.409 inch
Net weight	202 g		

Temperatures

Storage temperature	-40...85 °C	Operating temperature	-25...70 °C
---------------------	-------------	-----------------------	-------------

General data

LED status display per channel	No	Disconnection per channel	No
Type of test point	Soldering tags	Switch	No
Fuse per channel	No	LED status of the supply voltage	No
Power supply fuse	No		

Connection data

Connection (field side)	LM2NZF 5.08mm	Connection on control side	2 x KS (40P)
Number of poles (control side)	40-pole plug		

Ratings data

Operating voltage	50 V AC / 70 V DC	Max. current for common pole	1 A
Max. current per channel	1 A		

Insulation coordination (EN50178)

Rated insulation voltage	< 50 V AC	Surge voltage category	III
Pollution severity level	2	Pulse voltage test (1,2/50µs)	0.8 kV
Insulation test voltage AC	0.35 kV		

Connection field

Clamping range, max.	2.5 mm ²	Clamping range, min.	0.13 mm ²
Flexible with sleeve, max.	1.5 mm ²	Flexible with sleeve, min.	0.25 mm ²
Flexible, max. H05(07) V-K	1.5 mm ²	Flexible, min. H05(07) V-K	0.2 mm ²
Max. wire cross-section, AWG	AWG 14	Min. wire cross-section, AWG	AWG 24
Sleeve with plastic collar, max.	1.5 mm ²	Solid, max. H05(07) V-U	2.5 mm ²
Solid, min. H05(07) V-U	0.2 mm ²	Stripping length	7.5 mm
Type of connection	Tension-clamp connection		

Supply connection

Type of connection	Tension-clamp connection	Clamping range, min.	0.13 mm ²
Clamping range, max.	2.5 mm ²	Solid, min. H05(07) V-U	0.2 mm ²
Solid, max. H05(07) V-U	2.5 mm ²	Flexible, min. H05(07) V-K	0.2 mm ²
Flexible, max. H05(07) V-K	1.5 mm ²	Flexible with sleeve, max.	1.5 mm ²
Flexible with sleeve, min.	0.25 mm ²	Ferrule with plastic collar, max.	1.5 mm ²
Wire cross-section, min. AWG	AWG 14	Wire cross-section, max. AWG	AWG 24
Stripping length	7.5 mm		

TBY-RS-UNIV-SP-2KS-Z

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Classifications

ETIM 6.0	EC002780	ETIM 7.0	EC002780
ETIM 8.0	EC002780	ETIM 9.0	EC002780
ECLASS 9.0	27-14-11-52	ECLASS 9.1	27-14-11-52
ECLASS 10.0	27-14-11-52	ECLASS 11.0	27-14-11-52
ECLASS 12.0	27-14-11-52	ECLASS 13.0	27-14-11-52

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	9dd73319-d286-43a8-a0b7-6458fd2c03f9

Approvals

Approvals



Downloads

Catalogues	Catalogues in PDF-format
Brochures	

TBY-RS-UNIV-SP-2KS-Z

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

