

**THM WO VIN 17.8/34 WS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

THM WriteOn cable markers on reels are used for labelling conductors and cables with an outside diameter of up to 36 mm. The transparent adhesive strip fixes and protects the printing on the marker surface.

- Protection of the marking against dirt and abrasion by wrapping it with the transparent adhesive strip
- Simple and quick printing with the high-quality thermal transfer printers

**General ordering data**

|                    |   |
|--------------------|---|
| Version            | THM, Conductor and cable markers, 4.4 - 6.7 mm, 17.8 x 34 mm, white |
| Order No.          | <a href="#">1382930000</a>  |
| Type               | THM WO VIN 17.8/34 WS   |
| GTIN (EAN)         | 4050118185065   |
| Qty.               | 1 pc(s).  |
| compatible printer | <a href="#">2599430000</a> <a href="#">2599440000</a>               |

## THM WO VIN 17.8/34 WS

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |          |                 |            |
|------------|----------|-----------------|------------|
| Depth      | 0.065 mm | Depth (inches)  | 0.003 inch |
| Height     | 17.8 mm  | Height (inches) | 0.701 inch |
| Width      | 34 mm    | Width (inches)  | 1.339 inch |
| Net weight | 470 g    |                 |            |

## Temperatures

|                             |             |
|-----------------------------|-------------|
| Operating temperature range | -40...80 °C |
|-----------------------------|-------------|

## General data

|                                      |  |            |
|--------------------------------------|--|------------|
| Adhesive                             | Polyacrylate adhesive                      |            |
| Approval acc. to UL 969              | No   |            |
| Colour                               | white                                      |            |
| Halogen                              | Yes  |            |
| Material                             | Vinyl film                                 |            |
| Number of markers per combination    | 1 Label reel = Conductor and cable markers |            |
| Number of markers per packaging unit | Form of supply                             | Label reel |
| Number per roll                      | 3,000                                      |            |
| Operating temperature range          | -40...80 °C                                |            |
| Operating temperature range, max.    | 80 °C                                      |            |
| Operating temperature range, min.    | -40 °C                                     |            |
| Size of labelling field              | 13 x 17.8 mm                               |            |
| Type of printing                     | neutral                                    |            |
| UL 94 flammability rating            | V-0  |            |
| Version                              | Self-adhesive                              |            |
| Width                                | 34 mm                                      |            |

## Conductor and cable markers

|                               |                      |                                  |                           |
|-------------------------------|----------------------|----------------------------------|---------------------------|
| Conductor O.D.                | 4.4 - 6.7 mm         | Conductor O.D., max.             | 6.7 mm                    |
| Conductor O.D., min.          | 4.4 mm               | Conductor cross-section, max.    | 35 mm <sup>2</sup>        |
| Conductor cross-section, min. | 0.75 mm <sup>2</sup> | Cross-section for connected wire | 0.75 - 35 mm <sup>2</sup> |
| Halogen                       | Yes                  | Text field height                | 13 mm                     |
| Text field width              | 17.8 mm              |                                  |                           |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001530    | ETIM 7.0    | EC001530    |
| ETIM 8.0    | EC001530    | ETIM 9.0    | EC001530    |
| ECLASS 9.0  | 27-40-04-01 | ECLASS 9.1  | 27-40-04-01 |
| ECLASS 10.0 | 27-40-04-01 | ECLASS 11.0 | 27-28-11-02 |
| ECLASS 12.0 | 27-28-11-02 | ECLASS 13.0 | 27-28-11-02 |

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Downloads

|                  |  |
|------------------|--|
| Engineering Data | <a href="#">CAD data – STEP</a>          |
| Catalogues       | <a href="#">Catalogues in PDF-format</a> |

Drawings

