

THM WO VIN 12/18 WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

THM WriteOn cable markers on reels are used for labelling conductors and cables with an outside diameter of up to 36 mm. The transparent adhesive strip fixes and protects the printing on the marker surface.

- Protection of the marking against dirt and abrasion by wrapping it with the transparent adhesive strip
- Simple and quick printing with the high-quality thermal transfer printers

General ordering data

Version	THM, Conductor and cable markers, 2.9 - 2.9 mm, 12 x 18 mm, white
Order No.	1382940000
Type	THM WO VIN 12/18 WS
GTIN (EAN)	4050118185171
Qty.	1 pc(s).
compatible printer	2599430000 2599440000

THM WO VIN 12/18 WS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	0.065 mm	Depth (inches)	0.003 inch
Height	12 mm	Height (inches)	0.472 inch
Width	18 mm	Width (inches)	0.709 inch
Net weight	588 g		

Temperatures

Operating temperature range	-40...80 °C
-----------------------------	-------------

General data

Adhesive	Polyacrylate adhesive	
Approval acc. to UL 969	No	
Colour	white	
Halogen	Yes	
Material	Vinyl film	
Number of markers per combination	1 Label reel = Conductor and cable markers	
Number of markers per packaging unit	Form of supply	Label reel
Number per roll	10,000	
Operating temperature range	-40...80 °C	
Operating temperature range, max.	80 °C	
Operating temperature range, min.	-40 °C	
Size of labelling field	9 x 12 mm	
Type of printing	neutral	
UL 94 flammability rating	V-0	
Version	Self-adhesive	
Width	18 mm	

Conductor and cable markers

Conductor O.D.	2.9 - 2.9 mm	Conductor O.D., max.	2.9 mm
Conductor O.D., min.	2.9 mm	Conductor cross-section, max.	6 mm ²
Conductor cross-section, min.	0.75 mm ²	Cross-section for connected wire	0.75 - 6 mm ²
Halogen	Yes	Text field height	9 mm
Text field width	12 mm		

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ECLASS 9.0	27-40-04-01	ECLASS 9.1	27-40-04-01
ECLASS 10.0	27-40-04-01	ECLASS 11.0	27-28-11-02
ECLASS 12.0	27-28-11-02	ECLASS 13.0	27-28-11-02

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format

Drawings

