

SAISW-M-8/9 M12**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly.

Male plugs and female socket for customisable assembly for M8, M12, M16 and 7/8" connections which are highly robust and ideally suited to machine engineering, for instance. The M12 plug-in connectors offer a choice of 5 different connection systems.

The screw connection can be used in a wide range of applications. With this technology the conductor, optionally with wire-end ferrules, can be plugged into connection elements and secured with a screw. It is the classic, cheapest form of connection technology that also supports multi-conductor connections.

General ordering data

| | |
|------------|---|
| Version | Field attachable connector, M12, pin, 90° |
| Order No. | 1423040000 |
| Type | SAISW-M-8/9 M12 |
| GTIN (EAN) | 4050118227321 |
| Qty. | 1 pc(s). |

SAISW-M-8/9 M12

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | |
|------------|------|
| Net weight | 40 g |
|------------|------|

Technical data customisable plug-in connectors

| | | | |
|--------------------------------|----------------------|--------------------------------|---------------------|
| Cable diameter, max. | 8 mm | Cable diameter, min. | 6 mm |
| Coding | A-coded | Connection cross-section, max. | 0.5 mm ² |
| Connection cross-section, min. | 0.14 mm ² | Contact surface | Gold-plated |
| Housing main material | Zinc diecast | Number of poles | 8 |
| Plugging cycles | ≥ 100 | Pollution severity | 3 |
| Protection degree | IP67 | Rated current | 2 A |
| Rated voltage | 60 V | Shield connection | Yes |
| Temperature range of housing | -40 ... +85 °C | Threaded ring material | Diecast zinc |
| Type of connection | Screw connection | | |

General Info

| | | | |
|-------------------|-------|-----------------------|--------------|
| Number of poles | 8 | Connection 1 | M12 |
| Connection 2 | Screw | Housing main material | Zinc diecast |
| Connection thread | M12 | Contact surface | Gold-plated |
| Protection degree | IP67 | Plugging cycles | ≥ 100 |

Standards

| | |
|--------------------|-----------------|
| Connector standard | IEC 61076-2-101 |
|--------------------|-----------------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC002635 | ETIM 7.0 | EC002635 |
| ETIM 8.0 | EC002635 | ETIM 9.0 | EC002635 |
| ECLASS 9.0 | 27-44-01-02 | ECLASS 9.1 | 27-44-01-03 |
| ECLASS 10.0 | 27-44-01-02 | ECLASS 11.0 | 27-44-01-02 |
| ECLASS 12.0 | 27-44-01-16 | ECLASS 13.0 | 27-44-01-02 |

Environmental Product Compliance

| | |
|------------|---|
| REACH SVHC | Lead 7439-92-1 Imidazolidine-2-thione 96-45-7 |
| SCIP | bcee35cf-c0f5-43d2-8daf-65ab0d08641a |

Approvals

Approvals



| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|--------------------|--|
| Engineering Data | CAD data – STEP |
| User Documentation | Manual |
| Catalogues | Catalogues in PDF-format |
| Brochures | FL FIELDWIRING EN |

Creation date May 12, 2024 6:47:55 AM CEST

Catalogue status 04.05.2024 / We reserve the right to make technical changes.

SAISW-M-8/9 M12

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings

Pole scheme

