

**ACT20M-RTI-CO-EOLP-S****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image****ACT20M: The slim solution**

- Safe and space-saving (6 mm) isolation and conversion
- Quick installation of the power supply unit using the CH20M mounting rail bus
- Easy configuration via DIP switch or FDT/DTM software
- Extensive approvals such as ATEX, IECEx, GL, DNV
- High interference resistance

**General ordering data**

Version	Passive isolator, Without galvanic isolation, Input : Temperature, PT100, Output : 4-20 mA
Order No.	<a href="#">1435610000</a>
Type	ACT20M-RTI-CO-EOLP-S
GTIN (EAN)	4050118240528
Qty.	1 pc(s).

**ACT20M-RTI-CO-EOLP-S****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Depth	114.3 mm	Depth (inches)	4.5 inch
Height	112.5 mm	Height (inches)	4.429 inch
Width	6.1 mm	Width (inches)	0.24 inch
Net weight	80 g		

**Temperatures**

Storage temperature	-40 °C...85 °C	Operating temperature	-25 °C...70 °C
Humidity at operating temperature	0...95 % (no condensation)	Humidity	40 °C / 93 % rel. humidity, no condensation

**Probability of failure**

MTBF	227 a
------	-------

**Input**

Influence of the sensor cable resistance	<0.002 Ω/Ω	Line resistance in measuring circuit	50 Ω@ RTD (Pt100), 10 kΩ @ TC (J, K)
Number of inputs	1	Sensor	PT100 (2-/3-/4- wire)
Temperature input range	Configurable, PT100: -200...+850 °C, min. measurement range 10°C (RTD)		

**Output**

Load impedance current	≤ 600 Ω	Number of outputs	1
Output current	4...20 mA, loop-powered	Supply voltage (output)	16,8 V...31,2 V
Type	passive, connected control must be active	Wire break detection	Yes, Configurable, 3.5 mA / 23 mA / none
load impedance voltage	≥ 10 kΩ		

**General data**

Accuracy	absolute accuracy: <±0.1 % of the measurement range, Basic accuracy: <±0.2°C	
Cold-junction compensation error	±(2.0 °C + 0.4 °C x Δt) Δt = inside temperature – ambient temperature	
Configuration	DIP switch	
Delivery state	Input: 0 °C // Bandwidth: 100 Hz // Output: 0...20 mA // Output 2: 0...20 mA // Noise suppression: 50 Hz // Start temperature: -200 °C // End temperature: 0 °C	
Delivery state	Setting parameters	Input
	Configuration	0 °C
	Setting parameters	Bandwidth
	Configuration	100 Hz
	Setting parameters	Output
	Configuration	0...20 mA
	Setting parameters	Output 2
	Configuration	0...20 mA
	Setting parameters	Noise suppression
	Configuration	50 Hz
	Setting parameters	Start temperature
	Configuration	-200 °C
Setting parameters	End temperature	
Configuration	0 °C	
Nominal power consumption	0.5 VA	
Operating altitude	≤ 2000 m	

Creation date July 3, 2025 9:39:42 PM CEST

**ACT20M-RTI-CO-EOLP-S****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data**

Power consumption, max.	0.8 W
Power consumption, typ.	0.48 W
Protection degree	IP20
Rail	TS 35
Step response time	Configurable, ≤ 30 ms, <300 ms
Temperature coefficient	RTD (PT100) ≤0.01 % of the measurement range/°C or 0.02 °C/°C
Voltage supply	Output loop powered, 6...35 V

**Insulation coordination**

EMC standards	IEC 61326-1	Galvanic isolation	Without isolation
Pollution severity	2		

**Data for Ex applications (ATEX)**

Installation location	Device installed in safe area, zone 2	Marking	II 3 G Ex nA IIC T4 Gc
-----------------------	---------------------------------------	---------	------------------------

**Connection data**

Type of connection	Screw connection	Tightening torque, min.	0.4 Nm
Tightening torque, max.	0.6 Nm	Clamping range, rated connection	2.5 mm <sup>2</sup>
Clamping range, min.	0.5 mm <sup>2</sup>	Clamping range, max.	2.5 mm <sup>2</sup>
Wire connection cross section AWG, min.	AWG 30	Wire connection cross section AWG, max.	AWG 14

**EMC conformity and approvals**

EMC standards	IEC 61326-1	Standards	IEC 61010-1
---------------	-------------	-----------	-------------

**Classifications**

ETIM 6.0	EC002919	ETIM 7.0	EC002919
ETIM 8.0	EC002919	ETIM 9.0	EC002919
ETIM 10.0	EC002919	ECLASS 9.0	27-21-01-29
ECLASS 9.1	27-21-01-29	ECLASS 10.0	27-21-01-29
ECLASS 11.0	27-21-01-29	ECLASS 12.0	27-21-01-29
ECLASS 13.0	27-21-01-29	ECLASS 14.0	27-21-01-29
ECLASS 15.0	27-21-01-29		

# ACT20M-RTI-CO-EOLP-S

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Approvals

Approvals



Approvals MAMID	<a href="https://mdcop.weidmueller.com/mediadelivery/rendition/900_319228/-T1z1mm-S800/">https://mdcop.weidmueller.com/mediadelivery/rendition/900_319228/-T1z1mm-S800/</a> <a href="https://mdcop.weidmueller.com/mediadelivery/rendition/900_319234/-T1z1mm-S800/">https://mdcop.weidmueller.com/mediadelivery/rendition/900_319234/-T1z1mm-S800/</a> <a href="https://mdcop.weidmueller.com/mediadelivery/rendition/900_319237/-T1z1mm-S800/">https://mdcop.weidmueller.com/mediadelivery/rendition/900_319237/-T1z1mm-S800/</a> <a href="https://mdcop.weidmueller.com/mediadelivery/rendition/900_319240/-T1z1mm-S800/">https://mdcop.weidmueller.com/mediadelivery/rendition/900_319240/-T1z1mm-S800/</a> <a href="https://mdcop.weidmueller.com/mediadelivery/rendition/900_319243/-T1z1mm-S800/">https://mdcop.weidmueller.com/mediadelivery/rendition/900_319243/-T1z1mm-S800/</a> <a href="https://mdcop.weidmueller.com/mediadelivery/rendition/900_319260/-T1z1mm-S800/">https://mdcop.weidmueller.com/mediadelivery/rendition/900_319260/-T1z1mm-S800/</a>
ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E337701

### Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	7a, 7cl
REACH SVHC	Lead 7439-92-1
SCIP	2f6dd957-421a-46db-a0c2-cf1609156924

### Important note

Product information	<p>The ACT20M-RTCI-CO-OLP-S passive configurable temperature transducer isolates and converts analogue signals. An analogue RTD (Type Pt100) or TC (Type J, K) input signal is linearly converted into an analogue output signal and galvanically isolated. Power is supplied through the output measurement circuit (output- loop powered).</p> <p>The ACT20M-RTI-CO-EOLP-S passive configurable temperature transducer does not have any galvanic isolation and has no TC input.</p>
---------------------	--

### Downloads

Approval/Certificate/Document of Conformity	<a href="#">DNV-GL certificate</a> <a href="#">FM certificate</a> <a href="#">IECEX certificate</a> <a href="#">ATEX certificate</a> <a href="#">Certification UL for canada</a> <a href="#">Declaration of Conformity</a>
Engineering Data	<a href="#">CAD data – STEP</a>
Software	<a href="#">DIP switch configuration tool</a>
User Documentation	<a href="#">instruction sheet</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	


# ACT20M-RTI-CO-EOLP-S

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany


[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

### Connection diagram




### Dimensional drawing



### DIP switch setting

		Temperature range [°C]											
		PT100: -200...+500 °C				TC-0...TC-2: -200...+200 °C				TC-K...TC-L: -100...+1372 °C			
		Min	Max	S2	Min	Max	S2	Min	Max	S2	Min	Max	S2
RTD & TC sensor type	S1												
PT100 2 wire	1	1	1	1	1	1	1	1	1	1	1	1	1
PT100 3 wire	2	1	1	1	1	1	1	1	1	1	1	1	1
PT100 4 wire	3	1	1	1	1	1	1	1	1	1	1	1	1
TC (external 4-wire)	4	1	1	1	1	1	1	1	1	1	1	1	1
TC (external 4-wire)	5	1	1	1	1	1	1	1	1	1	1	1	1
TC (external 4-wire)	6	1	1	1	1	1	1	1	1	1	1	1	1
TC (external 4-wire)	7	1	1	1	1	1	1	1	1	1	1	1	1
TC (external 4-wire)	8	1	1	1	1	1	1	1	1	1	1	1	1
TC (external 4-wire)	9	1	1	1	1	1	1	1	1	1	1	1	1
TC (external 4-wire)	10	1	1	1	1	1	1	1	1	1	1	1	1
Output	S2												
4...20 mA	1	1	1	1	1	1	1	1	1	1	1	1	1
20...4 mA	2	1	1	1	1	1	1	1	1	1	1	1	1
Sensor error detection	S3												
enable	1	1	1	1	1	1	1	1	1	1	1	1	1
enable	2	1	1	1	1	1	1	1	1	1	1	1	1
enable	3	1	1	1	1	1	1	1	1	1	1	1	1
enable	4	1	1	1	1	1	1	1	1	1	1	1	1
enable	5	1	1	1	1	1	1	1	1	1	1	1	1
enable	6	1	1	1	1	1	1	1	1	1	1	1	1
enable	7	1	1	1	1	1	1	1	1	1	1	1	1
enable	8	1	1	1	1	1	1	1	1	1	1	1	1
enable	9	1	1	1	1	1	1	1	1	1	1	1	1
enable	10	1	1	1	1	1	1	1	1	1	1	1	1
Noise suppression	S4												
50 Hz	1	1	1	1	1	1	1	1	1	1	1	1	1
50 Hz	2	1	1	1	1	1	1	1	1	1	1	1	1
Response time	S5												
50 ms	1	1	1	1	1	1	1	1	1	1	1	1	1
500 ms	2	1	1	1	1	1	1	1	1	1	1	1	1

example for DIP switch setting  
(with ACT20M tool software)



example for DIP switch setting  
(with ACT20M tool software)

**ACT20M-RTI-CO-EOLP-S****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Blank**

MultiFit is the Weidmüller marker system used for other makes of terminals. Similar to the Weidmüller Dekafix, the markers of the MultiFit family are available ready-for-use with standard printing.

We recommend to carry out a test with sample markers on the terminals used when using MultiFit for the first time.

- One marker, suitable for different makes of terminals.
- Ready-to-use markers with standard printing
- Blank markers for printing with the PrintJet CONNECT or Plotter
- Delivery of individually printed markers according to customer CAE data or specifications
- One marking system for all applications

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**

Type	MF 5/7.5 MC NE WS	Version
Order No.	<a href="#">1877680000</a>	MultiFit, Terminal marker, 5 x 7.5 mm, Pitch in mm (P): 7.50 Adels
GTIN (EAN)	4032248468270	RKW, Phoenix, white
Qty.	320 pc(s).	