

**ACT20M-RTCI-CO-OLP-S****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image****ACT20M: The slim solution**

- Safe and space-saving (6 mm) isolation and conversion
- Quick installation of the power supply unit using the CH20M mounting rail bus
- Easy configuration via DIP switch or FDT/DTM software
- Extensive approvals such as ATEX, IECEx, GL, DNV
- High interference resistance

**General ordering data**

Version	Passive isolator, With galvanic isolation, Input : Temperature, PT100, thermocouple, Output : 4-20 mA
Order No.	<a href="#">1435590000</a>
Type	ACT20M-RTCI-CO-OLP-S
GTIN (EAN)	4050118240641
Qty.	1 pc(s).

**ACT20M-RTCI-CO-OLP-S****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Depth	114.3 mm	Depth (inches)	4.5 inch
Height	112.5 mm	Height (inches)	4.429 inch
Width	6.1 mm	Width (inches)	0.24 inch
Net weight	80 g		

**Temperatures**

Storage temperature	-40 °C...85 °C	Operating temperature	-25 °C...70 °C
Humidity at operating temperature	0...95 % (no condensation)	Humidity	40 °C / 93 % rel. humidity, no condensation

**Probability of failure**

MTBF	207 a
------	-------

**Input**

Influence of the sensor cable resistance	<0.002 Ω/Ω	Line resistance in measuring circuit	50 Ω@ RTD (Pt100), 10 kΩ @ TC (J, K)
Number of inputs	1	Sensor	PT100 (2-/3-/4- wire), Thermocouples: J, K
Temperature input range	Configurable, PT100: -200...+850 °C, min. measurement range 10°C (RTD), J: (-100...+1200 °C), K: (-180...+1372 °C), min. measurement range 50°C (TC)		

**Output**

Load impedance current	≤ 600 Ω	Number of outputs	1
Output current	configurable, 4...20 mA, 20...4 mA	Supply voltage (output)	16,8 V...31,2 V
Type	passive, connected control must be active	Wire break detection	Yes, Configurable, 3.5 mA / 23 mA / none

**General data**

Accuracy	absolute accuracy: <±0.05 % of the measurement range, RTD (PT100) Basic accuracy: <±0.1 °C of the measurement range, TC (J,K) Basic accuracy: <±0.5 °C of the measurement range		
Cold-junction compensation error	±(2.0 °C + 0.4 °C x Δt) Δt = inside temperature – ambient temperature		
Configuration	DIP switch		
Delivery state	Output: 4...20 mA (loop) // Sensor error detection: enabled // Output error level: downscale // Noise suppression: 50 Hz // Step response time: < 30 ms // Start temperature: -200 °C // End temperature: 0 °C		

**ACT20M-RTCI-CO-OLP-S****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data**

Delivery state	Setting parameters	Output
	Configuration	4...20 mA (loop)
	Setting parameters	Sensor error detection
	Configuration	enabled
	Setting parameters	Output error level
	Configuration	downscale
	Setting parameters	Noise suppression
	Configuration	50 Hz
	Setting parameters	Step response time
	Configuration	< 30 ms
	Setting parameters	Start temperature
	Configuration	-200 °C
	Setting parameters	End temperature
	Configuration	0 °C
Nominal power consumption	0.5 VA	
Power consumption, max.	0.8 W	
Power consumption, typ.	0.5 W	
Protection degree	IP20	
Rail	TS 35	
Step response time	Configurable, ≤ 30 ms, <300 ms	
Temperature coefficient	RTD (PT100) ±0.01 % of the measurement range/°C or 0.02 °C/°C, TC (J,K) 0.1 °C/°C	
Voltage supply	Output loop powered, 6...35 V	

**Insulation coordination**

EMC standards	IEC 61326-1	Galvanic isolation	2-way isolator
Insulation voltage	2.5 kV <sub>eff</sub> / 1 min.	Pollution severity	2
Rated voltage	300 V <sub>eff</sub>	Surge voltage category	II

**Data for Ex applications (ATEX)**

Installation location	Device installed in safe area, zone 2	Marking	II 3 G Ex nA IIC T4 Gc
-----------------------	---------------------------------------	---------	------------------------

**Connection data**

Type of connection	Screw connection	Tightening torque, min.	0.4 Nm
Tightening torque, max.	0.6 Nm	Clamping range, rated connection	2.5 mm <sup>2</sup>
Clamping range, min.	0.5 mm <sup>2</sup>	Clamping range, max.	2.5 mm <sup>2</sup>
Wire connection cross section AWG, min.	AWG 30	Wire connection cross section AWG, max.	AWG 14

**EMC conformity and approvals**

EMC standards	IEC 61326-1	Standards	IEC 61010-1
---------------	-------------	-----------	-------------

**Classifications**

ETIM 6.0	EC002919	ETIM 7.0	EC002919
ETIM 8.0	EC002919	ETIM 9.0	EC002919
ETIM 10.0	EC002919	ECLASS 9.0	27-21-01-29
ECLASS 9.1	27-21-01-29	ECLASS 10.0	27-21-01-29
ECLASS 11.0	27-21-01-29	ECLASS 12.0	27-21-01-29
ECLASS 13.0	27-21-01-29	ECLASS 14.0	27-21-01-29
ECLASS 15.0	27-21-01-29		

# ACT20M-RTCI-CO-OLP-S

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Approvals

Approvals



Approvals MAMID	<a href="https://mdcop.weidmueller.com/mediadelivery/rendition/900_319228/-T1z1mm-S800/">https://mdcop.weidmueller.com/mediadelivery/rendition/900_319228/-T1z1mm-S800/</a> <a href="https://mdcop.weidmueller.com/mediadelivery/rendition/900_319234/-T1z1mm-S800/">https://mdcop.weidmueller.com/mediadelivery/rendition/900_319234/-T1z1mm-S800/</a> <a href="https://mdcop.weidmueller.com/mediadelivery/rendition/900_319237/-T1z1mm-S800/">https://mdcop.weidmueller.com/mediadelivery/rendition/900_319237/-T1z1mm-S800/</a> <a href="https://mdcop.weidmueller.com/mediadelivery/rendition/900_319240/-T1z1mm-S800/">https://mdcop.weidmueller.com/mediadelivery/rendition/900_319240/-T1z1mm-S800/</a> <a href="https://mdcop.weidmueller.com/mediadelivery/rendition/900_319243/-T1z1mm-S800/">https://mdcop.weidmueller.com/mediadelivery/rendition/900_319243/-T1z1mm-S800/</a> <a href="https://mdcop.weidmueller.com/mediadelivery/rendition/900_319260/-T1z1mm-S800/">https://mdcop.weidmueller.com/mediadelivery/rendition/900_319260/-T1z1mm-S800/</a>
ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E337701

### Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	7a, 7cl
REACH SVHC	Lead 7439-92-1
SCIP	2f6dd957-421a-46db-a0c2-cf1609156924

### Important note

Product information	The ACT20M-RTCI-CO-OLP-S passive configurable temperature transducer isolates and converts analogue signals. An analogue RTD (Type Pt100) or TC (Type J, K) input signal is linearly converted into an analogue output signal and galvanically isolated. Power is supplied through the output measurement circuit (output- loop powered).
---------------------	---

### Downloads

Approval/Certificate/Document of Conformity	<a href="#">DNV-GL certificate</a> <a href="#">FM certificate</a> <a href="#">IECEx certificate</a> <a href="#">ATEX certificate</a> <a href="#">Certification UL for canada</a> <a href="#">Declaration of Conformity</a>
Engineering Data	<a href="#">CAD data – STEP</a>
Software	<a href="#">DIP switch configuration tool</a>
User Documentation	<a href="#">instruction sheet</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	


# ACT20M-RTCI-CO-OLP-S

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Drawings

### Connection diagram




### Dimensional drawing



### DIP switch setting

		Temperature range (°C)									
		PT100: -200...+850 °C					TC-K: -100...+1372 °C				
RTD & TC sensor type	S1	Min	S2	Max	S2	Min	S2	Max	S2	Min	S2
PT100 2 wire	1	-200	1	850	1	-100	1	1372	1	-100	1
PT100 3 wire	2	-200	2	850	2	-100	2	1372	2	-100	2
PT100 4 wire	3	-200	3	850	3	-100	3	1372	3	-100	3
TC (external CJC)	4	-200	4	850	4	-100	4	1372	4	-100	4
TC (external CJC II)	5	-200	5	850	5	-100	5	1372	5	-100	5
TC (external CJC III)	6	-200	6	850	6	-100	6	1372	6	-100	6
TC (external CJC IV)	7	-200	7	850	7	-100	7	1372	7	-100	7
TC (external CJC V)	8	-200	8	850	8	-100	8	1372	8	-100	8
TC (external CJC VI)	9	-200	9	850	9	-100	9	1372	9	-100	9
TC (external CJC VII)	10	-200	10	850	10	-100	10	1372	10	-100	10
Output	11	0	1	40	1	0	1	250	1	0	1
4...20 mA	12	0	2	40	2	0	2	250	2	0	2
20...4 mA	13	0	3	40	3	0	3	250	3	0	3
Sensor error detection	14	0	4	40	4	0	4	250	4	0	4
enable	15	0	5	40	5	0	5	250	5	0	5
disable	16	0	6	40	6	0	6	250	6	0	6
Output error level	17	0	7	40	7	0	7	250	7	0	7
0V	18	0	8	40	8	0	8	250	8	0	8
1V	19	0	9	40	9	0	9	250	9	0	9
Noise suppression	20	0	10	40	10	0	10	250	10	0	10
50 Hz	21	0	11	40	11	0	11	250	11	0	11
60 Hz	22	0	12	40	12	0	12	250	12	0	12
Response time	23	0	13	40	13	0	13	250	13	0	13
50 ms	24	0	14	40	14	0	14	250	14	0	14
100 ms	25	0	15	40	15	0	15	250	15	0	15
500 ms	26	0	16	40	16	0	16	250	16	0	16

example for DIP switch setting  
(with ACT20M tool software)



example for DIP switch setting  
(with ACT20M tool software)

**ACT20M-RTCI-CO-OLP-S****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Blank**

MultiFit is the Weidmüller marker system used for other makes of terminals. Similar to the Weidmüller Dekafix, the markers of the MultiFit family are available ready-for-use with standard printing.

We recommend to carry out a test with sample markers on the terminals used when using MultiFit for the first time.

- One marker, suitable for different makes of terminals.
- Ready-to-use markers with standard printing
- Blank markers for printing with the PrintJet CONNECT or Plotter
- Delivery of individually printed markers according to customer CAE data or specifications
- One marking system for all applications

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**

Type	MF 5/7.5 MC NE WS	Version
Order No.	<a href="#">1877680000</a>	MultiFit, Terminal marker, 5 x 7.5 mm, Pitch in mm (P): 7.50 Adels
GTIN (EAN)	4032248468270	RKW, Phoenix, white
Qty.	320 pc(s).	