

**IE-FCI-PWB-CH****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

FrontCom® Vario integrates multiple functions in only one single frame. The system is easy to install and you can select from a wide range of data, signal and power modules. In addition to being extremely compact, FrontCom® Vario offers a number of unique product features that will make your project planning and work activities secure, fast and future-proof. Furthermore, the FrontCom® Vario system has an attractive housing design that, by the way, offers highest impact-resistance and fully meets the requirements of IP 65 protection class.

**General ordering data**

|            |  |
|------------|--|
| Version    | FrontCom, Insert Power large, Type J, Socket connector, CH |
| Order No.  | <a href="#">1450780000</a>                                 |
| Type       | IE-FCI-PWB-CH  |
| GTIN (EAN) | 4050118255553  |
| Qty.       | 1 pc(s).   |

## IE-FCI-PWB-CH

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |      |
|------------|------|
| Net weight | 25 g |
|------------|------|

## Temperatures

|                     |                |                       |               |
|---------------------|----------------|-----------------------|---------------|
| Storage temperature | -10 °C...70 °C | Operating temperature | -5 °C...40 °C |
|---------------------|----------------|-----------------------|---------------|

## General data

|                |                    |                   |        |
|----------------|--------------------|-------------------|--------|
| Connector face | Type J             | Fire load         | 770 kJ |
| Insert type    | Insert Power large | Protection degree | IP20   |

## Clampable conductors

|  |                             |
|--|-----------------------------|
| Conductor connection cross-section, extremely flexible with wire end ferrule | 1.5 ... 1.5 mm <sup>2</sup> |
|--|-----------------------------|

|  |      |                     |
|--|------|---------------------|
| Conductor connection cross-section, extremely flexible with wire end ferrule | min. | 1.5 mm <sup>2</sup> |
|  | max. | 1.5 mm <sup>2</sup> |

|   |                             |
|---|-----------------------------|
| Conductor connection cross-section, extremely flexible without wire end ferrule | 1.5 ... 2.5 mm <sup>2</sup> |
|---|-----------------------------|

|   |      |                     |
|---|------|---------------------|
| Conductor connection cross-section, extremely flexible without wire end ferrule | min. | 1.5 mm <sup>2</sup> |
|   | max. | 2.5 mm <sup>2</sup> |

|  |                             |
|--|-----------------------------|
| Conductor connection cross-section, flexible with wire end ferrule | 1.5 ... 1.5 mm <sup>2</sup> |
|--|-----------------------------|

|  |      |                     |
|--|------|---------------------|
| Conductor connection cross-section, flexible with wire end ferrule | min. | 1.5 mm <sup>2</sup> |
|  | max. | 1.5 mm <sup>2</sup> |

|   |                             |
|---|-----------------------------|
| Conductor connection cross-section, flexible without wire end ferrule | 1.5 ... 2.5 mm <sup>2</sup> |
|---|-----------------------------|

|   |      |                     |
|---|------|---------------------|
| Conductor connection cross-section, flexible without wire end ferrule | min. | 1.5 mm <sup>2</sup> |
|   | max. | 2.5 mm <sup>2</sup> |

|   |      |                     |
|---|------|---------------------|
| Conductor connection cross-section, rigid | max. | 2.5 mm <sup>2</sup> |
|   | min. | 1.5 mm <sup>2</sup> |

|   |                             |
|---|-----------------------------|
| Conductor connection cross-section, rigid | 1.5 ... 2.5 mm <sup>2</sup> |
|---|-----------------------------|

|                  |       |
|------------------|-------|
| Stripping length | 10 mm |
|------------------|-------|

|                    |         |
|--------------------|---------|
| Type of connection | PUSH IN |
|--------------------|---------|

## Technical data

|                       |                  |               |      |
|-----------------------|------------------|---------------|------|
| Housing main material | Polycarbonate PC | Rated current | 10 A |
| Rated voltage (AC)    | 250 V            |               |      |

## General standards

|                       |            |
|-----------------------|------------|
| Certificate No. (DNV) | TAA000022B |
|-----------------------|------------|

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001121    | ETIM 7.0    | EC001121    |
| ETIM 8.0    | EC001121    | ETIM 9.0    | EC001121    |
| ECLASS 9.0  | 27-44-03-90 | ECLASS 9.1  | 27-18-90-90 |
| ECLASS 10.0 | 27-44-03-90 | ECLASS 11.0 | 27-44-03-90 |
| ECLASS 12.0 | 27-18-28-92 | ECLASS 13.0 | 27-18-28-92 |

**IE-FCI-PWB-CH****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Approvals**

Approvals



ROHS

Conform

**Downloads**Approval/Certificate/Document of Con-  
formity[GL FrontCom](#)

Engineering Data

[CAD data – STEP](#)

User Documentation

[MAN IE GUIDE DE](#)[MAN IE GUIDE EN](#)[Socket Insert Overview EN](#)[Socket Insert Overview DE](#)[Designation key / Type key](#)

Catalogues

[Catalogues in PDF-format](#)

Brochures



[MB FREECONCONTACT EN](#)[FL FIELDWIRING EN](#)[PI PROFINET CABLING EN](#)[PI PROFINET CABLING EN](#)

**IE-FCI-PWB-CH****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Drawings****Dimensioned drawing****Dimensioned drawing**

## IE-FCI-PWB-CH

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

### Rail adaptor for socket inserts



At Weidmüller you can get everything you need from one source - including accessories for Industrial Ethernet.

The benefits for you:

- tools
- testing instruments
- cable bushings
- cabinet connections
- markers
- dust protection
- power packs
- overvoltage protection

### General ordering data

|            |                            |
|------------|----------------------------|
| Type       | IE-DINRAIL-AD-PWB          |
| Order No.  | <a href="#">2534680000</a> |
| GTIN (EAN) | 4050118546354              |
| Qty.       | 1 pc(s).                   |