

VG M40 EXE SW**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

Polyamide cable glands, which are suitable for usage in explosion risk zones Ex e (increased safety) and Ex i (intrinsic safety).

Weidmüller offers a product family without restrictions and besides compliance with standards, the cable gland excels thanks to its increased impact resistance of 4/7 Joule and a possible temperature range down to -60°C without restrictions. They have been tested to the current standard and EN 60079-0 directive, they are ATEX and IECEx certified.

General ordering data

Version	VG Exe 4J (Ex plastic cable gland 4J Exe), Cable glands, straight, M 40, 18 mm, OD min. 22 - OD max. 32 mm, IP54, IP66, IP67, IP68 - 5 bar (30 min.), Polyamide 6
Order No.	1461180000
Type	VG M40 EXE SW
GTIN (EAN)	4050118267280
Qty.	10 pc(s).

VG M40 EXE SW**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Height	50 mm	Height (inches)	1.969 inch
Net weight	80.3 g		

Temperatures

Operating temperature	-40 °C...80 °C
-----------------------	----------------

Certificate numbers cable gland

Approval conditions	ATEX, IECEX	Certificate no. cable gland (ATEX)	IMQ 13 ATEX 010 X
Certificate no. cable gland (IECEX)	IECEX IMQ 13.0003X	Identification	Ex e IIC Gb, Ex tb IIIC Db IP66/68

General information

AF size 1	53 mm	AF size 2	53 mm
Cable glands	metric	Explosion protection type	Improved safety Ex e
External thread	M 40	Halogen	Yes
Impact resistance	4 J ATEX version	Installation guidelines	See assembly instructions
Length of thread	18 mm	Material	Polyamide 6
Operating temperature range, max.	80 °C	Operating temperature range, min.	-40 °C
Outer cable diameter, max.	32 mm	Outer cable diameter, min.	22 mm
Pitch of thread	1.5 mm	Protection degree	IP54, IP66, IP67, IP68 - 5 bar (30 min.)
Protection degree with GWDR	IP54, IP66, IP67, IP68 - 5 bar (30 min.)	Seal insert	CR
Standards	IEC 60079-0, IEC 60079-7, IEC 60079-31, EN 60079-0, EN 60079-7, EN 60079-31	UL 94 flammability rating	HB

Classifications

ETIM 6.0	EC000441	ETIM 7.0	EC000441
ETIM 8.0	EC000441	ETIM 9.0	EC000441
ECLASS 9.0	27-14-44-32	ECLASS 9.1	27-14-44-34
ECLASS 10.0	27-14-44-32	ECLASS 11.0	27-14-44-32
ECLASS 12.0	27-14-08-02	ECLASS 13.0	27-14-08-02

Approvals

Approvals	CE; EAC; ATEX; IECEX
ROHS	Conform

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format

VG M40 EXE SW

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Brass lock nuts, nickel-plated



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	SKMU M40 MS	Version
Order No.	1737030000	SKMU MS (brass locknut), Locknut, M 40, 5 mm, Brass, nickel-plated
GTIN (EAN)	4008190956509	
Qty.	50 pc(s).	