

**VGM25-MS68 EMC 11-20SET****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Similar to illustration**

The increasing sensitivity of electronic components and the increasing electromagnetic interference frequencies require cable glands to play an important role in the shielding concept of a system. This type of EMC cable glands are made for shielding against interference frequencies, with a 360° screening connection. A Finger-locking seal provides superior cable retention & strain relief, next to it, the cable gland meets the mechanical requirements of EN 62444. Due to the patented design a very easy and fast assembly will be possible.

**General ordering data**

Version	Accessories
Order No.	<a href="#">1463720000</a>
Type	VGM25-MS68 EMC 11-20SET
GTIN (EAN)	4050118269871
Qty.	1 pc(s).

**VGM25-MS68 EMC 11-20SET****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Length	63.5 mm	Length (inches)	2.5 inch
Net weight	94.44 g		

**Temperatures**

Limit temperature	-40 °C ... 130 °C
-------------------	-------------------

**General information**

AF size	30 mm	Cable glands	M 25, EMV
External thread	M 25	Length of thread	34 mm
Material	Brass, nickel-plated	O-Ring	NBR
Protection degree	IP68 - 15 bar	Standards	EN 45545-2:2013

**Classifications**

ETIM 6.0	EC000441	ETIM 7.0	EC000441
ETIM 8.0	EC000441	ETIM 9.0	EC000441
ECLASS 9.0	27-14-44-32	ECLASS 9.1	27-14-44-32
ECLASS 10.0	27-14-44-32	ECLASS 11.0	27-14-44-32
ECLASS 12.0	27-14-08-01	ECLASS 13.0	27-14-08-01

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
SCIP	b5ff1f66-ddba-4739-9fc0-0521ddb52139

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Engineering Data	<a href="#">CAD data – STEP</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">FL FIELDWIRING EN</a> <a href="#">FL FIELDWIRING EN</a>