

FP DUO LED DC HQ8**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Energy-efficient emergency lighting with a long service life**

- **developed and to be used in accordance with DIN EN 60598-2-22**
- LED lamp for harsh environmental conditions (shocks and vibration, temperature range)
- higher energy efficiency and service life than fluorescent lamps
- Can be used worldwide thanks to the multi-voltage input (20 V...60 VDC)
- high fire protection classification V0
- Beam direction to two sides
- 5W Power

Versions

- Pluggable with heavy duty connector and round connector
- Pre-assembled 2.5 mm²

General ordering data

Order No.	1488480000
Type	FP DUO LED DC HQ8
GTIN (EAN)	4050118298567

FP DUO LED DC HQ8

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Height	128 mm	Height (inches)	5.039 inch
Width	104 mm	Width (inches)	4.094 inch
Length	271 mm	Length (inches)	10.669 inch
Net weight	662 g		

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...70 °C
Humidity	92 % @ 25 °C		

General data

Amplitude of acceleration	5 m/s ² (@ 9-200 Hz)	Amplitude of deflection	1.5 mm (2-9 Hz)
Connector cross-section, max.	2.5 mm ²	Connector cross-section, min.	0.5 mm ²
Efficiency class (according to EU Directive No. 874/2012)	E	Halogen	No
Height	≤ 3000 m	Insulation voltage	<500 V (housing/PE)
LED operating life	> 50.000 h	Light colour (CCT)	Cool White, 6000K, 6000K
Light current (in total in both directions)	496 lm	Mounting position, installation notice	Arbitrary
Peak acceleration, type L	70 m/s ²	Pollution severity	2
Protection class	II	Protection degree	IP54
Shape of the LED module	Other	Shock resistance EN 60721-3-3	Class 3M3 portable
Short-circuit protection	Yes, internal	Silicone	No
Surge voltage category	II	Type of connection	Plug-in connector with fixed number of poles, HQ 8
UL 94 flammability rating	V-0	Vibration resistance EN 60721-3-3	Class 3M3 sinusoidal, stationary

Rated data acc. to IEC 60598-1

DC input voltage range	24...120 V DC	Input voltage	21.6 V ... 144 V DC /protected against reverse polarity
Power rating	5 W		

Classifications

ETIM 6.0	EC001959	ETIM 7.0	EC001959
ETIM 8.0	EC001959	ETIM 9.0	EC001959
ECLASS 9.0	27-11-06-40	ECLASS 9.1	27-11-06-40
ECLASS 10.0	27-11-06-40	ECLASS 11.0	27-11-06-40
ECLASS 12.0	27-11-06-40	ECLASS 13.0	27-11-06-40

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1 Potassium perfluorobutane sulfonate 29420-49-3 6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol 119-47-1
SCIP	8ef82740-ea38-4455-b067-0cceaab45207

FP DUO LED DC HQ8

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

UL File Number Search UL Website

Certificate no. (cULus) E345151

Downloads

Catalogues [Catalogues in PDF-format](#)