

IE-ANT-3G-806-2500-4-NF**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image****Antennas and antenna accessories (coax cables and mounts)**

- State-of-the-art antennas
- Industry proven
- Robust design (up to IP67 protection)
- For outdoor and indoor use
- Latest technology support
- Up to Wi-Fi 6 and Wi-Fi 6E (2.4 GHz, 5 GHz, 6 GHz)
- Up to 5G (NR) support (700 MHz - 3.8 GHz)
- Also support for other technologies (e.g. Bluetooth, GNSS, etc.)
- Appropriate coax cables at different lengths
- Suitable pole and wall mounts

General ordering data

Version	Mobile radio antenna, Omni-directional antenna, Gain of up to 4 dBi, Vertical, Linear, 1x N-type female, bottom, IP66, , Impedance: 50 Ω
Order No.	1491170000
Type	IE-ANT-3G-806-2500-4-NF
GTIN (EAN)	4050118300727
Qty.	1 pc(s).
Delivery status	This article will no longer be available in the future.
Available until	2023-12-01
Alternative product	2788150000

Creation date May 6, 2024 12:33:58 PM CEST

Catalogue status 04.05.2024 / We reserve the right to make technical changes.

IE-ANT-3G-806-2500-4-NF**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Height	48 mm	Height (inches)	1.89 inch
Diameter	36 mm	Net weight	164.68 g

Temperatures

Storage temperature	-40 °C...70 °C	Operating temperature	-40 °C...70
---------------------	----------------	-----------------------	-------------

Enclosure material

Colour	black	Housing main material	Plastic
--------	-------	-----------------------	---------

Included in delivery

Included in delivery	1 x antenna, 1x screw connection and mounting materials for vandal-proof mounting
----------------------	---

Technical data

Antenna gain	Band 1: 3 dBi, Band 2: 4 dBi	Composite power max.	100 W
Frequency range	Band 1: 806-960 (MHz), Band 2: 1710-2500 (MHz)	Impedance	50 Ω
Polarisation	Vertical, Linear	Radiation	Omnidirectional
Standing wave ratio	< 2	Type of connection	1x N-type female, bottom

Environmental conditions

Applications	for indoor and outdoor use	Operating temperature, max.	70
Operating temperature, min.	-40 °C	Storage temperature, max.	70 °C
Storage temperature, min.	-40 °C		

Classifications

ETIM 6.0	EC001698	ETIM 7.0	EC001698
ETIM 8.0	EC001698	ETIM 9.0	EC001698
ECLASS 9.1	19-07-01-90	ECLASS 10.0	19-07-01-07
ECLASS 11.0	19-07-01-07	ECLASS 12.0	19-07-01-07
ECLASS 13.0	19-07-01-07		

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Approvals

ROHS	Conform
------	---------

Downloads

User Documentation	Installation Instruction
Catalogues	Catalogues in PDF-format

IE-ANT-3G-806-2500-4-NF

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings

Product image



Antenna including mounting kit and screw
connection for vandal-proof installation