

**KLIPPON CS STB 2.1-7****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

IEC EX



On-site control with Ex-certified Klippon® Control Station: small command and signalling devices.  
Approved operating and display elements in stainless steel, aluminium or polyester enclosures.  
You want to control and safeguard your work processes in hazardous areas. For on-site control - approved Klippon® enclosure solutions with control and display elements.

**General ordering data**

Version	Klippon Control Station (control and signalling device), Control / signalling device, KLIPPON STB 2.1 SS, Stainless steel 1.4404 (316L), Pushbutton - red, Light module - green, Pushbutton - green, 2 NC contact, 2 NO contacts, -55 °C...+55 °C, IP54, IP66
Order No.	<a href="#">1537340000</a>
Type	KLIPPON CS STB 2.1-7
GTIN (EAN)	4050118341393
Qty.	1 pc(s).
Cable gland	<a href="#">1460070000</a>
Reference product	<a href="#">1002730000</a>

Creation date April 28, 2024 2:07:09 AM CEST

## KLIPPON CS STB 2.1-7

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	81.5 mm	Depth (inches)	3.209 inch
Depth with add-on components	103 mm	Height	190 mm
Height (inches)	7.48 inch	Width	150 mm
Width (inches)	5.905 inch	Mounting dimension - width	145 mm
Net weight	2,200 g		

## Temperatures

Ambient temperature	-55 °C...+55 °C
---------------------	-----------------

## Certificate numbers enclosure

Certificate No. (ATEX)	TUEV14ATEX7606X	Certificate No. (IECEX)	IECEXITA14.0013X
Certificate no. Terminal Box (ATEX)	TÜV 14 ATEX 7606 X	Certificate no. Terminal Box (IECEX)	IECEX ITA 14.0013X
Certificate no. Terminal Box (INMETRO)	LMP 21.0019X		

## General information

1 Position in enclosure	Pushbutton - red	2 Position in enclosure	Light module - green
3 Position in enclosure	Pushbutton - green	Contact design	2 NC contact, 2 NO contacts
Operating voltage, max.	250 V	Operating current at 40°C ambient temperature, max.	1.5 mm² - T6 10 A, 1.5 mm² - T5 16 A, 2.5 mm² - T6 16 A
Operating current at 55°C ambient temperature, max.	1.5 mm² - T4 16 A, 1.5 mm² - T5 10 A, 2.5 mm² - T5 16 A	Actuators	Pushbutton
Actuator colour	red, green	Drill holes side B	1 x M25
Lid attachment	M5 hexagonal screw with slot and 10mm distance across flats	Seal material of operating and display elements	EPDM
Enclosure seal material	Silicone (VMQ)	Torque for lid screws	2.5 Nm
Earth stud torque	7.5 Nm	External earth	M6 earthing studs, stainless steel
Internal earth	M6 x 10 earthing studs integrated in the lid, stainless steel	Marking	II 2 G Ex d e IIC T* Gb, II 2 D Ex tb IIIC T*°C Db
Cable gland clamping area, max.	18 mm	Cable gland clamping area, min.	10 mm
Wire connection cross section, finely stranded, max.	2.5 mm²	Illumination module colour	green
Type of mounting	Wall mounting	Surface finish	Mirror polished
Impact resistance	4 joules in acc. with IEC60079-0	Temperature class	T4, T5, T6
Material	Stainless steel 1.4404 (316L)		

## Housing

Drill holes side B	1 x M25	Material	Stainless steel 1.4404 (316L)
--------------------	---------	----------	-------------------------------

**KLIPPON CS STB 2.1-7****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Classifications**

ETIM 6.0	EC002503	ETIM 7.0	EC002503
ETIM 8.0	EC002503	ETIM 9.0	EC002503
ECLASS 9.0	27-18-05-02	ECLASS 9.1	27-18-05-90
ECLASS 10.0	27-18-05-02	ECLASS 11.0	27-18-05-02
ECLASS 12.0	27-18-05-02	ECLASS 13.0	27-18-05-02

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
SCIP	c0b142f1-4049-4b95-bbc3-9959a2d3b09c

**Approvals**

Approvals

**ATEX****Downloads**


Approval/Certificate/Document of Conformity	<a href="#">TUEV14ATEX7606X</a> <a href="#">IECEXITA14.0013X</a> <a href="#">INMETRO Certificado INMETRO - LMP 21.0019X KCS</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">PI KLIPPON CS EN</a>

**KLIPPON CS STB 2.1-7**
**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)
**Drawings**


Klippon CS POK 122189 - 4 - Lz8marLeBmss	
Actuating and illuminating elements	
B: Button	
I: Illuminated button	
L: Lamp	
a: NO	
m: NC and NO	
c: NC	
g: Green	
r: Red	
e: Emergency Stop	
p: Push	
k: Key	
3: Positions of the switch	
Drilling design	
Dimensions	
Enclosure Range	
POK (Polyester)	
K (Aluminium)	
STB (Stainless Steel)	
Product Name	
Control Station	
Brand Name	
Klippon®	