

SAI-WDF 8P M12 M16**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**General ordering data**

Version	Panel feed-through, Number of poles: 8, Coding: A-coded, M12, 30 V
Order No.	1543490000
Type	SAI-WDF 8P M12 M16
GTIN (EAN)	4050118348170
Qty.	1 pc(s).

SAI-WDF 8P M12 M16**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Net weight 24 g

Technical data customisable plug-in connectors

Coding	A-coded	Contact surface	Au (Gold)
Number of poles	8	Pollution severity	3
Protection degree	IP67	Rated current	1.5 A
Rated current	Contacts 1-4 8A, contact 5 2A, 2 A (8-pole)	Rated voltage	30 V
Shield connection	Yes	Temperature range of housing	-25...+85 °C
Threaded ring material	Diecast zinc		

General technical specifications

Coding	A-coded	Connection thread	M12
Contact surface	Au (Gold)	Number of poles	8
Pollution severity	3	Protection degree	IP67
Rated current	1.5 A	Rated voltage	30 V
Temperature range of housing	-25...+85 °C	Threaded ring material	Diecast zinc

Classifications

ETIM 6.0	EC002925	ETIM 7.0	EC002925
ETIM 8.0	EC002925	ETIM 9.0	EC002925
ECLASS 9.0	27-44-01-06	ECLASS 9.1	27-44-01-06
ECLASS 10.0	27-44-01-06	ECLASS 11.0	27-44-01-06
ECLASS 12.0	27-44-01-06	ECLASS 13.0	27-44-01-06

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	1c533b66-fcff-4da5-b89f-fd55fbf5cb55

Approvals

ROHS	Conform
------	---------

Downloads



Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN

SAI-WDF 8P M12 M16**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Drawings****Drawing****Pole scheme****Pole scheme**