

JB 25-50**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

Our potential equalisation terminal blocks allow you to achieve reliably integrated potential equalisation, even in extended systems.

General ordering data

Version	Potential distributor terminal, Screw connection, Number of connections: 2, Brass coloured
Order No.	1547500000
Type	JB 25-50
GTIN (EAN)	4050118387445
Qty.	10 pc(s).

JB 25-50**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	24 mm	Depth (inches)	0.945 inch
Height	32 mm	Height (inches)	1.26 inch
Width	33 mm	Width (inches)	1.299 inch
Net weight	134.505 g		

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-40°C bis +75°C
---------------------	----------------	---------------------	-----------------

Material data

Material	Brass	Colour	Brass coloured
----------	-------	--------	----------------

System specifications

Number of levels	1
------------------	---

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of mounting	when screwed in		

Conductors for clamping (additional connection)

Connection type, additional connection	Screw connection
--	------------------

Conductors for clamping (rated connection)

Clamping range, max.	50 mm ²	Clamping range, min.	10 mm ²
Clamping screw	M 6	Connection direction	on side
Number of connections	2	Stripping length	33 mm
Tightening torque, min.	5 Nm	Type of connection	Screw connection
Wire connection cross section, finely stranded, max.	50 mm ²	Wire connection cross section, finely stranded, min.	10 mm ²

General

Installation advice	Direct mounting
---------------------	-----------------

Rating data

Pollution severity	3
--------------------	---

Classifications

ETIM 6.0	EC000897	ETIM 7.0	EC000897
ETIM 8.0	EC000897	ETIM 9.0	EC000897
ECLASS 9.0	27-14-11-20	ECLASS 9.1	27-14-11-20
ECLASS 10.0	27-14-11-20	ECLASS 11.0	27-14-11-20
ECLASS 12.0	27-14-11-20	ECLASS 13.0	27-25-01-19

JB 25-50**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
SCIP	233a6569-7068-4d0c-aa40-90d1ca672d0b

Important note

Product information	Qualified in acc. IEC 60947-7-2, Can be used for functional equipotential bonding and protective equipotential bonding Mounting on cable trench with M6x9 screw
---------------------	---

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
User Documentation	Storage Conditions Terminal Blocks
Catalogues	Catalogues in PDF-format
Brochures	