

**CAN SUB-D M12 180 TERM****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Similar to illustration**

Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly.

**General ordering data**

Version	SUB-D
Order No.	<a href="#">1555290000</a>
Type	CAN SUB-D M12 180 TERM
GTIN (EAN)	4050118361216
Qty.	1 pc(s).

**CAN SUB-D M12 180 TERM****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	14.8 mm	Depth (inches)	0.583 inch
Height	80.7 mm	Height (inches)	3.177 inch
Width	31 mm	Width (inches)	1.22 inch
Net weight	90 g		

**Temperatures**

Humidity	Max. 75% at +25°C, non-condensing
----------	-----------------------------------

**Technical specifications for sub-D connector**

BUS interface	D-Sub 9-pole, Socket	BUS, cable interface	M12 A-coded, pin + socket
Data rate	1 Mbps	Housing main material	ZnAl
Humidity	Max. 75% at +25°C, non-condensing	Interlock	UNC4-40
Outgoing elbow	180°	Plugging cycles	≥ 200
Programming interface	No	Protection degree	IP30
Temperature range of housing	-20...+70 °C	Terminating resistor available	Yes

**Classifications**

ETIM 6.0	EC001132	ETIM 7.0	EC001132
ETIM 8.0	EC001132	ETIM 9.0	EC001132
ECLASS 9.0	27-44-03-02	ECLASS 9.1	27-44-03-90
ECLASS 10.0	27-44-03-02	ECLASS 11.0	27-44-03-02
ECLASS 12.0	27-44-03-02	ECLASS 13.0	27-44-03-02

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
SCIP	3ccc1d9b1-0f2a-47ed-a501-ddcfcfaaf625

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">FL FIELDWIRING EN</a>