


**HDC-C-HD-BM0.75-1.00AG****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Crimps provide a electrical and mechanical connection between wire and contact that is both secure and reliable. The optimal crimp connection is gas-tight and corrosion-resistant.

**General ordering data**

Version	Heavy-duty connectors, Crimp contact, HD, HDD, HQ, MixMate, Female, Conductor cross-section, max.: 1, turned, Copper alloy
Order No.	<a href="#">1601760000</a>
Type	HDC-C-HD-BM0.75-1.00AG
GTIN (EAN)	4008190158354
Qty.	100 pc(s).

## HDC-C-HD-BM0.75-1.00AG

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Diameter	3.5 mm	Net weight	0.6 g
----------	--------	------------	-------

## General data

Conductor cross-section, max.	1 mm <sup>2</sup>	Conductor cross-section, min.	0.75 mm <sup>2</sup>
Contact diameter, male Ø	1.6 mm	Contact material	Copper alloy
Cross-section for connected wire	0.75 - 1 mm <sup>2</sup>	Material	Copper alloy
Plugging cycles	≥ 500	Production methods	turned
Series	HD	Stripping length, rated connection	8 mm
Surface finish	silver	Type	Female
Type of connection	Crimp connection	Version insert	HD, HDD, HQ, MixMate
Volume resistance	≤4 mΩ		

## Classifications

ETIM 6.0	EC000796	ETIM 7.0	EC000796
ETIM 8.0	EC000796	ETIM 9.0	EC000796
ECLASS 9.0	27-44-02-04	ECLASS 9.1	27-44-02-04
ECLASS 10.0	27-44-02-04	ECLASS 11.0	27-44-02-04
ECLASS 12.0	27-44-02-04	ECLASS 13.0	27-44-02-04

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	6eabd5ae-2d6b-409e-8bdf-87c27ee10e40

## Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E92202

## Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">Zuken E3.S</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">FL FIELDWIRING EN</a> <a href="#">FL FIELDWIRING EN</a>

**HDC-C-HD-BM0.75-1.00AG****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Drawings**

Leiterquerschnitt	Abisolierlänge	
0,14 - 0,37 mm <sup>2</sup>	AWG 26-22	8 mm
0,50 mm <sup>2</sup>	AWG 20	8 mm
0,75 - 1,00 mm <sup>2</sup>	AWG 18	8 mm
1,50 mm <sup>2</sup>	AWG 16	8 mm
2,50 mm <sup>2</sup>	AWG 14	8 mm

