


VT SF 2/21 MC NE GE V0**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration



SlimFix are conductor and cable markers with a space-saving design. The markers can be fitted even after the conductor has been installed. They consist of halogen-free material and comply with flammability rating V0/V2. SlimFix is an acknowledged and accredited marker type for traffic engineering applications. The SF tool allows easy installation, even in case of small markers.

Advantages:

- Halogen-free material
- Flammability rating V0/V2
- Approved and accredited markers for traffic engineering applications, etc.
- Has to be fixed with cable ties if the conductor cross-section is larger than 16.0 mm²
- Markers in proven MultiCard format

General ordering data

Version	SlimFix, Conductor and cable markers, 2.2 - 2.9 mm, 21 x 3.6 mm, yellow
Order No.	1689410004
Type	VT SF 2/21 MC NE GE V0
GTIN (EAN)	4008190872434
Qty.	800 pc(s).
compatible printer	2715590000 2438520000 2438510000

VT SF 2/21 MC NE GE V0**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	3.65 mm	Depth (inches)	0.144 inch
Height	21 mm	Height (inches)	0.827 inch
Width	3.6 mm	Width (inches)	0.142 inch
Net weight	0.299 g		

Temperatures

Operating temperature range	-50...120 °C
-----------------------------	--------------

General data

Colour	yellow
Halogen	No
Material	Polyamide 66
Number of markers per combination	1 MultiCard = Conductor and cable markers
Number of markers per packaging unit	Form of supply MultiCard
Operating temperature range	-50...120 °C
Operating temperature range, max.	120 °C
Operating temperature range, min.	-50 °C
Recommended industries	Transportation, Machinery
Size of labelling field	21 x 3.6 mm
Type of printing	neutral
UL 94 flammability rating	V-0
Width	3.6 mm

Conductor and cable markers

Conductor O.D.	2.2 - 2.9 mm	Conductor O.D., max.	2.9 mm
Conductor O.D., min.	2.2 mm	Conductor cross-section, max.	1.5 mm ²
Conductor cross-section, min.	0.75 mm ²	Cross-section for connected wire	0.75 - 1.5 mm ²
Halogen	No		

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ECLASS 9.0	27-40-04-01	ECLASS 9.1	27-40-04-01
ECLASS 10.0	27-40-04-01	ECLASS 11.0	27-28-11-02
ECLASS 12.0	27-28-11-02	ECLASS 13.0	27-28-11-02

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Engineering Data	Zuken E3.S
Catalogues	Catalogues in PDF-format

VT SF 2/21 MC NE GE V0

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings

