


ZQV 2.5N/10 BL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

The plug-in cross-connections feature easy handling and quick installation. This saves a great deal of time during installation in comparison with screwed solutions.

General ordering data

Version	W-Series, Cross-connector, 24 A
Order No.	1718070000
Type	ZQV 2.5N/10 BL
GTIN (EAN)	4008190349684
Qty.	20 pc(s).
Delivery status	This article will no longer be available in the future.
Available until	2021-12-31
Alternative product	1527880000

ZQV 2.5N/10 BL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	23 mm	Depth (inches)	0.906 inch
Height	49.7 mm	Height (inches)	1.957 inch
Width	2.8 mm	Width (inches)	0.11 inch
Net weight	5.35 g		

Temperatures

Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-60
Continuous operating temp., max.	130		

Material data

Material	Wemid	Colour	blue
UL 94 flammability rating	V-0		

System specifications

Version	For the terminals
---------	-------------------

Additional technical data

Explosion-tested version	Yes	Installation advice	Direct mounting
Type of fixing	Plugged		

Cross-connector

Number of cross-connected terminals	10	Rated current, multi-pole	24 A
Type	Cross-connector		

Dimensions

Pitch in mm (P)	5.1 mm
-----------------	--------

General

Installation advice	Direct mounting	Number of poles	10
---------------------	-----------------	-----------------	----

Rating data

Rated current	24 A
---------------	------

Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ETIM 9.0	EC000489
ECLASS 9.0	27-14-11-40	ECLASS 9.1	27-14-11-40
ECLASS 10.0	27-14-11-40	ECLASS 11.0	27-14-11-40
ECLASS 12.0	27-14-11-40	ECLASS 13.0	27-25-03-03

Important note

Product information	Due to stability and temperature reasons It is only possible to break out 60% of contact elements The usage of cross connectors reduces the rated voltage to 400VThe voltage reduced to 25V if cut cross connection with blank cut edges are used
---------------------	---

ZQV 2.5N/10 BL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Approvals**

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Engineering Data	Zuken E3.S
User Documentation	StorageConditionsTerminalBlocks User Manual ZQV 2.5
Catalogues	Catalogues in PDF-format
Brochures	