

KLBUE 15-32 CPF**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

Thanks to special mounting feet, the product portfolio also includes shield clamping saddles that can be mounted on the C-profiles. The shield is diverted from the shield clamping saddles via the mounting foot to the C-profiles and thus to PE (ground).

General ordering data

| | |
|------------|-------------------------------------|
| Version | Clamping yoke, Clamping yoke, Steel |
| Order No. | 1752711001 |
| Type | KLBUE 15-32 CPF |
| GTIN (EAN) | 4032248044443 |
| Qty. | 10 pc(s). |

KLBUE 15-32 CPF**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

| | | | |
|------------|---------|-----------------|------------|
| Depth | 64 mm | Depth (inches) | 2.52 inch |
| Height | 32 mm | Height (inches) | 1.26 inch |
| Width | 33.5 mm | Width (inches) | 1.319 inch |
| Net weight | 84.5 g | | |

Temperatures

| | |
|---------------------|----------------|
| Storage temperature | -25 °C...55 °C |
|---------------------|----------------|

Material data

| | | | |
|----------|-------|--------|------|
| Material | Steel | Colour | grey |
|----------|-------|--------|------|

System specifications

| | | | |
|---------|-------------------------|------|-------|
| Version | For a shield connection | Rail | TS 27 |
|---------|-------------------------|------|-------|

Additional technical data

| | | | |
|--------------------------|-----------------|---------------------|-----------------|
| Explosion-tested version | Yes | Installation advice | Direct mounting |
| Type of fixing | when screwed in | | |

Conductors for clamping (rated connection)

| | | | |
|----------------------|-------|----------------------|-------|
| Cable diameter, max. | 32 mm | Cable diameter, min. | 15 mm |
|----------------------|-------|----------------------|-------|

Dimensions

| | |
|-----------------|-------|
| Pitch in mm (P) | 36 mm |
|-----------------|-------|

General

| | | | |
|---------------------|-----------------|------|-------|
| Installation advice | Direct mounting | Rail | TS 27 |
|---------------------|-----------------|------|-------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC002020 | ETIM 7.0 | EC002020 |
| ETIM 8.0 | EC002020 | ETIM 9.0 | EC002020 |
| ECLASS 9.0 | 27-14-11-50 | ECLASS 9.1 | 27-14-11-50 |
| ECLASS 10.0 | 27-14-11-50 | ECLASS 11.0 | 27-14-11-50 |
| ECLASS 12.0 | 27-14-11-50 | ECLASS 13.0 | 27-25-01-20 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|--------------------|--|
| Engineering Data | CAD data – STEP |
| User Documentation | Beipackzettel_KLBUE.pdf StorageConditionsTerminalBlocks |
| Catalogues | Catalogues in PDF-format |
| Brochures | |

KLBUE 15-32 CPF**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Steel**

Steel DIN rails are the most widespread on the market. Among metal DIN rails, they have the lowest shortcircuit protection, similar to stainless steel.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | TS 27X12.5M/ST/F.ZN | Version |
| Order No. | 1802690000 | Terminal rails, Rail, DIN EN 60715, Steel |
| GTIN (EAN) | 4032248257201 | |
| Qty. | 2 m | |