

TS 27X12.5M/ST/F.ZN**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

Steel DIN rails are the most widespread on the market. Among metal DIN rails, they have the lowest shortcircuit protection, similar to stainless steel.

General ordering data

Version	Terminal rails, Rail, DIN EN 60715, Steel
Order No.	1802690000
Type	TS 27X12.5M/ST/F.ZN
GTIN (EAN)	4032248257201
Qty.	2 m

TS 27X12.5M/ST/F.ZN

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	12.5 mm	Depth (inches)	0.492 inch
Height	27 mm	Height (inches)	1.063 inch
Width	2,000 mm	Width (inches)	78.74 inch
Net weight	50 g		

Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

Mounting rail

Installation advice	Direct mounting	
Length of the terminal rail	nominal	2,000 mm
	min.	0 mm
	max.	2,000 mm
Material	Steel	
Standards	DIN EN 60715	
Surface finish	galvanized	
Thickness	2 mm	

Classifications

ETIM 6.0	EC001285	ETIM 7.0	EC001285
ETIM 8.0	EC001285	ETIM 9.0	EC001285
ECLASS 9.0	27-40-06-02	ECLASS 9.1	27-40-06-02
ECLASS 10.0	27-40-06-02	ECLASS 11.0	27-40-06-02
ECLASS 12.0	27-40-06-02	ECLASS 13.0	27-40-06-02

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format
Brochures	

TS 27X12.5M/ST/F.ZN

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings

