

**SAIB-M8-4P****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly. Male plugs and female sockets for customisable assembly for M8, M12, M16 and 7/8" connections which are highly robust and ideally suited to machine engineering, for instance. The M8 round plug-in connectors are particularly suited to applications where space is limited. The screw connection can be used in a wide range of applications. With this technology the conductor, optionally with wire-end ferrules, can be plugged into connection elements and secured with a screw. It is the classic, cheapest form of connection technology that also supports multi-conductor connections.

**General ordering data**

Version	Field attachable connector, M8, Female socket, straight
Order No.	<a href="#">1803880000</a>
Type	SAIB-M8-4P
GTIN (EAN)	403224825986 1
Qty.	1 pc(s).

## SAIB-M8-4P

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Net weight	11 g
------------	------

## Technical data customisable plug-in connectors

Cable diameter	3.5...5 mm	Cable diameter, max.	5 mm
Cable diameter, min.	3.5 mm	Coding	none
Conductor cross-section, max.	0.5 mm <sup>2</sup>	Conductor cross-section, min.	0.14 mm <sup>2</sup>
Connection cross-section, max.	0.5 mm <sup>2</sup>	Connection cross-section, min.	0.14 mm <sup>2</sup>
Contact surface	Gold-plated	Housing main material	PA
Insulation strength	10 <sup>8</sup> Ω	Number of poles	4
Plugging cycles	≥ 50	Pollution severity	3
Protection degree	IP67	Rated current	4 A
Rated voltage	60 V	Shield connection	No
Temperature range of housing	-40 ... +85 °C	Threaded ring material	Diecast zinc
Type of connection	Screw connection		

## Classifications

ETIM 6.0	EC002635	ETIM 7.0	EC002635
ETIM 8.0	EC002635	ETIM 9.0	EC002635
ECLASS 9.0	27-44-01-02	ECLASS 9.1	27-44-01-03
ECLASS 10.0	27-44-01-02	ECLASS 11.0	27-44-01-02
ECLASS 12.0	27-44-01-16	ECLASS 13.0	27-44-01-02

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	ebf89fc8-a87f-4691-b87a-dfb9921774b4

## Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E307231

## Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">Zuken E3.S</a>
User Documentation	<a href="#">Manual</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">FL FIELDWIRING EN</a> <a href="#">FL FIELDWIRING EN</a>