



**SLS 5.08/16/180TB RF15 SN OR BX****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

Male plugs with clamping-yoke screw wire-connect system. With clip-on feet for attaching the male plugs on rail. The male plugs provide space for labelling and can be coded.

**General ordering data**

|              |  |
|--------------|--|
| Version      | PCB plug-in connector, male plug, 5.08 mm, Number of poles: 16, 180°, Clamping yoke connection, Clamping range, max. : 3.31 mm², Box |
| Order No.    | <a href="#">1846100000</a>   |
| Type         | SLS 5.08/16/180TB RF15 SN OR BX  |
| GTIN (EAN)   | 4032248362387  |
| Qty.         | 5 pc(s).   |
| Product data | IEC: 400 V / 21.5 A / 0.2 - 2.5 mm²<br>UL: 300 V / 14 A / AWG 26 - AWG 12  |
| Packaging    | Box  |

Creation date July 3, 2025 10:41:16 PM CEST

Catalogue status 21.06.2025 / We reserve the right to make technical changes.

## SLS 5.08/16/180TB RF15 SN OR BX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |          |                 |            |
|------------|----------|-----------------|------------|
| Depth      | 22.2 mm  | Depth (inches)  | 0.874 inch |
| Height     | 15.3 mm  | Height (inches) | 0.602 inch |
| Net weight | 31.856 g |                 |            |

## System Parameters

|  |  |                   |                            |
|--|--|-------------------|----------------------------|
| Product family                               | OMNIMATE Signal - series BL/SL 5.08              |                   |                            |
| Type of connection                           | Field connection                                 |                   |                            |
| Wire connection method                       | Clamping yoke connection                         |                   |                            |
| Pitch in mm (P)                              | 5.08 mm  |                   |                            |
| Pitch in inches (P)                          | 0.2 "  |                   |                            |
| Conductor outlet direction                   | 180°   |                   |                            |
| Number of poles                              | 16   |                   |                            |
| L1 in mm                                     | 76.2 mm  |                   |                            |
| L1 in inches                                 | 3 "  |                   |                            |
| Number of rows                               | 1  |                   |                            |
| Pin series quantity                          | 1  |                   |                            |
| Touch-safe protection acc. to DIN VDE 57 106 | finger-safe plugged/ back-of-hand-safe unplugged |                   |                            |
| Touch-safe protection acc. to DIN VDE 0470   | IP20 plugged/ IP10 unplugged                     |                   |                            |
| Protection degree                            | IP20, when fully mounted                         |                   |                            |
| Volume resistance                            | ≤5 mΩ  |                   |                            |
| Stripping length                             | 7 mm   |                   |                            |
| Screwdriver blade                            | 0.6 x 3.5  |                   |                            |
| Screwdriver blade standard                   | DIN 5264   |                   |                            |
| Plugging cycles                              | 25   |                   |                            |
| Tightening torque                            | Torque type                                      | Wire connection   |                            |
|  | Usage information                                | Tightening torque | min. 0.4 Nm<br>max. 0.5 Nm |

## Material data

|                                  |                            |                             |        |
|----------------------------------|----------------------------|-----------------------------|--------|
| Insulating material              | PBT                        | Colour                      | orange |
| Colour chart (similar)           | RAL 2000                   | Insulating material group   | IIIa   |
| Comparative Tracking Index (CTI) | ≥ 200                      | UL 94 flammability rating   | V-0    |
| Contact material                 | Cu-alloy                   | Contact surface             | tinned |
| Layer structure of plug contact  | 4...8 µm Sn hot-dip tinned | Storage temperature, min.   | -40 °C |
| Storage temperature, max.        | 70 °C                      | Operating temperature, min. | -50 °C |
| Operating temperature, max.      | 100 °C                     |                             |        |

## Conductors suitable for connection

|   |                      |
|---|----------------------|
| Clamping range, min.                    | 0.13 mm <sup>2</sup> |
| Clamping range, max.                    | 3.31 mm <sup>2</sup> |
| Wire connection cross section AWG, min. | AWG 26               |
| Wire connection cross section AWG, max. | AWG 12               |
| Solid, min. H05(07) V-U                 | 0.2 mm <sup>2</sup>  |
| Solid, max. H05(07) V-U                 | 2.5 mm <sup>2</sup>  |
| Stranded, min. H07V-R                   | 0.2 mm <sup>2</sup>  |
| Stranded, max. H07V-R                   | 2.5 mm <sup>2</sup>  |
| Flexible, min. H05(07) V-K              | 0.2 mm <sup>2</sup>  |
| Flexible, max. H05(07) V-K              | 2.5 mm <sup>2</sup>  |

Creation date July 3, 2025 10:41:16 PM CEST

## SLS 5.08/16/180TB RF15 SN OR BX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

w. plastic collar ferrule, DIN 46228 pt 4, 0.2 mm<sup>2</sup>  
min.w. plastic collar ferrule, DIN 46228 pt 4, 2.5 mm<sup>2</sup>  
max.w. wire end ferrule, DIN 46228 pt 1, 0.2 mm<sup>2</sup>  
min.w. wire end ferrule, DIN 46228 pt 1, 2.5 mm<sup>2</sup>  
max.

|                     |  |                              |                         |      |
|---------------------|--|------------------------------|-------------------------|------|
| Clampable conductor | Cross-section for conductor connection | Type                         | fine-wired              |      |
|                     |  | nominal                      | 0.5 mm <sup>2</sup>     |      |
|                     | wire end ferrule                       | Stripping length             | nominal                 | 6 mm |
|                     |  | Recommended wire-end ferrule | <a href="#">H0.5/6</a>  |      |
|                     | Cross-section for conductor connection | Type                         | fine-wired              |      |
|                     |  | nominal                      | 1 mm <sup>2</sup>       |      |
|                     | wire end ferrule                       | Stripping length             | nominal                 | 6 mm |
|                     |  | Recommended wire-end ferrule | <a href="#">H1.0/6</a>  |      |
|                     | Cross-section for conductor connection | Type                         | fine-wired              |      |
|                     |  | nominal                      | 1.5 mm <sup>2</sup>     |      |
|                     | wire end ferrule                       | Stripping length             | nominal                 | 7 mm |
|                     |  | Recommended wire-end ferrule | <a href="#">H1.5/7</a>  |      |
|                     | Cross-section for conductor connection | Type                         | fine-wired              |      |
|                     |  | nominal                      | 2.5 mm <sup>2</sup>     |      |
|                     | wire end ferrule                       | Stripping length             | nominal                 | 7 mm |
|                     |  | Recommended wire-end ferrule | <a href="#">H2.5/7</a>  |      |
|                     | Cross-section for conductor connection | Type                         | fine-wired              |      |
|                     |  | nominal                      | 0.75 mm <sup>2</sup>    |      |
|                     | wire end ferrule                       | Stripping length             | nominal                 | 6 mm |
|                     |  | Recommended wire-end ferrule | <a href="#">H0.75/6</a> |      |

Reference text The outside diameter of the plastic collar should not be larger than the pitch (P). Length of ferrules is to be chosen depending on the product and the rated voltage.

## Rated data acc. to IEC

|   |                        |   |        |
|---|------------------------|---|--------|
| tested acc. to standard   | IEC 60664-1, IEC 61984 | Rated current, min. number of poles (Tu=20°C)                         | 21.5 A |
| Rated current, max. number of poles (Tu=20°C)                             | 16 A                   | Rated current, min. number of poles (Tu=40°C)                         | 18 A   |
| Rated current, max. number of poles (Tu=40°C)                             | 14 A                   | Rated voltage for surge voltage class / pollution degree II/2         | 400 V  |
| Rated voltage for surge voltage class / pollution degree III/2            | 320 V                  | Rated voltage for surge voltage class / pollution degree III/3        | 250 V  |
| Rated impulse voltage for surge voltage class/ pollution degree II/2      | 4 kV                   | Rated impulse voltage for surge voltage class/ pollution degree III/2 | 4 kV   |
| Rated impulse voltage for surge voltage class/ contamination degree III/3 | 4 kV                   |   |        |

## Rated data acc. to CSA

|                                   |        |                                   |        |
|-----------------------------------|--------|-----------------------------------|--------|
| Rated voltage (Use group B / CSA) | 300 V  | Rated voltage (Use group D / CSA) | 300 V  |
| Rated current (Use group B / CSA) | 15 A   | Rated current (Use group D / CSA) | 10 A   |
| Wire cross-section, AWG, min.     | AWG 26 | Wire cross-section, AWG, max.     | AWG 12 |

**SLS 5.08/16/180TB RF15 SN OR BX****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Rated data acc. to UL 1059**

Institute (UR)



Certificate No. (UR)

E60693

Rated voltage (Use group B / UL 1059) 300 V

Rated voltage (Use group D / UL 1059) 300 V

Rated current (Use group B / UL 1059) 14 A

Rated current (Use group D / UL 1059) 10 A

Wire cross-section, AWG, min. AWG 26

Wire cross-section, AWG, max. AWG 12

Reference to approval values  
Specifications are maximum values, details - see approval certificate.**Packing**

Packaging

Box

VPE length

127 mm

VPE width

119 mm

VPE height

50 mm

**Classifications**

ETIM 6.0

EC002638

ETIM 7.0

EC002638

ETIM 8.0

EC002638

ETIM 9.0

EC002638

ETIM 10.0

EC002638

ECLASS 9.0

27-44-03-09

ECLASS 9.1

27-44-03-09

ECLASS 10.0

27-44-03-09

ECLASS 11.0

27-46-02-02

ECLASS 12.0

27-46-02-02

ECLASS 13.0

27-46-02-02

ECLASS 14.0

27-46-02-02

ECLASS 15.0

27-46-02-02

**Approvals**

Approvals



Approvals MAMID

[https://mdcop.weidmueller.com/mediadelivery/rendition/900\\_319262/-T1z1mm-S800/](https://mdcop.weidmueller.com/mediadelivery/rendition/900_319262/-T1z1mm-S800/)

ROHS

Conform

UL File Number Search

UL Website

Certificate No. (UR)

E60693

**Environmental Product Compliance**

RoHS Compliance Status

Compliant without exemption

REACH SVHC

No SVHC above 0.1 wt%

**SLS 5.08/16/180TB RF15 SN OR BX****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Important note**

|                |  |
|----------------|--|
| IPC conformity | Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request.   |
| Notes          | <ul style="list-style-type: none"> <li>• Additional variants on request</li> <li>• Rated current related to rated cross-section &amp; min. No. of poles.</li> <li>• Wire end ferrule without plastic collar to DIN 46228/1</li> <li>• Wire end ferrule with plastic collar to DIN 46228/4</li> <li>• P on drawing = pitch</li> <li>• Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards.</li> <li>• In accordance with IEC 61984, OMNIMATE-connectors are connectors without breaking capacity (COC). During designated use, connectors are not allowed to be engaged or disengaged when live or under load</li> <li>• Long term storage of the product with average temperature of 50 °C and maximum humidity 70%, 36 months</li> </ul> |

**Downloads**

|   |  |
|---|--|
| Approval/Certificate/Document of Conformity | <a href="#">Declaration of the Manufacturer</a>  |
| Engineering Data                            | <a href="#">CAD data – STEP</a>  |
| Product Change Notification                 | <a href="#">20220502 Änderung der Geometrie des Rastfußes SLAS RF 15 OR 1665 (2093330000)</a><br><a href="#">20220502 Change of geometry rail mount SLAS RF 15 OR 1665 (2093330000)</a>  |
| Catalogues                                  | <a href="#">Catalogues in PDF-format</a>   |
| Brochures                                   | <a href="#">FL DRIVES EN</a><br><a href="#">MB DEVICE MANUF. EN</a><br><a href="#">FL DRIVES DE</a><br><a href="#">FL BUILDING SAFETY EN</a><br><a href="#">FL APPL LED LIGHTING EN</a><br><a href="#">FL INDUSTR.CONTROLS EN</a><br><a href="#">FL MACHINE SAFETY EN</a><br><a href="#">FL HEATING ELECTR EN</a><br><a href="#">FL APPL INVERTER EN</a><br><a href="#">FL_BASE_STATION_EN</a><br><a href="#">FL ELEVATOR EN</a><br><a href="#">FL POWER SUPPLY EN</a><br><a href="#">FL 72H SAMPLE SER EN</a><br><a href="#">PO OMNIMATE EN</a><br><a href="#">PO OMNIMATE EN</a> |


## SLS 5.08/16/180TB RF15 SN OR BX

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany


[www.weidmueller.com](http://www.weidmueller.com)

## Drawings


### Product image



### Dimensional drawing



### Graph



WEITERGABE SOWIE Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet.  
Zuwendungen verpflichten zu Schadenersatz. Alle Rechte für den Fall der Patent-, Gebrauchsmuster- oder Geschmacksuntertragung vorbehalten.  
THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT AS WELL AS THE COMMUNICATION OF ITS CONTENTS TO OTHERS WITHOUT EXPLICIT AUTHORIZATION IS PROHIBITED.  
OFFENDERS WILL BE HELD LIABLE FOR THE PAYMENT OF DAMAGES. WEIDMÜLLER EXCLUSIVELY RESERVES THE RIGHT TO FILE FOR PATENTS, UTILITY MODELS OR DESIGNS.

WEIDMÜLLER INTERFACE GmbH & Co.KG

Technical Data

Rev.

Material data

|  |                 |
|--|-----------------|
| Insulation material type               | PBT             |
| Insulation material colours            | see order sheet |
| Insulation material flammability class | UL94            |
| Insulation resistance                  | MOhm            |
| Contact base material                  | Cu-alloy        |
| Contact plating                        | tin-plated      |

System characteristic values

|   |                  |                             |
|---|------------------|-----------------------------|
|   | with counterpart | BLZ 5.08 180°               |
| Pitch P   | mm/inch          | 5.08/0.2                    |
| Number of rows  |                  | 1                           |
| Dielectric strength (r.m.s withstand voltage)                 | kV               | >2.21                       |
| Mechanical operating cycles                                   | acc. to IEC 512  | 25                          |
| Plug in force (max.)  | N/pole           | 10                          |
| Pull out force (max.)   | N/pole           | 8                           |
| Through resistance (typical)                                  | mOhm             | 3.2                         |
| Operating temperature range                                   | °C               | -55...+100                  |
| Degree of protection acc. to VDE 0106 (plugged/unplugged)     |                  | finger safe / back of hands |
| Degree of protection acc. to DIN EN 60529 (plugged/unplugged) |                  | IP20 / IP10                 |
| Conductor connection method                                   |                  | clamping yoke               |
| Screw size  |                  | M2.5                        |
| Screw torque max. acc. to EN 60999                            | Nm               | 0.4                         |
| Screw driver type   |                  | SD 0.6 x 3.5                |

Application notes

|                                |        |                 |
|--------------------------------|--------|-----------------|
| Coding possibility             | yes/no | yes (accessory) |
| Joinable without loss of pitch | yes/no | no              |
| Manual assembly of modules     | yes/no | no              |
| Max. number of poles           | n      | 24              |

Conductor

|   |                 |                 |
|---|-----------------|-----------------|
| Clamping range                              | mm <sup>2</sup> | 0.08...2.5      |
| "e" solid H05(07) V-U                       | mm <sup>2</sup> | 0.5...2.5       |
| "f" flexible H05(07) V-K                    | mm <sup>2</sup> | 0.5...2.5       |
| "f" with ferrule acc. to DIN 46228/1        | mm <sup>2</sup> | 0.5...2.5       |
| ... with plastic collar acc. to DIN 46228/4 | mm <sup>2</sup> | 0.5...1.5       |
| Conductor insulation stripping length       | mm/inch         | 7/0.276         |
| Conductor insulation diameter max.          | mm/inch         | n.a.            |
| Two wire clamping range                     | mm <sup>2</sup> | n.a.            |
| Gauge to EN 60999 (a x b ; Ø)               | mm              | 2.8 x 2.4 ; 2.4 |

IEC 664-1 / VDE0110 (4.97) rated data

|  |                  |                    |
|--|------------------|--------------------|
| Rated cross section acc. to EN 60999         | mm <sup>2</sup>  | 2.5                |
| Rated current @ 20°C ambient (together with) | A                | 21 (BLZ 5.08 180°) |
| Rated current @ 40°C ambient (together with) | A                | 18 (BLZ 5.08 180°) |
| Overvoltage category / Pollution degree      | III/3 III/2 II/2 |                    |
| Rated voltage                                | V                | 250 320 400        |
| Rated impulse voltage                        | kV               | 4.0 4.0 4.0        |

UL 1059 rated data



File No.: E60693

|  |   |                 |
|--|---|-----------------|
| Rated voltage                                  | V | B 300 C - D 300 |
| Rated current                                  | A | 15 - 10         |
| AWG wire range (field wiring / factory wiring) |   | 26...12         |

CSA C22.2 rated data



File No.: LR12400

|  |   |                 |
|--|---|-----------------|
| Rated voltage                                  | V | B 300 C - D 300 |
| Rated current                                  | A | 14 - 10         |
| AWG wire range (field wiring / factory wiring) |   | 26...12         |

Packaging

carton

Downloads

www.weidmueller.de





- Without locking latches
- Sum of ambient temperature and temperature rise
- Referred to rated cross section and minimum pole number

n.a. = not applicable

Subject to technical changes

For the mounting of PCBs, it should be noted that the rated data stated here relates only to the PCB components alone.  
The necessary creepage and clearance paths must be observed in connection with the respective applicant in accordance to IEC 664 / VDE 0110.  
The current-carrying capacity and pitch tolerance is to be determined according to DIN IEC 326 part 3 very fine.

Weidmüller PCB components are tested to the DIN EN 61984 standard, and are valid for its field of application.  
Provided that the components are used to the intended purpose, all requirements with respect to the occurring of electrical, mechanical, thermic and corrosive stress will be satisfied.



1/1

SHOWN:SLS 5.08/4TB RF15

|   |                                 |                               |
|---|---------------------------------|-------------------------------|
| METRIC TOLERANCES:<br>X. = ±0.3<br>X.X = ±0.1<br>X.XX = ±0.05 | 40262/0<br>14.05.08 HELIS_MA 00 | CAT.NO.:<br><b>C 34203 02</b> |
| MODIFICATION  | DATE                            | NAME                          |
| DRAWN   | 16.05.2008                      | HECKERT_M                     |
| RESPONSIBLE   |                                 | HERTEL_S                      |
| CHECKED   | 16.05.2008                      | HECKERT_M                     |
| APPROVED  |                                 | HECKERT_M                     |
| SCALE: 2/1<br>SUPERSEDES: 4 34203/01                          |                                 | PRODUCT FILE: SLS 5.08        |

Weidmüller

SLS 5.08TB RF15  
STIFTFLEISTE  
PIN HEADER