


ESG 6/15 K MC NE GE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration



ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from manufacturers like Siemens, ABB, Beckhoff etc.

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| | |
|--------------------|--|
| Version | ESG, Device markers x 15 mm, PA 66, Colour: yellow, Self-adhesive |
| Order No. | 1880130000 |
| Type | ESG 6/15 K MC NE GE |
| GTIN (EAN) | 4032248478910 |
| Qty. | 200 pc(s). |
| compatible printer | 2715590000 2438520000 2438510000 |

ESG 6/15 K MC NE GE

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|---------|-----------------|------------|
| Depth | 1 mm | Depth (inches) | 0.039 inch |
| Height | 6 mm | Height (inches) | 0.236 inch |
| Width | 15 mm | Width (inches) | 0.591 inch |
| Net weight | 0.485 g | | |

Temperatures

| | |
|-----------------------------|-------------|
| Operating temperature range | -40...60 °C |
|-----------------------------|-------------|

General data

| | | | |
|--|------------------------------|-----------|--|
| Adhesive | Double-sided adhesive tape | | |
| Application/manufacturer | Self-adhesive | | |
| Colour | yellow | | |
| Halogen | No | | |
| Material | PA 66 | | |
| Material colour according to resistance code | 4 | | |
| Number of markers per combination | 1 MultiCard = Device markers | | |
| Number of markers per packaging unit | Form of supply | MultiCard | |
| Operating temperature range | -40...60 °C | | |
| Operating temperature range, max. | 60 °C | | |
| Operating temperature range, min. | -40 °C | | |
| UL 94 flammability rating | V-2 | | |
| Version | Self-adhesive | | |
| Width | 15 mm | | |

Device markers

| | |
|---------|----|
| Halogen | No |
|---------|----|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001288 | ETIM 7.0 | EC001288 |
| ETIM 8.0 | EC001288 | ETIM 9.0 | EC001288 |
| ECLASS 9.0 | 27-40-06-29 | ECLASS 9.1 | 27-40-06-29 |
| ECLASS 10.0 | 27-40-06-29 | ECLASS 11.0 | 27-28-11-04 |
| ECLASS 12.0 | 27-28-11-04 | ECLASS 13.0 | 27-28-11-04 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|-----------------------------|--|
| Engineering Data | CAD data – STEP |
| Product Change Notification | MultiCard Material modification MultiCard Material Modifikation |
| Catalogues | Catalogues in PDF-format |

ESG 6/15 K MC NE GE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

