

VT SF 0/12 MC SDR V0**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

SlimFix are conductor and cable markers with a space-saving design. The markers can be fitted even after the conductor has been installed. They consist of halogen-free material and comply with flammability rating V0/V2. SlimFix is an acknowledged and accredited marker type for traffic engineering applications. The SF tool allows easy installation, even in case of small markers.

Advantages:

- Halogen-free material
- Flammability rating V0/V2
- Approved and accredited markers for traffic engineering applications, etc.
- Has to be fixed with cable ties if the conductor cross-section is larger than 16.0 mm²
- Markers in proven MultiCard format

General ordering data

Version	SlimFix, Conductor and cable markers, 1.2 - 1.6 mm, 12 x 3.2 mm, To customer specification
Order No.	1906830000
Type	VT SF 0/12 MC SDR V0
GTIN (EAN)	4032248529223
Qty.	80 pc(s).
Alternative product	1919250000
compatible printer	2715590000 2438520000 2438510000

VT SF 0/12 MC SDR V0

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	3.2 mm	Depth (inches)	0.126 inch
Height	12 mm	Height (inches)	0.472 inch
Width	3.2 mm	Width (inches)	0.126 inch
Net weight	0.16 g		

Temperatures

Operating temperature range	-50...120 °C
-----------------------------	--------------

General data

Advice label	Colour based on customer requirements (Please send M-Print PRO file)	
Colour	To customer specification	
Colour of printing	black	
Halogen	No	
Material	Polyamide 66	
Number of markers per combination	1 MultiCard = Conductor and cable markers	
Number of markers per packaging unit	Form of supply	MultiCard
Operating temperature range	-50... 120 °C	
Operating temperature range, max.	120 °C	
Operating temperature range, min.	-50 °C	
Orientation of print	horizontal	
Printed characters	Based on customer requirements (Please send M-Print PRO file)	
Printing method	MC Laser	
Size of labelling field	12 x 3.2 mm	
Type of printing	To customer specification	
UL 94 flammability rating	V-0	
Width	3.2 mm	

Conductor and cable markers

Conductor O.D.	1.2 - 1.6 mm	Conductor O.D., max.	1.6 mm
Conductor O.D., min.	1.2 mm	Conductor cross-section, max.	0.5 mm ²
Conductor cross-section, min.	0.25 mm ²	Cross-section for connected wire	0.25 - 0.5 mm ²
Halogen	No		

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ECLASS 9.0	27-40-04-01	ECLASS 9.1	27-40-04-01
ECLASS 10.0	27-40-04-01	ECLASS 11.0	27-28-11-02
ECLASS 12.0	27-28-11-02	ECLASS 13.0	27-28-11-02

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--