

VG H M20 MS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications.

The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure.

Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

General ordering data

Version	VG H (HDC halved cable gland), Cable glands, straight, M 20, 7.5 mm, OD min. 4 - OD max. 13 mm, IP65, Brass, nickel-plated
Order No.	1921720000
Type	VG H M20 MS
GTIN (EAN)	4032248562909
Qty.	50 pc(s).

VG H M20 MS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Height	10.5 mm	Height (inches)	0.413 inch
Width	20 mm	Width (inches)	0.787 inch
Net weight	12.56 g		

Temperatures

Operating temperature	-20 °C...60 °C
-----------------------	----------------

General information

AF size	20 mm	AF size 1	20 mm
AF size 2	20 mm	Cable glands	metric, M 20
External thread	M 20	Halogen	Yes
Length of thread	7.5 mm	Material	Brass, nickel-plated
Notch multi-layer sealing diameter 1	4 mm	Notch multi-layer sealing diameter 2	7 mm
Notch multi-layer sealing diameter 3	10 mm	Notch multi-layer sealing diameter 4	13 mm
O-Ring	NBR	Operating temperature range, max.	60 °C
Operating temperature range, min.	-20 °C	Outer cable diameter, max.	13 mm
Outer cable diameter, min.	4 mm	Pitch of thread	1.5 mm
Protection degree	IP65	Protection degree with GWDR	IP65
Seal insert	NBR	Sealing	NBR

Classifications

ETIM 6.0	EC000441	ETIM 7.0	EC000441
ETIM 8.0	EC000441	ETIM 9.0	EC000441
ECLASS 9.0	27-14-44-32	ECLASS 9.1	27-14-44-32
ECLASS 10.0	27-14-44-32	ECLASS 11.0	27-14-44-32
ECLASS 12.0	27-14-08-01	ECLASS 13.0	27-14-08-01

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	b5ff1f66-ddba-4739-9fc0-0521ddb52139

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
Brochures	