

SF 3/12 MC NE WS V2**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

SlimFix are conductor and cable markers with a space-saving design. The markers can be fitted even after the conductor has been installed. They consist of halogen-free material and comply with flammability rating V0/V2. SlimFix is an acknowledged and accredited marker type for traffic engineering applications. The SF tool allows easy installation, even in case of small markers.

Advantages:

- Halogen-free material
- Flammability rating V0/V2
- Approved and accredited markers for traffic engineering applications, etc.
- Has to be fixed with cable ties if the conductor cross-section is larger than 16.0 mm²
- Markers in proven MultiCard format

General ordering data

Version	SlimFix, Conductor and cable markers, 3 - 3.7 mm, 12 x 4.6 mm, white
Order No.	1919540000
Type	SF 3/12 MC NE WS V2
GTIN (EAN)	4032248555833
Qty.	320 pc(s).
compatible printer	2715590000 2438520000 2438510000

SF 3/12 MC NE WS V2

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	4.8 mm	Depth (inches)	0.189 inch
Height	12 mm	Height (inches)	0.472 inch
Width	4.6 mm	Width (inches)	0.181 inch
Net weight	0.322 g		

Temperatures

Operating temperature range	-40...100 °C
-----------------------------	--------------

General data

Colour	white
Halogen	No
Material	Polyamide 66
Material colour according to resistance code	9
Number of markers per combination	1 MultiCard = Conductor and cable markers
Number of markers per packaging unit	Form of supply MultiCard
Operating temperature range	-40...100 °C
Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C
Recommended industries	Transportation, Machinery
Size of labelling field	12 x 4.6 mm
Type of printing	neutral
UL 94 flammability rating	V-2
Width	4.6 mm

Conductor and cable markers

Conductor O.D.	3 - 3.7 mm	Conductor O.D., max.	3.7 mm
Conductor O.D., min.	3 mm	Conductor cross-section, max.	2.5 mm ²
Conductor cross-section, min.	1.5 mm ²	Cross-section for connected wire	1.5 - 2.5 mm ²
Halogen	No		

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ECLASS 9.0	27-40-04-01	ECLASS 9.1	27-40-04-01
ECLASS 10.0	27-40-04-01	ECLASS 11.0	27-28-11-02
ECLASS 12.0	27-28-11-02	ECLASS 13.0	27-28-11-02

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Engineering Data	Zuken E3.S
Product Change Notification	Technical change to MultiCard material - DE Technical change to MultiCard material - EN MultiCard Material modification MultiCard Material Modifikation
Catalogues	Catalogues in PDF-format

Creation date April 28, 2024 9:41:46 PM CEST

Catalogue status 20.04.2024 / We reserve the right to make technical changes.

SF 3/12 MC NE WS V2

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

