

IE-USB-A-A-1.8M

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Assembled IE cables

General ordering data

Version	USB cable, USB A, USB A, PVC, 1.8 m
Order No.	1993550018
Type	IE-USB-A-A-1.8M
GTIN (EAN)	4050118378641
Qty.	1 pc(s).

IE-USB-A-A-1.8M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Length	1.8 m	Length (inches)	70.866 inch
Net weight	53 g		

Temperatures

Operating temperature	-15 °C...80
-----------------------	-------------

Technical specifications for cable

Sheathing colour	black
------------------	-------

General technical data

Contact surface	Gold over nickel
-----------------	------------------

Cable structure

Cross-section	2*AWG28 + 2*AWG24	Material sheath	PVC
Sheath diameter	4.5 mm	Sheath diameter, max.	4.7 mm
Sheath diameter, min.	4.3 mm	Sheathing colour	black

Plug

Plug left	USB A, IP20, male contact, straight, plug, Plastic, shielded	Plug right	USB A, IP20, male contact, straight, plug, Plastic, shielded
-----------	--	------------	--

Plug, left

Contact surface, plug, left	Gold over nickel	Plug left	USB A, IP20, male contact, straight, plug, Plastic, shielded
-----------------------------	------------------	-----------	--

Plug, right

Contact surface	Gold over nickel	Plug right	USB A, IP20, male contact, straight, plug, Plastic, shielded
-----------------	------------------	------------	--

Classifications

ETIM 6.0	EC001408	ETIM 7.0	EC001408
ETIM 8.0	EC001408	ETIM 9.0	EC001408
ECLASS 9.0	27-06-20-11	ECLASS 9.1	27-06-90-90
ECLASS 10.0	27-06-01-06	ECLASS 11.0	27-06-01-06
ECLASS 12.0	27-06-01-06	ECLASS 13.0	27-06-01-06

Approvals

ROHS	Conform
------	---------

IE-USB-A-A-1.8M

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN PI PROFINET CABLING EN PI PROFINET CABLING EN