

VPU I 3+1 280V/25KA**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

Weidmüller VPU I (Type I), VPU II (Type II) and VPU III (Type III) surge protection products effectively reduce the interference coupling that can occur due to transient surge voltages, even significantly below the limits prescribed by insulation co-ordination according to EN 60664-3 / DIN VDE 0110-3. This means that the whole installation is exposed to fewer malfunctions. The arresters are co-ordinated using technical means. This means that decoupling between Types I, II and III is unnecessary. The arresters are tested according to product standard IEC 61643-11 / DIN EN 61643-11 and can be installed in systems according to IEC 61643-12 / VDE 0675-6-12 and IEC 62305-4 / VDE 0185-4. This lightning and surge protection device is suited for installation in power supply systems. Weidmüller offers different products depending on the particular mains network type and voltage level. A special Type I and Type II protective device is even available for photovoltaic applications.

General ordering data

Version	Surge voltage arrester, Low voltage, without telecomm. contact, TN-C-S, TN-S, IT without N, TT
Order No.	2063080000
Type	VPU I 3+1 280V/25KA
GTIN (EAN)	4050118414714
Qty.	1 pc(s).
Delivery status	This article will no longer be available in the future.
Available until	2024-03-31
Alternative product	2726760000
Replacement parts	2067650000 1351940000

VPU I 3+1 280V/25KA

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	69 mm	Depth (inches)	2.717 inch
Height	94 mm	Height (inches)	3.701 inch
Width	142.4 mm	Width (inches)	5.606 inch
Mounting dimension - height	75 mm	Net weight	1,150 g

Temperatures

Storage temperature	-40 °C...80 °C	Operating temperature	-40 °C...70 °C
Humidity	5 - 95% rel. humidity		

General data

Colour	black, orange, blue	Design	Installation housing; 8 TE, Insta IP 20
Operating altitude	≤ 2000 m	Optical function display	green = OK; red = arrester is defective - replace
Protection degree	IP20	Rail	TS 35
Segment	Power distribution	UL 94 flammability rating	V-0
Version	without telecomm. contact		

Insulation coordination acc. to EN 50178

Pollution severity	2	Surge voltage category	IV
--------------------	---	------------------------	----

Rated data IEC / EN

Discharge current I_{\max} (8/20 μ s) N-PE	100 kA	Discharge current I_{\max} (8/20 μ s) wire-PE	100 kA
Discharge current I_n (8/20 μ s) N-PE	100 kA	Discharge current I_n (8/20 μ s) wire-PE	25 kA
Energy coordination (≤10 m)	Type I, Type II, Type III	Follow-on current extinguishing capability I_{fi}	Not available due for technical reasons
Fuse	No Fuse necessary ≤250 A gG, 250 A gL (if back up fuse > 250 A)	Leakage current at U_n	100 μ A
Lightning test current I_{imp} (10/350 μ s) (L-PE)	25 kA	Lightning test current, I_{imp} (10/350 μ s) (N-PE)	100 kA
Low voltage network	TN-C-S, TN-S, IT without N, TT	Mains voltage	230 V / 400 V
Max. continuous voltage, U_c (AC)	280 V	Max. continuous voltage, U_c (N-PE)	260 V
Number of poles	4	Protection level U_p at I_N (L/N-PE)	≤ 1.4 kV
Protection level U_p at I_N (N-PE)	≤ 1.6 kV	Rated load current I_L	100 A
Rated voltage (AC)	230 V	Requirements category acc. to IEC 61643-11	Type I, Type II
Requirements class, acc. to EN 61643-11	T1, T2	Response time	≤ 25 ns
Short-circuit current rating I_{SCCR}	25 kA	Signalling contact	No
Standards	IEC61643-11, EN61643-11	Temporary surge voltage (over-voltage) - TOV	438 V
Voltage type	AC		

VPU I 3+1 280V/25KA

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Connection data

Stripping length	15 mm	Type of connection	Screw connection
Stripping length, rated connection	15 mm	Tightening torque, min.	2 Nm
Tightening torque, max.	3 Nm	Clamping range, rated connection	16 mm ²
Clamping range, min.	4 mm ²	Clamping range, max.	35 mm ²
Wire cross-section, solid, min.	2.5 mm ²	Wire cross-section, solid, max.	16 mm ²
Wire connection cross section, finely stranded, min.	2.5 mm ²	Wire connection cross section, finely stranded, max.	25 mm ²
Conductor cross-section, flexible, AEH (DIN 46228-1), min.	2.5 mm ²	Conductor cross-section, flexible, AEH (DIN 46228-1), max.	50 mm ²
Connection cross-section, stranded, min.	2.5 mm ²	Connection cross-section, stranded, max.	50 mm ²

Classifications

ETIM 6.0	EC000941	ETIM 7.0	EC000941
ETIM 8.0	EC000941	ETIM 9.0	EC000941
ECLASS 9.0	27-13-08-05	ECLASS 9.1	27-13-08-05
ECLASS 10.0	27-13-08-05	ECLASS 11.0	27-13-08-05
ECLASS 12.0	27-17-90-90	ECLASS 13.0	27-17-90-90

Important note

Product information	Only applicable to IT power systems where the earth on the distribution transformer is interconnected with the earth on the consumer side (RE=RA in Figure 44.A1 of IEC 60634-4-44:2018).
---------------------	---

Approvals

Approvals



ROHS

Conform

Downloads

Approval/Certificate/Document of Conformity	EU_Konformitätserklärung / EU_Declaration_of_Conformity
Engineering Data	CAD data – STEP
User Documentation	Beipackzettel / Instruction sheet
Catalogues	Catalogues in PDF-format
Brochures	


VPU I 3+1 280V/25KA

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Electric symbol



Schematic circuit diagram