

**ZQV 2.5N/20 RD****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

The plug-in cross-connections feature easy handling and quick installation. This saves a great deal of time during installation in comparison with screwed solutions.

**General ordering data**

|            |   |
|------------|---|
| Version    | Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 20, Pitch in mm (P): 5.10, Insulated: Yes, Width: 102 mm |
| Order No.  | <a href="#">2108920000</a>  |
| Type       | ZQV 2.5N/20 RD  |
| GTIN (EAN) | 4050118485899   |
| Qty.       | 20 pc(s).   |

**ZQV 2.5N/20 RD****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 24.7 mm | Depth (inches)  | 0.972 inch |
| Height     | 2.8 mm  | Height (inches) | 0.11 inch  |
| Width      | 102 mm  | Width (inches)  | 4.016 inch |
| Net weight | 11.95 g |                 |            |

**Temperatures**

|                     |                |
|---------------------|----------------|
| Storage temperature | -25 °C...55 °C |
|---------------------|----------------|

**Material data**

|                           |       |        |     |
|---------------------------|-------|--------|-----|
| Material                  | Wemid | Colour | red |
| UL 94 flammability rating | V-0   |        |     |

**Additional technical data**

|                          |                 |                |         |
|--------------------------|-----------------|----------------|---------|
| Explosion-tested version | No              | Type of fixing | Plugged |
| Type of mounting         | Direct mounting |                |         |

**Cross-connector**

|                                     |    |
|-------------------------------------|----|
| Number of cross-connected terminals | 20 |
|-------------------------------------|----|

**Dimensions**

|                 |        |
|-----------------|--------|
| Pitch in mm (P) | 5.1 mm |
|-----------------|--------|

**General**

|                 |    |
|-----------------|----|
| Number of poles | 20 |
|-----------------|----|

**Rating data**

|               |      |
|---------------|------|
| Rated current | 24 A |
|---------------|------|

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000489    | ETIM 7.0    | EC000489    |
| ETIM 8.0    | EC000489    | ETIM 9.0    | EC000489    |
| ECLASS 9.0  | 27-14-11-40 | ECLASS 9.1  | 27-14-11-40 |
| ECLASS 10.0 | 27-14-11-40 | ECLASS 11.0 | 27-14-11-40 |
| ECLASS 12.0 | 27-14-11-40 | ECLASS 13.0 | 27-25-03-03 |

**Environmental Product Compliance**

|                        |                             |
|------------------------|-----------------------------|
| REACH SVHC             | /                           |
| RoHS Compliance Status | Compliant without exemption |

**Important note**

|                     |   |
|---------------------|---|
| Product information | Due to stability and temperature reasons It is only possible to break out 60% of contact elements The usage of cross connectors reduces the rated voltage to 400VThe voltage reduced to 25V if cut cross connection with blank cut edges are used |
|---------------------|---|

**ZQV 2.5N/20 RD****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|   |  |
|---|--|
| Approval/Certificate/Document of Conformity | <a href="#">Confirmation of Standards EN 45545-2_2020-10</a> |
|---|--|

|                  |                                 |
|------------------|---------------------------------|
| Engineering Data | <a href="#">CAD data – STEP</a> |
|------------------|---------------------------------|

|                  |                            |
|------------------|----------------------------|
| Engineering Data | <a href="#">Zuken E3.S</a> |
|------------------|----------------------------|

|                    |   |
|--------------------|---|
| User Documentation | <a href="#">2434520000_BED-ANL.ZQV_A_REIHE.pdf</a><br><a href="#">StorageConditionsTerminalBlocks</a> |
|--------------------|---|

|            |  |
|------------|--|
| Catalogues | <a href="#">Catalogues in PDF-format</a> |
|------------|--|