

VG M20 EMV-4 MS 6-12**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration****Produktabbildung**

The increasing sensitivity of electronic components and the increasing electromagnetic interference frequencies require cable glands to play an important role in the shielding concept of a system. This type of EMC cable glands are made for shielding against interference frequencies, with a 360° screening connection. A Finger-locking seal provides superior cable retention & strain relief, next to it, the cable gland meets the mechanical requirements of EN 62444. Due to the patented design a very easy and fast assembly will be possible.

General ordering data

Version	VG EMV GEN 4 (EMC cable gland with clamping cage), Cable glands, straight, M 20, 6, OD min. 6 - OD max. 12 mm, IP54, IP66, IP67, IP68 - 5 bar (30 min.), IP69K, Brass, nickel-plated
Order No.	2435150000
Type	VG M20 EMV-4 MS 6-12
GTIN (EAN)	4050118446906
Qty.	50 pc(s).

VG M20 EMV-4 MS 6-12

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Height	32 mm	Height (inches)	1.26 inch
Length	38 mm	Length (inches)	1.496 inch
Net weight	0.044 g		

Temperatures

Operating temperature	-40 °C...100 °C
-----------------------	-----------------

Certificate numbers cable gland

Approval conditions	DNV, UL, cULus	Certificate no. cable gland (GERML-LOYD)	E-14047
---------------------	----------------	--	---------

General information

AF size	22 mm	AF size 1	22 mm
AF size 2	22 mm	Cable glands	metric, M 20
Clamp insert	Polyamide	External thread	M 20
Halogen	Yes	Length of thread	6 mm
Material	Brass, nickel-plated	O-Ring	NBR
Operating temperature range, max.	100 °C	Operating temperature range, min.	-40 °C
Outer cable diameter, max.	12 mm	Outer cable diameter, min.	6 mm
Pitch of thread	1.5 mm	Protection class (UL)	Type 4X
Protection degree	IP66, IP68 - 5 bar (30 min.), IP69K	Protection degree with GWDR	IP54, IP66, IP67, IP68 - 5 bar (30 min.), IP69K
Seal insert	CR	Sealing	NBR
Shield diameter, max.	10 mm	Shield diameter, min.	4.5 mm
Tightening torque	5.5 Nm	Torque for cap nut, max.	6.5 Nm
Torque for cap nut, min.	5.5 Nm	Torque for connecting adapter, max.	6.5 Nm
Torque for connecting adapter, min.	5.5 Nm		

Classifications

ETIM 6.0	EC000441	ETIM 7.0	EC000441
ETIM 8.0	EC000441	ETIM 9.0	EC000441
ECLASS 9.0	27-14-44-32	ECLASS 9.1	27-14-44-32
ECLASS 10.0	27-14-44-32	ECLASS 11.0	27-14-44-32
ECLASS 12.0	27-14-08-01	ECLASS 13.0	27-14-08-01

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	b5ff1f66-ddba-4739-9fc0-0521ddb52139

Approvals

ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	EU Declaration of Conformity - EMC brass nickel plated cable gland - DE PS2480 210608 004ISS00
Engineering Data	CAD data - STEP
Catalogues	Catalogues in PDF-format
Brochures	

Creation date May 21, 2024 1:01:13 PM CEST

VG M20 EMV-4 MS 6-12**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Brass nuts for EMC**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	SKMU EMV M20	Version
Order No.	1777630000	SKMU MS EMV (brass locknut - EMC), Locknut, M 20, 3.6 mm, Brass,
GTIN (EAN)	4032248157907	nickel-plated
Qty.	100 pc(s).	