

**BKP-16DO-SDV541-V0-S****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

The digital output interfaces via relay are used to isolate the field sensors from the card and/or to adapt the operation of the said elements to the voltage required by the DCS. The interfaces also support additional characteristics that provide many benefits such as:

- **Redundancy:** the interfaces have 2 50-pole (AKB) connectors for redundancy purposes.
- Many of the interfaces activate a relay to indicate if one of the two possible power sources has dropped below a value of approximately 12 V
- The cards can be mounted via tension clamp or screw connection.
- The input sensors can be connected in two ways: supplied with power directly from the card or directly from the field.

**General ordering data**

Version	2 x AKB (50P)
Order No.	<a href="#">2461730000</a>
Type	BKP-16DO-SDV541-V0-S
GTIN (EAN)	4050118476965
Qty.	1 pc(s).

**BKP-16DO-SDV541-V0-S****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Depth	125 mm	Depth (inches)	4.921 inch
Height	168 mm	Height (inches)	6.614 inch
Width	376 mm	Width (inches)	14.803 inch
Net weight	3,875 g		

**Temperatures**

Storage temperature	-40...85 °C	Operating temperature	-25...50 °C
---------------------	-------------	-----------------------	-------------

**General data**

Power supply fuse	2 A
-------------------	-----

**Connection data**

Connection on control side	2 x AKB (50P)	Connection supply	LP 5.08mm
Number of poles (control side)	50-pole plug		

**Ratings data output**

Relay type	SIL3
------------	------

**Insulation coordinates (EN50178)**

Rated input insulation voltage	50 V AC / 70 V DC	Rated output insulation voltage	< 300 V AC
Overvoltage category input/input	III	Overvoltage category input/output	III
Overvoltage category output/output	III	Pollution severity level	2
Pulse voltage test (1,2/50µs)	6 kV	Insulation test voltage AC	1.2 kV
Clearance input/output	≥ 5.5 mm	Clearance input/input	≥ 0.3 mm
Clearance output/output	≥ 5.5 mm		

**Connection field**

Clamping range, max.	2.5 mm <sup>2</sup>	Clamping range, min.	0.13 mm <sup>2</sup>
Flexible with sleeve, max.	2.5 mm <sup>2</sup>	Flexible with sleeve, min.	0.2 mm <sup>2</sup>
Flexible, max. H05(07) V-K	2.5 mm <sup>2</sup>	Flexible, min. H05(07) V-K	0.2 mm <sup>2</sup>
Max. wire cross-section, AWG	AWG 14	Min. wire cross-section, AWG	AWG 26
Solid, max. H05(07) V-U	2.5 mm <sup>2</sup>	Solid, min. H05(07) V-U	0.2 mm <sup>2</sup>
Stripping length	6 mm	Type of connection	Screw connection

**Supply connection**

Type of connection	Screw connection	Clamping range, min.	0.13 mm <sup>2</sup>
Clamping range, max.	6 mm <sup>2</sup>	Solid, min. H05(07) V-U	0.5 mm <sup>2</sup>
Solid, max. H05(07) V-U	6 mm <sup>2</sup>	Flexible, min. H05(07) V-K	0.5 mm <sup>2</sup>
Flexible, max. H05(07) V-K	4 mm <sup>2</sup>	Flexible with sleeve, max.	2.5 mm <sup>2</sup>
Flexible with sleeve, min.	2.5 mm <sup>2</sup>	Ferrule with plastic collar, max.	0.5 mm <sup>2</sup>
Wire cross-section, min. AWG	AWG 12	Wire cross-section, max. AWG	AWG 26
Tightening torque, min.	0.5 Nm	Tightening torque, max.	0.6 Nm
Stripping length	6 mm		

**BKP-16DO-SDV541-V0-S****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Classifications**

ETIM 6.0	EC002780	ETIM 7.0	EC002780
ETIM 8.0	EC002780	ETIM 9.0	EC002780
ECLASS 9.0	27-14-11-52	ECLASS 9.1	27-24-22-16
ECLASS 10.0	27-14-11-52	ECLASS 11.0	27-14-11-52
ECLASS 12.0	27-14-11-52	ECLASS 13.0	27-14-11-52

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
SCIP	372daba8-74bf-4b17-b456-421792bf2a85

**Approvals**

Approvals

**Downloads**


Approval/Certificate/Document of Conformity	<a href="#">Declaration of Conformity</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

## BKP-16DO-SDV541-V0-S

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings



## Derating curve safety output

