

**SAI-08L-VP12-3A-M08L-AND****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

SAI – logic module These devices allow the combination of signals by means of an AND or an OR gate. This function leads to a reduction in the amount of wiring. The required inputs to the PLC can be reduced by up to 6 inputs. This process therefore saves the amount of wiring and material in the field.

**General ordering data**

Version	with M12 outlet, M8, 30 V, , LED: Yes, LED initiator: Yes, Wiring type: AND
Order No.	<a href="#">2512820000</a>
Type	SAI-08L-VP12-3A-M08L-AND
GTIN (EAN)	4050118527919
Qty.	1 pc(s).

**SAI-08L-VP12-3A-M08L-AND****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Net weight	107.2 g
------------	---------

**Temperatures**

Operating temperature	-20 - 90°C
-----------------------	------------

**Connection data**

Distributor outlet	with M12 outlet	Tightening torque	M8: 0.5 - 0.6 Nm, M12: 0.8 - 1.2 Nm
--------------------	-----------------	-------------------	--

**Electrical data**

Rated voltage, min.	15 V	Rated voltage, max.	30 V
Rated voltage	24 V	Rated current	500 mA
Max. current-carrying capacity per slot	500 mA	Total current	2 A

**General technical data**

Logic function	and	Protection degree	IP67
Number of poles	3	Number of contact sockets	8
Connection thread	M8	Pollution severity	3
Fire behaviour	V-0	LED	Yes
LED initiator	Yes	LED colour for indicating operation	green
LED colour for I/O function	red, green		

**Material data**

Housing main material	PBT	Housing colour	black (similar to RAL 9005)
Screw socket	Nickel-plated CuZn	Contact material	Nickel-plated CuZn
Contact surface	Gold-plated	Contact carrier material	PBT (UL 94 V0)

**Technical data cable**

Number of poles	3
-----------------	---

**Classifications**

ETIM 6.0	EC002585	ETIM 7.0	EC003558
ETIM 8.0	EC003558	ETIM 9.0	EC003558
ECLASS 9.0	27-44-01-08	ECLASS 9.1	27-44-01-08
ECLASS 10.0	27-44-01-11	ECLASS 11.0	27-44-01-11
ECLASS 12.0	27-44-01-11	ECLASS 13.0	27-44-01-11

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
SCIP	22cbd99b-5f46-4c36-9938-bd61e241a9ab

## SAI-08L-VP12-3A-M08L-AND

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

# Technical data

## Approvals

Approvals



ROHS

Conform

## Downloads

Engineering Data

[CAD data – STEP](#)

Product Change Notification

[20211208 Technical change to SAI M8 Line Distribution Boxes](#)

[20211208 Technische Änderung zu SAI M8 Line Verteiler](#)

Catalogues

[Catalogues in PDF-format](#)


**SAI-08L-VP12-3A-M08L-AND**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany


www.weidmueller.com

## Drawings

### Detailed drawing




## Dimensioned drawing



Connection	Dimension L	Dimension R	B±0,1
8 times	139	7x13=91	132
4 times	87	3x13=39	80

## Wiring diagram



## Pole scheme

