

WIL-LWXXXX-6500D024-655SXX5.0BXXXXXXXXXX**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The WIL-LED lights family: Only 8mm (9.4mm with magnet) high LED lamp for 24V DC with very high luminous efficacy and high lifespan (greater 60 000h). Very robust construction, by full potting and metal housing - water-proof (IP67). Due to its 6500K light color (daylight) suitable for the various applications. Optionally easily connectable with M12 connection. Due to the low power consumption, a small enough power supply with 24V for operation.

General ordering data

| | |
|------------|--|
| Order No. | 2535880000 |
| Type | WIL-LWXXXX-6500D024-655SXX5.0BXXXXXXXXXX |
| GTIN (EAN) | 4050118547542 |
| Qty. | 1 pc(s). |

WIL-LWXXXX-6500D024-655SXX5.0BXXXXXXXXXX**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

| | | | |
|------------|--------|-----------------|-------------|
| Depth | 40 mm | Depth (inches) | 1.575 inch |
| Height | 8 mm | Height (inches) | 0.315 inch |
| Width | 655 mm | Width (inches) | 25.787 inch |
| Net weight | 450 g | | |

Temperatures

| | |
|-----------------------|------------|
| Operating temperature | -20 - 60°C |
|-----------------------|------------|

Cable technical specifications

| | | | |
|----------------|-----|--------------------|----------------------|
| Cable Material | PUR | Sheathing colour | black |
| Cable length | 5 m | Core cross-section | 0.34 mm ² |

Connection data

| | | | |
|-----------------|----------------|-------------------|---|
| Version | Cable end open | Connection thread | without |
| Number of poles | 2 | Wiring | Pin 4 (Strand: black) control white LED, Pin 3 (Strand: blue) |

Electric data

| | | | |
|---------------|---------|---------------|---------|
| Rated voltage | 24 V DC | Rated current | 0.957 A |
| Power | 23.0 W | Dimmable | Yes |

General technical data

| | | | |
|---------------------------------------|-------------|--|---------------------|
| Electronic equipment on rolling stock | No | Recommended class according to UL for use of an power supply | NEC Class 2 |
| Shape of the LED module | Rectangular | Type of connection | Pre-assembled cable |
| Number of LEDs | 126 | Light colour (CCT) | 6500K, White |
| Luminosity | 3,470 cd | Light current | 1,933 lm |
| Emitting angle | 40 ° | Illumination level | 666 lux |
| Operating life | 60.000 h | Type of mounting | Screw mounting |
| Drill hole spacing | 640 mm | Impact resistance | IK05 |
| Protection degree | IP67 | Efficiency class (according to EU Directive No. 874/2012) | G |

Material data

| | | | |
|-----------------------|-----------------------------|------------------------|--------|
| Housing main material | hard anodised aluminium | Encapsulation compound | PUR V0 |
| Material of end caps | Diecast zinc, nickel-plated | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000996 | ETIM 7.0 | EC000996 |
| ETIM 8.0 | EC000996 | ETIM 9.0 | EC000996 |
| ECLASS 9.1 | 27-11-06-35 | ECLASS 10.0 | 27-11-06-35 |
| ECLASS 11.0 | 27-11-06-35 | ECLASS 12.0 | 27-11-06-35 |
| ECLASS 13.0 | 27-11-06-35 | | |

Environmental Product Compliance

| | |
|---------------------------|---------|
| EPREL Registration number | 1323270 |
|---------------------------|---------|

Creation date May 4, 2024 2:56:09 PM CEST

Catalogue status 20.04.2024 / We reserve the right to make technical changes.

WIL-LWXXXX-6500D024-655SXX5.0BXXXXXXXXXX**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Approvals**

Approvals



| | |
|-------------------------|------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate no. (cULus) | E354496 |

Downloads

| | |
|--------------------|--|
| Engineering Data | CAD data – STEP |
| User Documentation | Designation key WIL Flyer WIL |
| Catalogues | Catalogues in PDF-format |


WIL-LWXXXX-6500D024-655SXX5.0BXXXXXXXXXX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Dimensioned drawing



WIL-LWXXXX-6500D024-655SXX5.0BXXXXXXXXXX

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings

