

**IE-FCI-PWB-ISR****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

FrontCom® Vario integrates multiple functions in only one single frame. The system is easy to install and you can select from a wide range of data, signal and power modules. In addition to being extremely compact, FrontCom® Vario offers a number of unique product features that will make your project planning and work activities secure, fast and future-proof. Furthermore, the FrontCom® Vario system has an attractive housing design that, by the way, offers highest impact-resistance and fully meets the requirements of IP 65 protection class.

**General ordering data**

Version	FrontCom, Insert Power large, Type H, Socket connector, ISR
Order No.	<a href="#">2531060000</a>
Type	IE-FCI-PWB-ISR
GTIN (EAN)	4050118541175
Qty.	1 pc(s).

## IE-FCI-PWB-ISR

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Net weight	36 g
------------	------

## Temperatures

Operating temperature	-5 °C...40 °C
-----------------------	---------------

## General data

Connector face	Type H	Insert type	Insert Power large
Protection degree	IP20		

## Clampable conductors

Conductor connection cross-section, extremely flexible with wire end ferrule	1.5 ... 1.5 mm <sup>2</sup>
--	-----------------------------

Conductor connection cross-section, extremely flexible with wire end ferrule	min.	1.5 mm <sup>2</sup>
	max.	1.5 mm <sup>2</sup>

Conductor connection cross-section, extremely flexible without wire end ferrule	...
---	-----

Conductor connection cross-section, flexible with wire end ferrule	1.5 ... 1.5 mm <sup>2</sup>
--	-----------------------------

Conductor connection cross-section, flexible with wire end ferrule	max.	1.5 mm <sup>2</sup>
	min.	1.5 mm <sup>2</sup>

Conductor connection cross-section, flexible without wire end ferrule	...
---	-----

Conductor connection cross-section, rigid	1.5 ... 2.5 mm <sup>2</sup>
---	-----------------------------

Conductor connection cross-section, rigid	min.	1.5 mm <sup>2</sup>
	max.	2.5 mm <sup>2</sup>

Stripping length	11 mm
------------------	-------

Type of connection	Screw connection
--------------------	------------------

## Technical data

Housing main material	PP	Rated current	16 A
Rated voltage (AC)	250 V		

## Classifications

ETIM 6.0	EC001121	ETIM 7.0	EC001121
ETIM 8.0	EC001121	ETIM 9.0	EC001121
ECLASS 9.0	27-44-03-90	ECLASS 9.1	27-18-90-90
ECLASS 10.0	27-44-03-90	ECLASS 11.0	27-44-03-90
ECLASS 12.0	27-18-28-92	ECLASS 13.0	27-18-28-92

## Approvals

ROHS	Conform
------	---------

## IE-FCI-PWB-ISR

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">Socket Insert Overview EN</a> <a href="#">Socket Insert Overview DE</a> <a href="#">Designation key / Type key</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>


## IE-FCI-PWB-ISR

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

**Dimensioned drawing**



**Dimensioned drawing**

