

**WIL-LWXXXX-6500D024-350SXX5.0BXXXXXXXXXX****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

The WIL-LED lights family: Only 8mm (9.4mm with magnet) high LED lamp for 24V DC with very high luminous efficacy and high lifespan (greater 60 000h). Very robust construction, by full potting and metal housing - water-proof (IP67). Due to its 6500K light color (daylight) suitable for the various applications. Optionally easily connectable with M12 connection. Due to the low power consumption, a small enough power supply with 24V for operation.

**General ordering data**

Order No.	<a href="#">2535820000</a>
Type	WIL-LWXXXX-6500D024-350SXX5.0BXXXXXXXXXX
GTIN (EAN)	4050118547481
Qty.	1 pc(s).

**WIL-LWXXXX-6500D024-350SXX5.0BXXXXXXXXXX****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Depth	40 mm	Depth (inches)	1.575 inch
Height	8 mm	Height (inches)	0.315 inch
Width	350 mm	Width (inches)	13.78 inch
Net weight	200 g		

**Temperatures**

Operating temperature	-20 - 60°C
-----------------------	------------

**Cable technical specifications**

Cable Material	PUR	Sheathing colour	black
Cable length	5 m	Core cross-section	0.34 mm <sup>2</sup>

**Connection data**

Version	Cable end open	Connection thread	without
Number of poles	2	Wiring	Pin 4 (Strand: black) control white LED, Pin 3 (Strand: blue)

**Electric data**

Rated voltage	24 V DC	Rated current	0.477 A
Power	11.5 W	Dimmable	Yes

**General technical data**

Electronic equipment on rolling stock	No	Recommended class according to UL for use of an power supply	NEC Class 2
Shape of the LED module	Rectangular	Type of connection	Pre-assembled cable
Number of LEDs	63	Light colour (CCT)	6500K, White
Luminosity	3,470 cd	Light current	958 lm
Emitting angle	40 °	Illumination level	330 lux
Operating life	60.000 h	Type of mounting	Screw mounting
Drill hole spacing	335 mm	Impact resistance	IK05
Protection degree	IP67	Efficiency class (according to EU Directive No. 874/2012)	G

**Material data**

Housing main material	hard anodised aluminium	Encapsulation compound	PUR V0
Material of end caps	Diecast zinc, nickel-plated		

**Classifications**

ETIM 6.0	EC000996	ETIM 7.0	EC000996
ETIM 8.0	EC000996	ETIM 9.0	EC000996
ECLASS 9.1	27-11-06-35	ECLASS 10.0	27-11-06-35
ECLASS 11.0	27-11-06-35	ECLASS 12.0	27-11-06-35
ECLASS 13.0	27-11-06-35		

**Environmental Product Compliance**

EPREL Registration number	1323206
---------------------------	---------

Creation date May 4, 2024 5:24:01 PM CEST

**WIL-LWXXXX-6500D024-350SXX5.0BXXXXXXXXXX****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Approvals**

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E354496

**Downloads**

Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">Designation key WIL</a> <a href="#">Flyer WIL</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>


**WIL-LWXXXX-6500D024-350SXX5.0BXXXXXXXXXX**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

## Dimensioned drawing



**WIL-LWXXXX-6500D024-350SXX5.0BXXXXXXXXXX**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

Drawings

