

WIL-LBXXXX-W450D024-240SXX0.3BM12GM12G**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

The WIL-LED lights family: Only 8mm (9.4mm with magnet) high LED lamp for 24V DC with very high luminous efficacy and high lifespan (greater 60 000h). Very robust construction, by full potting and metal housing - waterproof (IP67). Due to its blue light color suitable for special color effects- Optionally easily connectable with M12 connection. Due to the low power consumption, a small enough power supply with 24V for operation.

General ordering data

Order No.	2576970000
Type	WIL-LBXXXX- W450D024-240SXX0.3BM12GM12G
GTIN (EAN)	4050118611144
Qty.	1 pc(s).

WIL-LBXXX-W450D024-240SXX0.3BM12GM12G**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	40 mm	Depth (inches)	1.575 inch
Height	8 mm	Height (inches)	0.315 inch
Width	240 mm	Width (inches)	9.449 inch
Net weight	215 g		

Temperatures

Operating temperature	-20 - 60°C
-----------------------	------------

Cable technical specifications

Cable Material	PUR	Sheathing colour	black
Cable length	0.3 m	Core cross-section	0.34 mm ²

Connection data

Version	Male, straight - female, straight	Connection thread	M12 / M12
Coding	A-coded	Tightening torque	0.8 Nm
Wiring	Pin 4 (Strand: black) control white LED, Pin 3 (Strand: blue)		

Electric data

Rated voltage	24 V DC	Rated current	0.317 A
Power	7.6 W	Dimmable	Yes

General technical data

Electronic equipment on rolling stock	No	Recommended class according to UL for use of an power supply	NEC Class 2
Shape of the LED module	Rectangular	Type of connection	Pre-assembled cable
Number of LEDs	42	Light colour (CCT)	Blue
Light current	98 lm	Emitting angle	40 °
Spectral colour	445 - 460 nm	Illumination level	34 lux
Operating life	60.000 h	Type of mounting	Screw mounting
Drill hole spacing	225 mm	Impact resistance	IK05
Protection degree	IP67		

Material data

Housing main material	hard anodised aluminium	Encapsulation compound	PUR V0
Threaded ring material	PA	Material of end caps	Diecast zinc, nickel-plated

Classifications

ETIM 6.0	EC000996	ETIM 7.0	EC000996
ETIM 8.0	EC000996	ETIM 9.0	EC000996
ECLASS 9.1	27-11-06-35	ECLASS 10.0	27-11-06-35
ECLASS 11.0	27-11-06-35	ECLASS 12.0	27-11-06-35
ECLASS 13.0	27-11-06-35		

WIL-LBXXXX-W450D024-240SXX0.3BM12GM12G**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germanywww.weidmueller.com**Technical data****Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
SCIP	bf1e8170-69bb-4440-b3e0-4da351a9a3b0

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E354496

Downloads

Engineering Data	CAD data – STEP
User Documentation	Designation key WIL
Catalogues	Catalogues in PDF-format


WIL-LBXXXX-W450D024-240SXX0.3BM12GM12G

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings


Dimensioned drawing



Detailed drawing



Pole scheme



Detailed drawing

