


**VPU AC II O 300/50****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

In the event of a defective arrester, you can easily reorder this spare arrester, replace the defective arrester and thus restore protection.

**General ordering data**

Version	Spare arrester, Surge protection
Order No.	<a href="#">2591010000</a>
Type	VPU AC II O 300/50
GTIN (EAN)	4050118599923
Qty.	1 pc(s).

## VPU AC II O 300/50

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	64 mm	Depth (inches)	2.52 inch
Height	45 mm	Height (inches)	1.772 inch
Width	18 mm	Width (inches)	0.709 inch
Net weight	0.64 g		

## Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...85 °C
Humidity	5 - 95% rel. humidity		

## Rated data UL

Ambient temperature (operational), max. 85 °C		Rated Voltage $U_N$	240 V
VPR (L/N-PE)	900 V	MCOV (L/N-PE)	300 V
SCCR	150 kA	$I_n$	20 kA
Category	SPD TYPE 1CA	Ambient temperature (operational), min. -40 °C	
Certificate No. (cURus)	E354261	VPR (L-PE)	900 V
Voltage type	AC		

## General data

Colour	orange	Operating altitude	≤ 2000 m
Optical function display	green = OK; red = arrester is defective - replace	Protection degree	IP20 in installed state
Rail	TS 35	Segment	Power distribution
UL 94 flammability rating	V-0	Version	Surge protection

## Rated data IEC / EN

Combined pulse $U_{OC}$	6 kV	Discharge current (type III)	3 kA
Discharge current $I_{max}$ (8/20μs) wire-PE	50 kA	Energy coordination (≤10 m)	Type II, Type III
Follow-on current extinguishing capability $I_{fi}$	Follow current need not be taken into account	Frequency range, max.	60 Hz
Frequency range, min.	50 Hz	Leakage current at $U_n$	0.3 mA
Max. continuous voltage, $U_c$ (AC)	300 V	Number of poles	1
Protection level $U_p$ at $I_N$ (L/N-PE)	≤ 1.5 kV	Rated voltage (AC)	230 V
Requirements category acc. to IEC 61643-11	Type II/III, Type II, Type III	Requirements class, acc. to EN 61643-11	T2, T3
Response time	≤ 25 ns	SPD type	T2, T3
Standards	IEC61643-11, EN61643-11, UL 1449	Voltage type	AC

## Connection data

Type of connection	Plug-in connection
--------------------	--------------------

## Guarantee

Time interval	5 years
---------------	---------

## VPU AC II 0 300/50

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Classifications

ETIM 6.0	EC000941	ETIM 7.0	EC000941
ETIM 8.0	EC000941	ETIM 9.0	EC000941
ECLASS 9.0	27-13-08-05	ECLASS 9.1	27-13-08-05
ECLASS 10.0	27-13-08-05	ECLASS 11.0	27-13-08-05
ECLASS 12.0	27-17-90-90	ECLASS 13.0	27-17-90-90

## Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E354261

## Downloads

Approval/Certificate/Document of Conformity	<a href="#">EU Konformitätserklärung / EU Declaration of Conformity</a>
Engineering Data	<a href="#">CAD data – STEP</a>
Tender specification	<a href="#">Ausschreibungstext DE</a> <a href="#">Tenderspecification EN</a>
User Documentation	<a href="#">Beipackzettel / Instruction sheet</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

## VPU AC II 0 300/50

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

# Drawings

## Electric symbol



**VPU AC II 0 300/50****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Crosshead screwdriver Phillips**

VDE insulated crosshead screwdriver, for Phillips screws, SDIK PH DIN 7438, ISO 8764/2-PH, output to ISO 8764-PH, SoftFinish grip

**General ordering data**

Type	SDIK PH1 X 80	Version
Order No.	<a href="#">2749890000</a>	Screwdriver, Blade width (B): 1 mm, 80 mm, Blade thickness (A): 1
GTIN (EAN)	4050118897098	
Qty.	1 pc(s).	

**Slotted screwdriver**

VDE insulated slot-head screwdriver, SDI DIN 7437, ISO 2380/2, drive output acc. to DIN 5264, ISO 2380/1. SoftFinish grip

**General ordering data**

Type	SDIS 1.0X5.5X125	Version
Order No.	<a href="#">2749850000</a>	Screwdriver, Blade width (B): 5.5 mm, Blade length: 125 mm, Blade
GTIN (EAN)	4050118897050	thickness (A): 1 mm
Qty.	1 pc(s).	