


HS-FR 4.8-9.5/50 MM Y**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The heat-shrinkable sleeve is printable on 2 sides and can be used for marking and insulating cables and wires. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

General ordering data

| | |
|--------------------|---|
| Version | Conductor and cable markers, 4.8 - 9.5 mm, 49.8 x 15.1 mm, yellow |
| Order No. | 2621830000 |
| Type | HS-FR 4.8-9.5/50 MM Y |
| GTIN (EAN) | 4050118625219 |
| Qty. | 500 pc(s). |
| compatible printer | 2599430000 2599440000 |

HS-FR 4.8-9.5/50 MM Y**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

| | | | |
|------------|---------|-----------------|------------|
| Depth | 0.77 mm | Depth (inches) | 0.03 inch |
| Height | 49.8 mm | Height (inches) | 1.961 inch |
| Width | 15.1 mm | Width (inches) | 0.594 inch |
| Net weight | 1.166 g | | |

Temperatures

| | |
|-----------------------------|--------------|
| Operating temperature range | -55...125 °C |
|-----------------------------|--------------|

General data

| | | | |
|-----------------------------------|----------------|-----------------------------------|--------------|
| Colour | yellow | Halogen | No |
| Material | Polyolefine | Operating temperature range | -55...125 °C |
| Operating temperature range, max. | 125 °C | Operating temperature range, min. | -55 °C |
| Size of labelling field | 15.1 x 49.8 mm | Width | 15.1 mm |

Conductor and cable markers

| | | | |
|---|-------------------|---|------------------------|
| Conductor O.D. | 4.8 - 9.5 mm | Conductor O.D., max. | 9.5 mm |
| Conductor O.D., min. | 4.8 mm | Conductor cross-section, max. | 16 mm ² |
| Conductor cross-section, min. | 4 mm ² | Cross-section for connected wire | 4 - 16 mm ² |
| Halogen | No | Rate of shrinkage | 2:1 |
| Recommended shrinking temperature | 90 °C | Wire connection cross section AWG, max. | AWG 6 |
| Wire connection cross section AWG, min. | AWG 12 | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001530 | ETIM 7.0 | EC001530 |
| ETIM 8.0 | EC001530 | ETIM 9.0 | EC001530 |
| ECLASS 9.0 | 27-40-04-01 | ECLASS 9.1 | 27-40-04-01 |
| ECLASS 10.0 | 27-40-04-01 | ECLASS 11.0 | 27-28-11-02 |
| ECLASS 12.0 | 27-28-11-02 | ECLASS 13.0 | 27-28-11-02 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------|--|
| Catalogues | Catalogues in PDF-format |
|------------|--|

HS-FR 4.8-9.5/50 MM Y

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

