

**AAM 1.5 YE FLASH****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

Warning covers with a flash symbol provide more safety for man and machine. They are used where external voltage must be indicated within the application.

**General ordering data**

|            |  |
|------------|--|
| Version    | Terminal marker, 6.2 x 3.5 mm, Pitch in mm (P):<br>3.50 yellow |
| Order No.  | <a href="#">2635520000</a>                                     |
| Type       | AAM 1.5 YE FLASH   |
| GTIN (EAN) | 4050118674088  |
| Qty.       | 40 pc(s).  |

**AAM 1.5 YE FLASH****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

|            |        |                 |            |
|------------|--------|-----------------|------------|
| Depth      | 4.8 mm | Depth (inches)  | 0.189 inch |
| Height     | 6.2 mm | Height (inches) | 0.244 inch |
| Width      | 3.5 mm | Width (inches)  | 0.138 inch |
| Net weight | 0.05 g |                 |            |

**Temperatures**

|                             |              |
|-----------------------------|--------------|
| Operating temperature range | -40...100 °C |
|-----------------------------|--------------|

**Material data**

|                           |        |        |        |
|---------------------------|--------|--------|--------|
| Material                  | PA 6.6 | Colour | yellow |
| UL 94 flammability rating | V-2    |        |        |

**Rating data IECEx/ATEX**

|                             |              |
|-----------------------------|--------------|
| Operating temperature range | -40...100 °C |
|-----------------------------|--------------|

**Dimensions**

|                 |        |
|-----------------|--------|
| Pitch in mm (P) | 3.5 mm |
|-----------------|--------|

**General**

|                                   |        |                                   |        |
|-----------------------------------|--------|-----------------------------------|--------|
| Operating temperature range, max. | 100 °C | Operating temperature range, min. | -40 °C |
|-----------------------------------|--------|-----------------------------------|--------|

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000761    | ETIM 7.0    | EC000761    |
| ETIM 8.0    | EC000761    | ETIM 9.0    | EC000761    |
| ECLASS 9.0  | 27-14-11-37 | ECLASS 9.1  | 27-14-11-37 |
| ECLASS 10.0 | 27-14-11-37 | ECLASS 11.0 | 27-28-11-01 |
| ECLASS 12.0 | 27-28-11-01 | ECLASS 13.0 | 27-28-11-01 |

**Downloads**

|                  |  |
|------------------|--|
| Engineering Data | <a href="#">CAD data – STEP</a>          |
| Catalogues       | <a href="#">Catalogues in PDF-format</a> |