

HDC MHE 4 MP**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image****Flexible**

The four module sizes make for individual plug solutions that save a huge amount of space. The smaller pitch translates into an optimised design too.

General ordering data

| | |
|------------|----------------------------|
| Version | Signal module |
| Order No. | 2635980000 |
| Type | HDC MHE 4 MP |
| GTIN (EAN) | 4050118692785 |
| Qty. | 1 pc(s). |

HDC MHE 4 MP

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|---------|-----------------|------------|
| Depth | 34 mm | Depth (inches) | 1.339 inch |
| Height | 59.6 mm | Height (inches) | 2.346 inch |
| Width | 7.15 mm | Width (inches) | 0.281 inch |
| Net weight | 17 g | | |

Temperatures

| | |
|-------------------|-------------------|
| Limit temperature | -40 °C ... 125 °C |
|-------------------|-------------------|

General data

| | | | |
|------------------------------|--------------------|--------------------------------------|---------------------------------------|
| Insulation strength | 10 ¹² Ω | Material | Polycarbonate, glass fibre reinforced |
| Number of poles | 4 | Number of potentials | 4 |
| Plugging cycles | ≥ 500 | Pollution severity | 3 |
| Rated current (DIN EN 61984) | 16 A | Rated impulse voltage (DIN EN 61984) | 4 kV |
| Rated voltage (DIN EN 61984) | 250 V | Rated voltage according to UL/CSA | 600 V |
| Required plug-in slots | 0.5 | Series | ModuPlug |
| Surge voltage category | III | Type | Male |
| UL 94 flammability rating | V-0 | | |

PE connection data

| | |
|--------------------|-----------------------------------|
| Connection type PE | Screw connection via module frame |
|--------------------|-----------------------------------|

Version

| | | | |
|---|---------------------|---|-----------------------|
| Conductor cross-section, max. | 2.5 mm ² | Conductor cross-section, min. | 0.5 mm ² |
| Stripping length, rated connection | 10 mm | Type of connection | PUSH IN with actuator |
| Wire connection cross section AWG, max. | AWG 14 | Wire connection cross section AWG, min. | AWG 20 |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC002312 | ETIM 7.0 | EC002312 |
| ETIM 8.0 | EC002312 | ETIM 9.0 | EC002312 |
| ECLASS 9.0 | 27-44-02-92 | ECLASS 9.1 | 27-44-02-18 |
| ECLASS 10.0 | 27-44-02-92 | ECLASS 11.0 | 27-44-02-92 |
| ECLASS 12.0 | 27-44-02-92 | ECLASS 13.0 | 27-44-02-92 |

Environmental Product Compliance

| | |
|------------|---|
| REACH SVHC | Lead 7439-92-1 Potassium perfluorobutane sulfonate 29420-49-3 |
| SCIP | 9ed66ce7-2fe8-4987-bb46-06cab3f02292 |

Approvals

Approvals



| | |
|-------------------------|------------|
| UL File Number Search | UL Website |
| Certificate No. (cURus) | E92202 |

Creation date May 11, 2024 5:40:08 AM CEST

Catalogue status 04.05.2024 / We reserve the right to make technical changes.

HDC MHE 4 MP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Downloads

| | |
|---|--|
| Approval/Certificate/Document of Conformity | Manufacturer's declaration |
| Engineering Data | CAD data – STEP |
| Product Change Notification | Technical change - EN Technical change - DE |
| Catalogues | Catalogues in PDF-format |


HDC MHE 4 MP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany


www.weidmueller.com

Drawings

Product image



HDC MHE 4 FQT mit HDC MHE 4 MQT /
H07V-K2,5



HDC MHE 4 FQT with HDC MHE 4 MQT /
H07V-K2,5

